



Agastat Relays / TE Connectivity



2-1617788-3

Tau Wae:	2-1617788-3
Kaihanga / Waitohu:	Agastat Relays / TE Connectivity
Whakaahuatanga hua	FCA-210-0932M=M83536/9-032M
Ngā Rauemi:	
RoHS Tūnga	 Kei roto nga rangatira / RoHS kaore i te ture
Waeheere Stock	594 pcs stock
Tuhinga mai i	Hong Kong
Te Ara Tuhi	DHL/Fedex/TNT/UPS/EMS

TONO MO TE WHAKAHUA

Ko te whakaahua he tohu. Tirohia nga korero mo nga taipitopito hua.













Ngā whakaaturanga o 2-1617788-3

TAU WAE	2-1617788-3
KAIHANGA	Agastat Relays / TE Connectivity
WHAKAAHUATANGA	FCA-210-0932M=M83536/9-032M
WHAKAHAERE TOKO WHAKAHAERE / ROHS TŪNGA	Kei roto nga rangatira / RoHS kaore i te ture
HE RAHINGA KEI TE WĀTEA	594 pcs
PEPA RARAUNGA	
RAUPAPA	*
ĒTAHI INGOA	FCA-210-0932M M83536/9-032M
WHAKAHAERE TOKO WHAKAHAERE / ROHS TŪNGA	Contains lead / RoHS non-compliant
WHAKAAHUATANGA TAIPITOPITO	Relay Coil

Ngā tūtohu e hāngai ana

Agastat Relays / TE Connectivity 2-1617788-3	2-1617788-3 Kaiwhiwhi	2-1617788-3 Kaiwhakarato
2-1617788-3 Utu	2-1617788-3 Pikitia	2-1617788-3 Whakaahua
2-1617788-3 PDF Datasheet	2-1617788-3 Download Datasheet	Tuhinga 2-1617788-3
2-1617788-3 Stock	Hokona 2-1617788-3	Hokona Agastat Relays / TE Connectivity 2-1617788-3
Agastat Relays / TE Connectivity 2-1617788-3	Agastat Relays / TE Connectivity Kaiwhakarato	Agastat Relays / TE Connectivity Kaiwhiwhi
Agastat Relays / TE Connectivity 2-1617788-3	Axicom Relays / TE Connectivity 2-1617788-3	Buchanan Terminal Blocks / TE Connectivity 2-1617788-3
CGS Resistors / TE Connectivity 2-1617788-3	CII / TE Connectivity 2-1617788-3	Elcon Connectors / TE Connectivity 2-1617788-3
Holsworthy Resistors / TE Connectivity 2-1617788-3	Kilovac Relays / TE Connectivity 2-1617788-3	Neohm Resistors / TE Connectivity 2-1617788-3
OEG Relays / TE Connectivity 2-1617788-3	Products Unlimited Transformers & Relays / TE Conn 2-1617788-3	Q-Cee's / TE Connectivity 2-1617788-3
Schrack Relays / TE Connectivity 2-1617788-3	Sigma Inductors / TE Connectivity 2-1617788-3	TE Connectivity's Agastat Relays 2-1617788-3
TE Connectivity's Axicom Relays 2-1617788-3	TE Connectivity's Buchanan Terminal Blocks 2-1617788-3	TE Connectivity's CGS Resistors 2-1617788-3
TE Connectivity's CII 2-1617788-3	TE Connectivity's Elcon Connectors 2-1617788-3	TE Connectivity's Holsworthy Resistors 2-1617788-3
TE Connectivity's Neohm Resistors 2-1617788-3	TE Connectivity's OEG Relays 2-1617788-3	TE Connectivity's Q-Cee's 2-1617788-3
TE Connectivity's Schrack Relays 2-1617788-3	TE Connectivity's Sigma Inductors 2-1617788-3	TE Connectivity's Products Unlimited Transformers 2-1617788-3
TE Connectivity's Kilovac Relays 2-1617788-3		

Ngā Hua e hāngai ana

<div style="border: 1px solid #ccc; padding: 5px;">  <p>2-1617787-6 Kaihanga: Agastat Relays / TE Connectivity Whakaahuatanga: FCB-405-0530M=M83536/5-030M I roto i te taonga: 639 pcs</p> <p style="text-align: center; background-color: #ccc; padding: 2px; font-weight: bold;">RFQ</p> </div>	<div style="border: 1px solid #ccc; padding: 5px;">  <p>2-1617788-1 Kaihanga: Agastat Relays / TE Connectivity Whakaahuatanga: FCA-210-0931M=M83536/9-031M I roto i te taonga: 665 pcs</p> <p style="text-align: center; background-color: #ccc; padding: 2px; font-weight: bold;">RFQ</p> </div>
<div style="border: 1px solid #ccc; padding: 5px;">  <p>2-1617787-8 Kaihanga: Agastat Relays / TE Connectivity Whakaahuatanga: FCB-405-0531M=M83536/5-031M I roto i te taonga: 588 pcs</p> <p style="text-align: center; background-color: #ccc; padding: 2px; font-weight: bold;">RFQ</p> </div>	<div style="border: 1px solid #ccc; padding: 5px;">  <p>2-1617788-4 Kaihanga: Agastat Relays / TE Connectivity Whakaahuatanga: FCA-210-0933L=M83536/9-033L I roto i te taonga: 668 pcs</p> <p style="text-align: center; background-color: #ccc; padding: 2px; font-weight: bold;">RFQ</p> </div>
<div style="border: 1px solid #ccc; padding: 5px;">  <p>2-1617788-9 Kaihanga: Agastat Relays / TE Connectivity Whakaahuatanga: FCA-210-0935M=M83536/9-035M I roto i te taonga: 651 pcs</p> <p style="text-align: center; background-color: #ccc; padding: 2px; font-weight: bold;">RFQ</p> </div>	<div style="border: 1px solid #ccc; padding: 5px;">  <p>2-1617788-7 Kaihanga: Agastat Relays / TE Connectivity Whakaahuatanga: FCA-210-0934M=M83536/9-034M I roto i te taonga: 760 pcs</p> <p style="text-align: center; background-color: #ccc; padding: 2px; font-weight: bold;">RFQ</p> </div>
<div style="border: 1px solid #ccc; padding: 5px;">  <p>2-1617787-9 Kaihanga: Agastat Relays / TE Connectivity Whakaahuatanga: FCB-405-0532L=M83536/5-032L I roto i te taonga: 564 pcs</p> <p style="text-align: center; background-color: #ccc; padding: 2px; font-weight: bold;">RFQ</p> </div>	<div style="border: 1px solid #ccc; padding: 5px;">  <p>2-1617788-6 Kaihanga: Agastat Relays / TE Connectivity Whakaahuatanga: FCA-210-0934L=M83536/9-034L I roto i te taonga: 768 pcs</p> <p style="text-align: center; background-color: #ccc; padding: 2px; font-weight: bold;">RFQ</p> </div>
<div style="border: 1px solid #ccc; padding: 5px;">  <p>2-1617788-2 Kaihanga: Agastat Relays / TE Connectivity Whakaahuatanga: FCA-210-0932L=M83536/9-032L I roto i te taonga: 692 pcs</p> <p style="text-align: center; background-color: #ccc; padding: 2px; font-weight: bold;">RFQ</p> </div>	<div style="border: 1px solid #ccc; padding: 5px;">  <p>2-1617788-8 Kaihanga: Agastat Relays / TE Connectivity Whakaahuatanga: FCA-210-0935L=M83536/9-035L I roto i te taonga: 727 pcs</p> <p style="text-align: center; background-color: #ccc; padding: 2px; font-weight: bold;">RFQ</p> </div>
<div style="border: 1px solid #ccc; padding: 5px;">  <p>2-1617787-7 Kaihanga: Agastat Relays / TE Connectivity Whakaahuatanga: FCB-405-0531L=M83536/5-031L I roto i te taonga: 643 pcs</p> <p style="text-align: center; background-color: #ccc; padding: 2px; font-weight: bold;">RFQ</p> </div>	<div style="border: 1px solid #ccc; padding: 5px;">  <p>2-1617788-5 Kaihanga: Agastat Relays / TE Connectivity Whakaahuatanga: FCA-210-0933M=M83536/9-033M I roto i te taonga: 628 pcs</p> <p style="text-align: center; background-color: #ccc; padding: 2px; font-weight: bold;">RFQ</p> </div>