



Omron Automation & Safety

## A22NZ-2BL-NRA

Tau Wae:

A22NZ-2BL-NRA

Kaihanga / Waitohu:

Omron Automation & Safety

Whakaahuatanga hua

CONFIG SW BODY SELECTR NON-ILLUM

Ngā Rauemi:

A22NZ-2BL-NRA.pdf

RoHS Tūnga

Whakahaerehia te kore utu / RoHS

Waehere Stock

18211 pcs stock

Tuhinga mai i

Hong Kong

Te Ara Tuhi

DHL/Fedex/TNT/UPS/EMS



**TONO MO TE WHAKAHUA**

Ko te whakaahua he tohu. Tirohia nga korero mo nga taipitopito hua.

### Ngā whakaaturanga o A22NZ-2BL-NRA

|  |   |
|--|---|
| TAU WAE  | A22NZ-2BL-NRA                                     |
| KAIHANGA   | Omron Automation & Safety                         |
| WHAKAAHUATANGA   | CONFIG SW BODY SELECTR NON-ILLUM                  |
| WHAKAHAERE TOKO WHAKAHAERE / ROHS TŪNGA                          | Whakahaerehia te kore utu / RoHS                  |
| HE RAHINGA KEI TE WĀTEA  | 18211 pcs   |
| PEPA RARAUNGA  | A22NZ-2BL-NRA.pdf                                 |
| MOMO   | Momentary   |
| RAUPAPA  | A22NS   |
| E HIAHIA ANA   | Contact Block(s)                                  |
| PIHANGA WHAKAPAE PAEPAE  | 22.3mm (Round)                                    |
| ĒTAHI INGOA  | A22NZ2BLNRA                                       |
| TAUMATA WHAKAARO MOE (MSL)                                       | 1 (Unlimited)                                     |
| WHAKAHAERE TOKO WHAKAHAERE / ROHS TŪNGA                          | Lead free / RoHS Compliant                        |
| WHAKAAHUATANGA   | Non-Illuminated                                   |
| WHAKAAHUATANGA TAIPITOPITO                                       | Configurable Switch Body Selector Non-Illuminated |
| MOMO KAIHOKO   | Selector  |
| (TĪPAKOHIA TUATAHI, KA WHAKAMAHIA NGĀ TAEKA) RARAUNGA WHAKAMAHIA | Omron, A22NS                                      |

### Ngā tūtohu e hāngai ana

|   |   |  |
|---|---|--|
| Omron Automation & Safety A22NZ-2BL-NRA | A22NZ-2BL-NRA Kaiwhiwhi                   | A22NZ-2BL-NRA Kaiwhakarato                     |
| A22NZ-2BL-NRA Utu                       | A22NZ-2BL-NRA Pikitia                     | A22NZ-2BL-NRA Whakaahua                        |
| A22NZ-2BL-NRA PDF Datasheet             | A22NZ-2BL-NRA Download Datasheet          | Tuhinga A22NZ-2BL-NRA                          |
| A22NZ-2BL-NRA Stock                     | Hokona A22NZ-2BL-NRA                      | Hokona Omron Automation & Safety A22NZ-2BL-NRA |
| Omron Automation & Safety A22NZ-2BL-NRA | Omron Automation & Safety Kaiwhakarato    | Omron Automation & Safety Kaiwhiwhi            |
| Omron Automation & Safety A22NZ-2BL-NRA | Omron Automation and Safety A22NZ-2BL-NRA |  |

### Ngā Hua e hāngai ana

|   |   |
|---|---|
| <p><b>A22NZ-2BL-NWA</b><br/>Kaihanga: Omron Automation &amp; Safety<br/>Whakaahuatanga: CONFIG SW BODY SELECTR NON-ILLUM<br/>I roto i te taonga: 16751 pcs</p> <p><b>RFQ</b></p>        | <p><b>A22NZ-2BL-TOA</b><br/>Kaihanga: Omron Automation &amp; Safety<br/>Whakaahuatanga: CONFIG SW BODY SELECTOR ILLUM<br/>I roto i te taonga: 15429 pcs</p> <p><b>RFQ</b></p>           |
| <p><b>A22NZ-2BL-TAA</b><br/>Kaihanga: Omron Automation &amp; Safety<br/>Whakaahuatanga: CONFIG SW BODY SELECTOR ILLUM<br/>I roto i te taonga: 15312 pcs</p> <p><b>RFQ</b></p>           | <p><b>A22NZ-2BL-TGA</b><br/>Kaihanga: Omron Automation &amp; Safety<br/>Whakaahuatanga: CONFIG SW BODY SELECTOR ILLUM<br/>I roto i te taonga: 12201 pcs</p> <p><b>RFQ</b></p>           |
| <p><b>A22NZ-2BL-NYA</b><br/>Kaihanga: Omron Automation &amp; Safety<br/>Whakaahuatanga: CONFIG SW BODY SELECTR NON-ILLUM<br/>I roto i te taonga: 17896 pcs</p> <p><b>RFQ</b></p>        | <p><b>A22NZ-2BL-NBA</b><br/>Kaihanga: Omron Automation &amp; Safety<br/>Whakaahuatanga: CONFIG SW BODY SELECTR NON-ILLUM<br/>I roto i te taonga: 14145 pcs</p> <p><b>RFQ</b></p>        |
| <p><b>A22NW-3RM-TYA-G102-YE</b><br/>Kaihanga: Omron Automation &amp; Safety<br/>Whakaahuatanga: SWITCH SELECT 3POS DPST 10A 120V<br/>I roto i te taonga: 2600 pcs</p> <p><b>RFQ</b></p> | <p><b>A22NZ-2BL-NGA</b><br/>Kaihanga: Omron Automation &amp; Safety<br/>Whakaahuatanga: CONFIG SW BODY SELECTR NON-ILLUM<br/>I roto i te taonga: 17426 pcs</p> <p><b>RFQ</b></p>        |
| <p><b>A22NZ-2BL-01BA</b><br/>Kaihanga: Omron Automation &amp; Safety<br/>Whakaahuatanga: CONFIG SW BODY KEYLOCK NON-ILLUM<br/>I roto i te taonga: 8402 pcs</p> <p><b>RFQ</b></p>        | <p><b>A22NW-3RM-TYA-G102-YD</b><br/>Kaihanga: Omron Automation &amp; Safety<br/>Whakaahuatanga: SWITCH SELECT 3POS DPST 10A 120V<br/>I roto i te taonga: 3141 pcs</p> <p><b>RFQ</b></p> |
| <p><b>A22NZ-2BL-NAA</b><br/>Kaihanga: Omron Automation &amp; Safety<br/>Whakaahuatanga: CONFIG SW BODY SELECTR NON-ILLUM<br/>I roto i te taonga: 17961 pcs</p> <p><b>RFQ</b></p>        | <p><b>A22NZ-2BL-TRA</b><br/>Kaihanga: Omron Automation &amp; Safety<br/>Whakaahuatanga: CONFIG SW BODY SELECTOR ILLUM<br/>I roto i te taonga: 13963 pcs</p> <p><b>RFQ</b></p>           |

