

**Agastat Relays / TE Connectivity**

**2-1617787-7**

Tau Wae:	2-1617787-7
Kaihanga / Waitohu:	Agastat Relays / TE Connectivity
Whakaahuatanga hua	FCB-405-0531L=M83536/5-031L
Ngā Rauemi:	
RoHS Tūnga	Kei roto nga rangatira / RoHS kaore i te ture
Waehere Stock	643 pcs stock
Tuhinga mai i	Hong Kong
Te Ara Tuhi	DHL/Fedex/TNT/UPS/EMS

TONO MO TE WHAKAHUA

Ko te whakaahua he tohu. Tirohia nga korero mo nga taipitopito hua.

## Ngā whakaaturanga o 2-1617787-7

TAU WAE	2-1617787-7
KAIHANGA	Agastat Relays / TE Connectivity
WHAKAAHUATANGA	FCB-405-0531L=M83536/5-031L
WHAKAHAERE TOKO WHAKAHAERE / ROHS TŪNGA	Kei roto nga rangatira / RoHS kaore i te ture
HE RAHINGA KEI TE WĀTEA	643 pcs
PEPA RARAUNGA	
RAUPAPA	*
ĒTAHI INGOA	FCB-405-0531L M83536/5-031L
WHAKAHAERE TOKO WHAKAHAERE / ROHS TŪNGA	Contains lead / RoHS non-compliant
WHAKAAHUATANGA TAIPITOPITO	Relay Coil

**Ngā tūtohu e hāngai ana**

Agastat Relays / TE Connectivity 2-1617787-7	2-1617787-7 Kaiwhiwhi	2-1617787-7 Kaiwhakarato
2-1617787-7 Utu	2-1617787-7 Pikitia	2-1617787-7 Whakaahua
2-1617787-7 PDF Datasheet	2-1617787-7 Download Datasheet	Tuhinga 2-1617787-7
2-1617787-7 Stock	Hokona 2-1617787-7	Hokona Agastat Relays / TE Connectivity 2-1617787-7
Agastat Relays / TE Connectivity 2-1617787-7	Agastat Relays / TE Connectivity Kaiwhakarato	Agastat Relays / TE Connectivity Kaiwhiwhi
Agastat Relays / TE Connectivity 2-1617787-7	Axicom Relays / TE Connectivity 2-1617787-7	Buchanan Terminal Blocks / TE Connectivity 2-1617787-7
CGS Resistors / TE Connectivity 2-1617787-7	CII / TE Connectivity 2-1617787-7	Elcon Connectors / TE Connectivity 2-1617787-7
Holsworthy Resistors / TE Connectivity 2-1617787-7	Kilovac Relays / TE Connectivity 2-1617787-7	Neohm Resistors / TE Connectivity 2-1617787-7
OEG Relays / TE Connectivity 2-1617787-7	Products Unlimited Transformers & Relays / TE Conn 2-1617787-7	Q-Cee's / TE Connectivity 2-1617787-7
Schrack Relays / TE Connectivity 2-1617787-7	Sigma Inductors / TE Connectivity 2-1617787-7	TE Connectivity's Agastat Relays 2-1617787-7
TE Connectivity's Axicom Relays 2-1617787-7	TE Connectivity's Buchanan Terminal Blocks 2-1617787-7	TE Connectivity's CGS Resistors 2-1617787-7
TE Connectivity's CII 2-1617787-7	TE Connectivity's Elcon Connectors 2-1617787-7	TE Connectivity's Holsworthy Resistors 2-1617787-7
TE Connectivity's Neohm Resistors 2-1617787-7	TE Connectivity's OEG Relays 2-1617787-7	TE Connectivity's Q-Cee's 2-1617787-7
TE Connectivity's Schrack Relays 2-1617787-7	TE Connectivity's Sigma Inductors 2-1617787-7	TE Connectivity's Products Unlimited Transformers 2-1617787-7
TE Connectivity's Kilovac Relays 2-1617787-7		

**Ngā Hua e hāngai ana**

<div style="border: 1px solid #ccc; padding: 5px;"> <p><b>2-1617787-3</b> Kaihanga: Agastat Relays / TE Connectivity Whakaahuatanga: FCB-405-0529L=M83536/5-029L I roto i te taonga: 657 pcs</p> <p style="text-align: center;"><a href="#" style="background-color: #ccc; padding: 2px 5px;">RFQ</a></p> </div>	<div style="border: 1px solid #ccc; padding: 5px;"> <p><b>2-1617787-9</b> Kaihanga: Agastat Relays / TE Connectivity Whakaahuatanga: FCB-405-0532L=M83536/5-032L I roto i te taonga: 564 pcs</p> <p style="text-align: center;"><a href="#" style="background-color: #ccc; padding: 2px 5px;">RFQ</a></p> </div>
<div style="border: 1px solid #ccc; padding: 5px;"> <p><b>2-1617787-5</b> Kaihanga: Agastat Relays / TE Connectivity Whakaahuatanga: FCB-405-0530L=M83536/5-030L I roto i te taonga: 576 pcs</p> <p style="text-align: center;"><a href="#" style="background-color: #ccc; padding: 2px 5px;">RFQ</a></p> </div>	<div style="border: 1px solid #ccc; padding: 5px;"> <p><b>2-1617787-4</b> Kaihanga: Agastat Relays / TE Connectivity Whakaahuatanga: FCB-405-0529M=M83536/5-029M I roto i te taonga: 643 pcs</p> <p style="text-align: center;"><a href="#" style="background-color: #ccc; padding: 2px 5px;">RFQ</a></p> </div>
<div style="border: 1px solid #ccc; padding: 5px;"> <p><b>2-1617787-6</b> Kaihanga: Agastat Relays / TE Connectivity Whakaahuatanga: FCB-405-0530M=M83536/5-030M I roto i te taonga: 639 pcs</p> <p style="text-align: center;"><a href="#" style="background-color: #ccc; padding: 2px 5px;">RFQ</a></p> </div>	<div style="border: 1px solid #ccc; padding: 5px;"> <p><b>2-1617787-8</b> Kaihanga: Agastat Relays / TE Connectivity Whakaahuatanga: FCB-405-0531M=M83536/5-031M I roto i te taonga: 588 pcs</p> <p style="text-align: center;"><a href="#" style="background-color: #ccc; padding: 2px 5px;">RFQ</a></p> </div>
<div style="border: 1px solid #ccc; padding: 5px;"> <p><b>2-1617788-2</b> Kaihanga: Agastat Relays / TE Connectivity Whakaahuatanga: FCA-210-0932L=M83536/9-032L I roto i te taonga: 692 pcs</p> <p style="text-align: center;"><a href="#" style="background-color: #ccc; padding: 2px 5px;">RFQ</a></p> </div>	<div style="border: 1px solid #ccc; padding: 5px;"> <p><b>2-1617787-1</b> Kaihanga: Agastat Relays / TE Connectivity Whakaahuatanga: FCB-405-0528L=M83536/5-028L I roto i te taonga: 597 pcs</p> <p style="text-align: center;"><a href="#" style="background-color: #ccc; padding: 2px 5px;">RFQ</a></p> </div>
<div style="border: 1px solid #ccc; padding: 5px;"> <p><b>2-1617788-1</b> Kaihanga: Agastat Relays / TE Connectivity Whakaahuatanga: FCA-210-0931M=M83536/9-031M I roto i te taonga: 665 pcs</p> <p style="text-align: center;"><a href="#" style="background-color: #ccc; padding: 2px 5px;">RFQ</a></p> </div>	<div style="border: 1px solid #ccc; padding: 5px;"> <p><b>2-1617788-4</b> Kaihanga: Agastat Relays / TE Connectivity Whakaahuatanga: FCA-210-0933L=M83536/9-033L I roto i te taonga: 668 pcs</p> <p style="text-align: center;"><a href="#" style="background-color: #ccc; padding: 2px 5px;">RFQ</a></p> </div>
<div style="border: 1px solid #ccc; padding: 5px;"> <p><b>2-1617788-3</b> Kaihanga: Agastat Relays / TE Connectivity Whakaahuatanga: FCA-210-0932M=M83536/9-032M I roto i te taonga: 594 pcs</p> <p style="text-align: center;"><a href="#" style="background-color: #ccc; padding: 2px 5px;">RFQ</a></p> </div>	<div style="border: 1px solid #ccc; padding: 5px;"> <p><b>2-1617787-2</b> Kaihanga: Agastat Relays / TE Connectivity Whakaahuatanga: FCB-405-0528M=M83536/5-028M I roto i te taonga: 652 pcs</p> <p style="text-align: center;"><a href="#" style="background-color: #ccc; padding: 2px 5px;">RFQ</a></p> </div>