

Agastat Relays / TE Connectivity

3-1617785-9

Tau Wae:	3-1617785-9
Kaihanga / Waitohu:	Agastat Relays / TE Connectivity
Whakaahuatanga hua	FCA-410-1510M=M83536/15-010M
Ngā Rauemi:	
RoHS Tūnga	Kei roto nga rangatira / RoHS kaore i te ture
Waehere Stock	573 pcs stock
Tuhinga mai i	Hong Kong
Te Ara Tuhi	DHL/Fedex/TNT/UPS/EMS

TONO MO TE WHAKAHUA

Ko te whakaahua he tohu. Tirohia nga korero mo nga taipitopito hua.

Ngā whakaaturanga o 3-1617785-9

TAU WAE	3-1617785-9
KAIHANGA	Agastat Relays / TE Connectivity
WHAKAAHUATANGA	FCA-410-1510M=M83536/15-010M
WHAKAHAERE TOKO WHAKAHAERE / ROHS TŪNGA	Kei roto nga rangatira / RoHS kaore i te ture
HE RAHINGA KEI TE WĀTEA	573 pcs
PEPA RARAUNGA	
RAUPAPA	*
ĒTAHI INGOA	FCA-410-1510M M83536/15-010M
WHAKAHAERE TOKO WHAKAHAERE / ROHS TŪNGA	Contains lead / RoHS non-compliant
WHAKAAHUATANGA TAIPITOPITO	Relay Coil

Ngā tūtohu e hāngai ana

Agastat Relays / TE Connectivity 3-1617785-9	3-1617785-9 Kaiwhiwhi	3-1617785-9 Kaiwhakarato
3-1617785-9 Utu	3-1617785-9 Pikitia	3-1617785-9 Whakaahua
3-1617785-9 PDF Datasheet	3-1617785-9 Download Datasheet	Tuhinga 3-1617785-9
3-1617785-9 Stock	Hokona 3-1617785-9	Hokona Agastat Relays / TE Connectivity 3-1617785-9
Agastat Relays / TE Connectivity 3-1617785-9	Agastat Relays / TE Connectivity Kaiwhakarato	Agastat Relays / TE Connectivity Kaiwhiwhi
Agastat Relays / TE Connectivity 3-1617785-9	Axicom Relays / TE Connectivity 3-1617785-9	Buchanan Terminal Blocks / TE Connectivity 3-1617785-9
CGS Resistors / TE Connectivity 3-1617785-9	CII / TE Connectivity 3-1617785-9	Elcon Connectors / TE Connectivity 3-1617785-9
Holsworthy Resistors / TE Connectivity 3-1617785-9	Kilovac Relays / TE Connectivity 3-1617785-9	Neohm Resistors / TE Connectivity 3-1617785-9
OEG Relays / TE Connectivity 3-1617785-9	Products Unlimited Transformers & Relays / TE Conn 3-1617785-9	Q-Cee's / TE Connectivity 3-1617785-9
Schrack Relays / TE Connectivity 3-1617785-9	Sigma Inductors / TE Connectivity 3-1617785-9	TE Connectivity's Agastat Relays 3-1617785-9
TE Connectivity's Axicom Relays 3-1617785-9	TE Connectivity's Buchanan Terminal Blocks 3-1617785-9	TE Connectivity's CGS Resistors 3-1617785-9
TE Connectivity's CII 3-1617785-9	TE Connectivity's Elcon Connectors 3-1617785-9	TE Connectivity's Holsworthy Resistors 3-1617785-9
TE Connectivity's Neohm Resistors 3-1617785-9	TE Connectivity's OEG Relays 3-1617785-9	TE Connectivity's Q-Cee's 3-1617785-9
TE Connectivity's Schrack Relays 3-1617785-9	TE Connectivity's Sigma Inductors 3-1617785-9	TE Connectivity's Products Unlimited Transformers 3-1617785-9
TE Connectivity's Kilovac Relays 3-1617785-9		

Ngā Hua e hāngai ana

<div style="border: 1px solid #ccc; padding: 5px;"> <p>3-1617785-3 Kaihanga: Agastat Relays / TE Connectivity Whakaahuatanga: FCA-410-1507M=M83536/15-007M I roto i te taonga: 545 pcs</p> <p style="text-align: center; background-color: #ccc; padding: 2px; width: fit-content; margin: 0 auto;">RFQ</p> </div>	<div style="border: 1px solid #ccc; padding: 5px;"> <p>3-1617785-4 Kaihanga: Agastat Relays / TE Connectivity Whakaahuatanga: FCA-410-1508L=M83536/15-008L I roto i te taonga: 618 pcs</p> <p style="text-align: center; background-color: #ccc; padding: 2px; width: fit-content; margin: 0 auto;">RFQ</p> </div>
<div style="border: 1px solid #ccc; padding: 5px;"> <p>3-1617785-7 Kaihanga: Agastat Relays / TE Connectivity Whakaahuatanga: FCA-410-1509M=M83536/15-009M I roto i te taonga: 614 pcs</p> <p style="text-align: center; background-color: #ccc; padding: 2px; width: fit-content; margin: 0 auto;">RFQ</p> </div>	<div style="border: 1px solid #ccc; padding: 5px;"> <p>3-1617785-8 Kaihanga: Agastat Relays / TE Connectivity Whakaahuatanga: FCA-410-1510L=M83536/15-010L I roto i te taonga: 640 pcs</p> <p style="text-align: center; background-color: #ccc; padding: 2px; width: fit-content; margin: 0 auto;">RFQ</p> </div>
<div style="border: 1px solid #ccc; padding: 5px;"> <p>3-1617786-7 Kaihanga: Agastat Relays / TE Connectivity Whakaahuatanga: FCB-205-0210L=M83536/2-010L I roto i te taonga: 683 pcs</p> <p style="text-align: center; background-color: #ccc; padding: 2px; width: fit-content; margin: 0 auto;">RFQ</p> </div>	<div style="border: 1px solid #ccc; padding: 5px;"> <p>3-1617786-3 Kaihanga: Agastat Relays / TE Connectivity Whakaahuatanga: FCB-205-0207M=M83536/2-007M I roto i te taonga: 556 pcs</p> <p style="text-align: center; background-color: #ccc; padding: 2px; width: fit-content; margin: 0 auto;">RFQ</p> </div>
<div style="border: 1px solid #ccc; padding: 5px;"> <p>3-1617785-5 Kaihanga: Agastat Relays / TE Connectivity Whakaahuatanga: FCA-410-1508M=M83536/15-008M I roto i te taonga: 534 pcs</p> <p style="text-align: center; background-color: #ccc; padding: 2px; width: fit-content; margin: 0 auto;">RFQ</p> </div>	<div style="border: 1px solid #ccc; padding: 5px;"> <p>3-1617786-6 Kaihanga: Agastat Relays / TE Connectivity Whakaahuatanga: FCB-205-0209M=M83536/2-009M I roto i te taonga: 624 pcs</p> <p style="text-align: center; background-color: #ccc; padding: 2px; width: fit-content; margin: 0 auto;">RFQ</p> </div>
<div style="border: 1px solid #ccc; padding: 5px;"> <p>3-1617786-5 Kaihanga: Agastat Relays / TE Connectivity Whakaahuatanga: FCB-205-0209L=M83536/2-009L I roto i te taonga: 570 pcs</p> <p style="text-align: center; background-color: #ccc; padding: 2px; width: fit-content; margin: 0 auto;">RFQ</p> </div>	<div style="border: 1px solid #ccc; padding: 5px;"> <p>3-1617786-0 Kaihanga: Agastat Relays / TE Connectivity Whakaahuatanga: FCB-205-0205M=M83536/2-005M I roto i te taonga: 694 pcs</p> <p style="text-align: center; background-color: #ccc; padding: 2px; width: fit-content; margin: 0 auto;">RFQ</p> </div>
<div style="border: 1px solid #ccc; padding: 5px;"> <p>3-1617786-2 Kaihanga: Agastat Relays / TE Connectivity Whakaahuatanga: FCB-205-0207L=M83536/2-007L I roto i te taonga: 662 pcs</p> <p style="text-align: center; background-color: #ccc; padding: 2px; width: fit-content; margin: 0 auto;">RFQ</p> </div>	<div style="border: 1px solid #ccc; padding: 5px;"> <p>3-1617785-6 Kaihanga: Agastat Relays / TE Connectivity Whakaahuatanga: FCA-410-1509L=M83536/15-009L I roto i te taonga: 567 pcs</p> <p style="text-align: center; background-color: #ccc; padding: 2px; width: fit-content; margin: 0 auto;">RFQ</p> </div>