



Optek Technology / TT Electronics

OP600B

Tau Wae:
 Kaihanga / Waitohu:
 Whakaahuatanga hua
 Ngā Rauemi:
 RoHS Tūnga
 Waehere Stock
 Tuhiinga mai i
 Te Ara Tuhi

OP600B
 Optek Technology / TT Electronics
 PHOTOTRNS SILCN NPN HERMETC PILL
 OP600B.pdf
 Whakahaerehia te kore utu / RoHS
 37143 pcs stock
 Hong Kong
 DHL/Fedex/TNT/UPS/EMS

TONO MO TE WHAKAHUA

Ko te whakaahua he tohu. Tirohia nga korero mo nga taipitopito hua.

Ngā whakaaturanga o OP600B

TAU WAE	OP600B
KAIHANGA	Optek Technology / TT Electronics
WHAKAAHUATANGA	PHOTOTRNS SILCN NPN HERMETC PILL
WHAKAHAERE TOKO WHAKAHAERE / ROHS TŪNGA	Whakahaerehia te kore utu / RoHS
HE RAHINGA KEI TE WĀTEA	37143 pcs
PEPA RARAUNGA	OP600B.pdf
WAIMOTU	890nm
NGAOHIHI - TE WHAKATERE EMITTER BREAK (MAX)	25V
TIROHIA TE ANGLE	-
RAUPAPA	*
MANA - MAX	50mW
PACKAGING	Bulk
PAA / CASE	Pill
ĒTAHI INGOA	365-1611 OP600B-ND
WHAKATAKOTORANGA	Top View
TAE MAHI	-65°C ~ 125°C (TA)
MOMO TAE	Surface Mount
TAUMATA WHAKAARO MOE (MSL)	1 (Unlimited)
WHAKAHAERE TOKO WHAKAHAERE / ROHS TŪNGA	Lead free / RoHS Compliant
WHAKAAHUATANGA TAIPITOPITO	Phototransistor 890nm Top View Pill
I TEIE NEI - DARK (ID) (MAX)	100nA
I TEIE NEI - KOHIKOHI (IC) (MAX)	50mA

Ngā tūtohu e hāngai ana

Optek Technology / TT Electronics OP600B	OP600B Kaiwhiwhi	OP600B Kaiwhakarato
OP600B Utu	OP600B Pikitia	OP600B Whakaahua
OP600B PDF Datasheet	OP600B Download Datasheet	Tuhinga OP600B
OP600B Stock	Hokona OP600B	Hokona Optek Technology / TT Electronics OP600B
Optek Technology / TT Electronics OP600B	Optek Technology / TT Electronics Kaiwhakarato	Optek Technology / TT Electronics Kaiwhiwhi
Optek Technology / TT Electronics OP600B	OPTEK Technologies OP600B	Optek Technology OP600B
TT Electronics/Optek Technology OP600B		

Ngā Hua e hāngai ana

<p>OP602TXV Kaihanga: Optek Technology / TT Electronics Whakaahuatanga: PHOTOTRNS SILCN NPN HERMETC PILL I roto i te taonga: 6718 pcs RFQ</p>	<p>OP641SL Kaihanga: Optek Technology / TT Electronics Whakaahuatanga: PHOTOTRNS SILCN NPN HERMETC PILL I roto i te taonga: 4458 pcs RFQ</p>
<p>OP603TXV Kaihanga: Optek Technology / TT Electronics Whakaahuatanga: PHOTOTRNS SILCN NPN HERMETC PILL I roto i te taonga: 2518 pcs RFQ</p>	<p>OP643SL Kaihanga: Optek Technology / TT Electronics Whakaahuatanga: PHOTOTRNS SILCN NPN HERMET PILL I roto i te taonga: 52156 pcs RFQ</p>
<p>OP604TXV Kaihanga: Optek Technology / TT Electronics Whakaahuatanga: PHOTOTRNS SILCN NPN HERMETC PILL I roto i te taonga: 3481 pcs RFQ</p>	<p>OP642SL Kaihanga: Optek Technology / TT Electronics Whakaahuatanga: PHOTOTRNS SILCN NPN HERMETC PILL I roto i te taonga: 4012 pcs RFQ</p>
<p>OP600C Kaihanga: Optek Technology / TT Electronics Whakaahuatanga: PHOTOTRNS SILCN NPN HERMETC PILL I roto i te taonga: 41704 pcs RFQ</p>	<p>OP602TX Kaihanga: Optek Technology / TT Electronics Whakaahuatanga: PHOTOTRNS SILCN NPN HERMETC PILL I roto i te taonga: 3400 pcs RFQ</p>
<p>OP603TX Kaihanga: Optek Technology / TT Electronics Whakaahuatanga: PHOTOTRNS SILCN NPN HERMETC PILL I roto i te taonga: 2222 pcs RFQ</p>	<p>OP600A Kaihanga: Optek Technology / TT Electronics Whakaahuatanga: PHOTOTRNS SILCN NPN HERMETC PILL I roto i te taonga: 41332 pcs RFQ</p>
<p>OP604TX Kaihanga: Optek Technology / TT Electronics Whakaahuatanga: PHOTOTRNS SILCN NPN HERMETC PILL I roto i te taonga: 5559 pcs RFQ</p>	<p>OP604S Kaihanga: Optek Technology / TT Electronics Whakaahuatanga: PHOTOTRNS SILCN NPN HERMETC PILL I roto i te taonga: 250 pcs RFQ</p>

