



Omron Automation & Safety

## A22NZ-MGM-TOA

Tau Wae:

A22NZ-MGM-TOA

Kaihanga / Waitohu:

Omron Automation & Safety

Whakaahuatanga hua

CONFIG SW BODY PUSHBUTTON ILLUM

Ngā Rauemi:

A22NZ-MGM-TOA.pdf

RoHS Tūnga

Whakahaerehia te kore utu / RoHS

Waehere Stock

11578 pcs stock

Tuhinga mai i

Hong Kong

Te Ara Tuhi

DHL/Fedex/TNT/UPS/EMS



**TONO MO TE WHAKAHUA**

Ko te whakaahua he tohu. Tirohia nga korero mo nga taipitopito hua.

### Ngā whakaaturanga o A22NZ-MGM-TOA

TAU WAE	A22NZ-MGM-TOA
KAIHANGA	Omron Automation & Safety
WHAKAAHUATANGA	CONFIG SW BODY PUSHBUTTON ILLUM
WHAKAHAERE TOKO WHAKAHAERE / ROHS TŪNGA	Whakahaerehia te kore utu / RoHS
HE RAHINGA KEI TE WĀTEA	11578 pcs
PEPA RARAUNGA	A22NZ-MGM-TOA.pdf
MOMO	Momentary
RAUPAPA	A22NL
E HIAHIA ANA	Contact Block(s), Illumination Source
PIHANGA WHAKAPAE PAEPAE	22.3mm (Round)
ĒTAHI INGOA	A22NZMGTOA
TAUMATA WHAKAARO MOE (MSL)	1 (Unlimited)
WHAKAHAERE TOKO WHAKAHAERE / ROHS TŪNGA	Lead free / RoHS Compliant
WHAKAAHUATANGA	Illuminated - Orange
WHAKAAHUATANGA TAIPITOPITO	Configurable Switch Body Pushbutton, Round Illuminated - Orange
MOMO KAIHOKO	Pushbutton, Round
(TĪPAKOHIA TUATAHI, KA WHAKAMAHIA NGĀ TAEKA) RARAUNGA WHAKAMAHIA	Omron, A22NL

### Ngā tūtohu e hāngai ana

Omron Automation & Safety A22NZ-MGM-TOA	A22NZ-MGM-TOA Kaiwhiwhi	A22NZ-MGM-TOA Kaiwhakarato
A22NZ-MGM-TOA Utu	A22NZ-MGM-TOA Pikitia	A22NZ-MGM-TOA Whakaahua
A22NZ-MGM-TOA PDF Datasheet	A22NZ-MGM-TOA Download Datasheet	Tuhinga A22NZ-MGM-TOA
A22NZ-MGM-TOA Stock	Hokona A22NZ-MGM-TOA	Hokona Omron Automation & Safety A22NZ-MGM-TOA
Omron Automation & Safety A22NZ-MGM-TOA	Omron Automation & Safety Kaiwhakarato	Omron Automation & Safety Kaiwhiwhi
Omron Automation & Safety A22NZ-MGM-TOA	Omron Automation and Safety A22NZ-MGM-TOA	

### Ngā Hua e hāngai ana

<p><b>A22NZ-MGM-UGA</b> Kaihanga: Omron Automation &amp; Safety Whakaahuatanga: CONFIG SW BODY PUSHBUT NON-ILLUM I roto i te taonga: 15447 pcs</p> <p><b>RFQ</b></p>	<p><b>A22NZ-MGM-TWA</b> Kaihanga: Omron Automation &amp; Safety Whakaahuatanga: CONFIG SW BODY PUSHBUTTON ILLUM I roto i te taonga: 13071 pcs</p> <p><b>RFQ</b></p>
<p><b>A22NZ-MGM-TAA</b> Kaihanga: Omron Automation &amp; Safety Whakaahuatanga: CONFIG SW BODY PUSHBUTTON ILLUM I roto i te taonga: 14617 pcs</p> <p><b>RFQ</b></p>	<p><b>A22NZ-MGM-TYA</b> Kaihanga: Omron Automation &amp; Safety Whakaahuatanga: CONFIG SW BODY PUSHBUTTON ILLUM I roto i te taonga: 12626 pcs</p> <p><b>RFQ</b></p>
<p><b>A22NZ-MGM-NYA</b> Kaihanga: Omron Automation &amp; Safety Whakaahuatanga: CONFIG SW BODY PUSHBUT NON-ILLUM I roto i te taonga: 16135 pcs</p> <p><b>RFQ</b></p>	<p><b>A22NZ-MGM-UOA</b> Kaihanga: Omron Automation &amp; Safety Whakaahuatanga: CONFIG SW BODY PUSHBUT NON-ILLUM I roto i te taonga: 13437 pcs</p> <p><b>RFQ</b></p>
<p><b>A22NZ-MGM-TRA</b> Kaihanga: Omron Automation &amp; Safety Whakaahuatanga: CONFIG SW BODY PUSHBUTTON ILLUM I roto i te taonga: 12597 pcs</p> <p><b>RFQ</b></p>	<p><b>A22NZ-MGM-UAA</b> Kaihanga: Omron Automation &amp; Safety Whakaahuatanga: CONFIG SW BODY PUSHBUT NON-ILLUM I roto i te taonga: 14004 pcs</p> <p><b>RFQ</b></p>
<p><b>A22NZ-MGM-NWA</b> Kaihanga: Omron Automation &amp; Safety Whakaahuatanga: CONFIG SW BODY PUSHBUT NON-ILLUM I roto i te taonga: 16835 pcs</p> <p><b>RFQ</b></p>	<p><b>A22NZ-MGM-NGA</b> Kaihanga: Omron Automation &amp; Safety Whakaahuatanga: CONFIG SW BODY PUSHBUT NON-ILLUM I roto i te taonga: 16305 pcs</p> <p><b>RFQ</b></p>
<p><b>A22NZ-MGM-NRA</b> Kaihanga: Omron Automation &amp; Safety Whakaahuatanga: CONFIG SW BODY PUSHBUT NON-ILLUM I roto i te taonga: 16696 pcs</p> <p><b>RFQ</b></p>	<p><b>A22NZ-MGM-TGA</b> Kaihanga: Omron Automation &amp; Safety Whakaahuatanga: CONFIG SW BODY PUSHBUTTON ILLUM I roto i te taonga: 12775 pcs</p> <p><b>RFQ</b></p>

