



Omron Automation & Safety

A22NZ-RNA-UGA

Tau Wae:

A22NZ-RNA-UGA

Kaihanga / Waitohu:

Omron Automation & Safety

Whakaahuatanga hua

CONFIG SW BODY PUSHBUT NON-ILLUM

Ngā Rauemi:

A22NZ-RNA-UGA.pdf

RoHS Tūnga

Whakahaerehia te kore utu / RoHS

Waehere Stock

21725 pcs stock

Tuhinga mai i

Hong Kong

Te Ara Tuhi

DHL/Fedex/TNT/UPS/EMS



TONO MO TE WHAKAHUA

Ko te whakaahua he tohu. Tirohia nga korero mo nga taipitopito hua.

Ngā whakaaturanga o A22NZ-RNA-UGA

TAU WAE	A22NZ-RNA-UGA
KAIHANGA	Omron Automation & Safety
WHAKAAHUATANGA	CONFIG SW BODY PUSHBUT NON-ILLUM
WHAKAHAERE TOKO WHAKAHAERE / ROHS TŪNGA	Whakahaerehia te kore utu / RoHS
HE RAHINGA KEI TE WĀTEA	21725 pcs
PEPA RARAUNGA	A22NZ-RNA-UGA.pdf
MOMO	Maintained
RAUPAPA	A22NN
E HIAHIA ANA	Contact Block(s)
PIHANGA WHAKAPAE PAEPAE	22.3mm (Round)
ĒTAHI INGOA	A22NZRNAUGA
TAUMATA WHAKAARO MOE (MSL)	1 (Unlimited)
WHAKAHAERE TOKO WHAKAHAERE / ROHS TŪNGA	Lead free / RoHS Compliant
WHAKAAHUATANGA	Non-Illuminated
WHAKAAHUATANGA TAIPITOPITO	Configurable Switch Body Pushbutton, Round Non-Illuminated
MOMO KAIHOKO	Pushbutton, Round
(TĪPAKOHIA TUATAHI, KA WHAKAMAHIA NGĀ TAEKA) RARAUNGA WHAKAMAHIA	Omron, A22NN

Ngā tūtohu e hāngai ana

Omron Automation & Safety A22NZ-RNA-UGA	A22NZ-RNA-UGA Kaiwhiwhi	A22NZ-RNA-UGA Kaiwhakarato
A22NZ-RNA-UGA Utu	A22NZ-RNA-UGA Pikitia	A22NZ-RNA-UGA Whakaahua
A22NZ-RNA-UGA PDF Datasheet	A22NZ-RNA-UGA Download Datasheet	Tuhinga A22NZ-RNA-UGA
A22NZ-RNA-UGA Stock	Hokona A22NZ-RNA-UGA	Hokona Omron Automation & Safety A22NZ-RNA-UGA
Omron Automation & Safety A22NZ-RNA-UGA	Omron Automation & Safety Kaiwhakarato	Omron Automation & Safety Kaiwhiwhi
Omron Automation & Safety A22NZ-RNA-UGA	Omron Automation and Safety A22NZ-RNA-UGA	

Ngā Hua e hāngai ana

<p>A22NZ-RNA-URA</p> <p>Kaihanga: Omron Automation & Safety Whakaahuatanga: CONFIG SW BODY PUSHBUT NON-ILLUM I roto i te taonga: 20909 pcs</p> <p>RFQ</p>	<p>A22NZ-RNA-UYA</p> <p>Kaihanga: Omron Automation & Safety Whakaahuatanga: CONFIG SW BODY PUSHBUT NON-ILLUM I roto i te taonga: 18907 pcs</p> <p>RFQ</p>
<p>A22NZ-RNA-TOA</p> <p>Kaihanga: Omron Automation & Safety Whakaahuatanga: CONFIG SW BODY PUSHBUTTON ILLUM I roto i te taonga: 19488 pcs</p> <p>RFQ</p>	<p>A22NZ-RNM-NBA</p> <p>Kaihanga: Omron Automation & Safety Whakaahuatanga: CONFIG SW BODY PUSHBUT NON-ILLUM I roto i te taonga: 24433 pcs</p> <p>RFQ</p>
<p>A22NZ-RNA-UWA</p> <p>Kaihanga: Omron Automation & Safety Whakaahuatanga: CONFIG SW BODY PUSHBUT NON-ILLUM I roto i te taonga: 22116 pcs</p> <p>RFQ</p>	<p>A22NZ-RNA-TYA</p> <p>Kaihanga: Omron Automation & Safety Whakaahuatanga: CONFIG SW BODY PUSHBUTTON ILLUM I roto i te taonga: 20126 pcs</p> <p>RFQ</p>
<p>A22NZ-RNA-UAA</p> <p>Kaihanga: Omron Automation & Safety Whakaahuatanga: CONFIG SW BODY PUSHBUT NON-ILLUM I roto i te taonga: 20312 pcs</p> <p>RFQ</p>	<p>A22NZ-RNA-TWA</p> <p>Kaihanga: Omron Automation & Safety Whakaahuatanga: CONFIG SW BODY PUSHBUTTON ILLUM I roto i te taonga: 21314 pcs</p> <p>RFQ</p>
<p>A22NZ-RNA-TGA</p> <p>Kaihanga: Omron Automation & Safety Whakaahuatanga: CONFIG SW BODY PUSHBUTTON ILLUM I roto i te taonga: 19008 pcs</p> <p>RFQ</p>	<p>A22NZ-RNA-TRA</p> <p>Kaihanga: Omron Automation & Safety Whakaahuatanga: CONFIG SW BODY PUSHBUTTON ILLUM I roto i te taonga: 23708 pcs</p> <p>RFQ</p>
<p>A22NZ-RNM-NAA</p> <p>Kaihanga: Omron Automation & Safety Whakaahuatanga: CONFIG SW BODY PUSHBUT NON-ILLUM I roto i te taonga: 23223 pcs</p> <p>RFQ</p>	<p>A22NZ-RNA-UOA</p> <p>Kaihanga: Omron Automation & Safety Whakaahuatanga: CONFIG SW BODY PUSHBUT NON-ILLUM I roto i te taonga: 17729 pcs</p> <p>RFQ</p>

