

SURFBOARDS®

THE BREADBOARDING MEDIUM FOR SURFACE MOUNT™




33000 SERIES APPLICATION SPECIFIC ADAPTERS

IDS33518
REV A-10-2011

MODEL **33518**

8 LEAD .5 mm PITCH DEVICES

DEVICE LEAD WIDTH 1.5, To Max 3.0 MM



ACCEPTS

PARTIAL LISTING

FAIRCHILD	8LD,MICROPAK 1.6MM SQ.
ON SEMI	ULLGA8 1.5x1.5,0.5P UQFN8 1.5x1.5,0.5P UQFN8 1.6x1.6,0.5P
TEXAS INST.	RSE (S-PQFP-N8) UQFN RUG (S-PQFP-N8)

ALWAYS CONSULT DEVICE DATA SHEET TO INSURE PROPER FIT

Feature Pins on .1 in. Centers designed for use with Solderless breadboards, Conventional Breadboards, and Sockets with standard .1 in. centers.

Use For Prototyping, Device Test or Evaluation and SMD to Through Hole Conversion.

JUST ADD PARTS AND PLUG-IN™

FIG.	MM	IN.	NOTE:
A	20.32	.800	BOARD WIDTH +- .5mm .020in.
B	10.16	.400	BOARD HEIGHT +- .5mm .020in.
C	2.54	.100	SIP PIN SPACE +- .20mm .008in.
D, D1	2.1	.083	PAD CENTERLINE
E	.5	.020	DEVICE LEAD PITCH
F	1.4	.055	PAD LENGTH
G	.3	.012	PAD WIDTH
H	.2	.008	GAP
I	3.0	.118	MAX LEAD WIDTH
J	1.5	.059	TYPICAL LEAD WIDTH
P	3.3	.130	LENGTH FROM SHOULDER +- .5mm .020in.
S	1.57	.062	PIN SHOULDER HEIGHT
W	.5	.020	PIN WIDTH

TOLERANCES: If not noted are + 20%. Nominal values are given. Controlling unit is Millimeters. Values rounded to nearest decimal. Slight Variations due to manufacturing process can occur.

Copyright 2011 by Capital Advanced Technologies, Inc. All rights reserved. Surfboards is a registered trademark of Capital Advanced Technologies, Inc. The Breadboarding medium for surface mount, Just add parts and plug-in, and the Leaf Circuit Logo are trademarks of Capital Advanced Technologies, Inc. All other trademarks are the property of their respective owners. Specifications, availability, and price is subject to change without notice. All information given is believed to be accurate but is not guaranteed. The user of information given or products represented by such information is responsible for determining the suitability of said information or products for a given purpose. No inducement is intended or permission granted for infringement of any patent or unauthorized use of any intellectual property of Capital Advanced Technologies or others.



CAPITAL ADVANCED TECHNOLOGIES, INC.

CAROL STREAM, ILLINOIS. USA PHONE 630-690-1696 FAX 630-690-2498

WWW.CapitalAdvanced.Com

MADE
IN
USA