

**Agastat Relays / TE Connectivity**

### 3-1393236-9

Tau Wae:	3-1393236-9
Kaihanga / Waitohu:	Agastat Relays / TE Connectivity
Whakaahuatanga hua:	V23092A1048A801=SNR
Ngā Rauemi:	3-1393236-9.pdf
RoHS Tūnga:	Whakahaerehia te kore utu / RoHS
Waehere Stock:	12302 pcs stock
Tuhinga mai i:	Hong Kong
Te Ara Tuhi:	DHL/Fedex/TNT/UPS/EMS

**TONO MO TE WHAKAHUA**

Ko te whakaahua he tohu. Tirohia nga korero mo nga taipitopito hua.

**Ngā whakaaturanga o 3-1393236-9**

TAU WAE	3-1393236-9
KAIHANGA	Agastat Relays / TE Connectivity
WHAKAAHUATANGA	V23092A1048A801=SNR
WHAKAHAERE TOKO WHAKAHAERE / ROHS TŪNGA	Whakahaerehia te kore utu / RoHS
HE RAHINGA KEI TE WĀTEA	12302 pcs
PEPA RARAUNGA	3-1393236-9.pdf
RAUPAPA	*
ĒTAHI INGOA	V23092A1048A801
WHAKAHAERE TOKO WHAKAHAERE / ROHS TŪNGA	Lead free / RoHS Compliant
WHAKAAHUATANGA TAIPITOPITO	Relay Coil

### Ngā tūtohu e hāngai ana

Agastat Relays / TE Connectivity 3-1393236-9	3-1393236-9 Kaiwhiwhi	3-1393236-9 Kaiwhakarato
3-1393236-9 Utu	3-1393236-9 Pikitia	3-1393236-9 Whakaahua
3-1393236-9 PDF Datasheet	3-1393236-9 Download Datasheet	Tuhinga 3-1393236-9
3-1393236-9 Stock	Hokona 3-1393236-9	Hokona Agastat Relays / TE Connectivity 3-1393236-9
Agastat Relays / TE Connectivity 3-1393236-9	Agastat Relays / TE Connectivity Kaiwhakarato	Agastat Relays / TE Connectivity Kaiwhiwhi
Agastat Relays / TE Connectivity 3-1393236-9	Axicom Relays / TE Connectivity 3-1393236-9	Buchanan Terminal Blocks / TE Connectivity 3-1393236-9
CGS Resistors / TE Connectivity 3-1393236-9	CII / TE Connectivity 3-1393236-9	Elcon Connectors / TE Connectivity 3-1393236-9
Holsworthy Resistors / TE Connectivity 3-1393236-9	Kilovac Relays / TE Connectivity 3-1393236-9	Neohm Resistors / TE Connectivity 3-1393236-9
OEG Relays / TE Connectivity 3-1393236-9	Products Unlimited Transformers & Relays / TE Conn 3-1393236-9	Q-Cee's / TE Connectivity 3-1393236-9
Schrack Relays / TE Connectivity 3-1393236-9	Sigma Inductors / TE Connectivity 3-1393236-9	TE Connectivity's Agastat Relays 3-1393236-9
TE Connectivity's Axicom Relays 3-1393236-9	TE Connectivity's Buchanan Terminal Blocks 3-1393236-9	TE Connectivity's CGS Resistors 3-1393236-9
TE Connectivity's CII 3-1393236-9	TE Connectivity's Elcon Connectors 3-1393236-9	TE Connectivity's Holsworthy Resistors 3-1393236-9
TE Connectivity's Neohm Resistors 3-1393236-9	TE Connectivity's OEG Relays 3-1393236-9	TE Connectivity's Q-Cee's 3-1393236-9
TE Connectivity's Schrack Relays 3-1393236-9	TE Connectivity's Sigma Inductors 3-1393236-9	TE Connectivity's Products Unlimited Transformers 3-1393236-9
TE Connectivity's Kilovac Relays 3-1393236-9		

### Ngā Hua e hāngai ana

<div style="display: flex; align-items: center;"> <div> <p><b>3-1393240-8</b></p> <p>Kaihanga: Agastat Relays / TE Connectivity Whakaahuatanga: RT334F05 I roto i te taonga: 27492 pcs</p> <p style="text-align: center; background-color: #ccc; padding: 2px 5px;"><b>RFQ</b></p> </div> </div>	<div style="display: flex; align-items: center;"> <div> <p><b>3-1393231-8</b></p> <p>Kaihanga: Agastat Relays / TE Connectivity Whakaahuatanga: RELAY GEN PURPOSE SPDT 12A 24V I roto i te taonga: 2916 pcs</p> <p style="text-align: center; background-color: #ccc; padding: 2px 5px;"><b>RFQ</b></p> </div> </div>
<div style="display: flex; align-items: center;"> <div> <p><b>3-1393240-0</b></p> <p>Kaihanga: Agastat Relays / TE Connectivity Whakaahuatanga: RELAY GEN PURP I roto i te taonga: 23607 pcs</p> <p style="text-align: center; background-color: #ccc; padding: 2px 5px;"><b>RFQ</b></p> </div> </div>	<div style="display: flex; align-items: center;"> <div> <p><b>3-1393240-1</b></p> <p>Kaihanga: Agastat Relays / TE Connectivity Whakaahuatanga: RELAY GEN PURP I roto i te taonga: 16753 pcs</p> <p style="text-align: center; background-color: #ccc; padding: 2px 5px;"><b>RFQ</b></p> </div> </div>
<div style="display: flex; align-items: center;"> <div> <p><b>3-1393278-7</b></p> <p>Kaihanga: Agastat Relays / TE Connectivity Whakaahuatanga: RELAY AUTOMOTIVE SPDT 45A 24V I roto i te taonga: 25032 pcs</p> <p style="text-align: center; background-color: #ccc; padding: 2px 5px;"><b>RFQ</b></p> </div> </div>	<div style="display: flex; align-items: center;"> <div> <p><b>3-1393235-9</b></p> <p>Kaihanga: Agastat Relays / TE Connectivity Whakaahuatanga: RELAY GEN PURP I roto i te taonga: 13240 pcs</p> <p style="text-align: center; background-color: #ccc; padding: 2px 5px;"><b>RFQ</b></p> </div> </div>
<div style="display: flex; align-items: center;"> <div> <p><b>3-1393225-2</b></p> <p>Kaihanga: Agastat Relays / TE Connectivity Whakaahuatanga: RY613018 I roto i te taonga: 27937 pcs</p> <p style="text-align: center; background-color: #ccc; padding: 2px 5px;"><b>RFQ</b></p> </div> </div>	<div style="display: flex; align-items: center;"> <div> <p><b>3-1393231-5</b></p> <p>Kaihanga: Agastat Relays / TE Connectivity Whakaahuatanga: RELAY GEN PURP I roto i te taonga: 7964 pcs</p> <p style="text-align: center; background-color: #ccc; padding: 2px 5px;"><b>RFQ</b></p> </div> </div>
<div style="display: flex; align-items: center;"> <div> <p><b>3-1393225-5</b></p> <p>Kaihanga: Agastat Relays / TE Connectivity Whakaahuatanga: RY613060 I roto i te taonga: 12505 pcs</p> <p style="text-align: center; background-color: #ccc; padding: 2px 5px;"><b>RFQ</b></p> </div> </div>	<div style="display: flex; align-items: center;"> <div> <p><b>3-1393224-9</b></p> <p>Kaihanga: Agastat Relays / TE Connectivity Whakaahuatanga: RY210032 I roto i te taonga: 16580 pcs</p> <p style="text-align: center; background-color: #ccc; padding: 2px 5px;"><b>RFQ</b></p> </div> </div>
<div style="display: flex; align-items: center;"> <div> <p><b>3-1393237-2</b></p> <p>Kaihanga: Agastat Relays / TE Connectivity Whakaahuatanga: RELAY GEN PURPOSE DPDT 8A 22V I roto i te taonga: 27790 pcs</p> <p style="text-align: center; background-color: #ccc; padding: 2px 5px;"><b>RFQ</b></p> </div> </div>	<div style="display: flex; align-items: center;"> <div> <p><b>3-1393240-9</b></p> <p>Kaihanga: Agastat Relays / TE Connectivity Whakaahuatanga: RELAY GEN PURP I roto i te taonga: 14096 pcs</p> <p style="text-align: center; background-color: #ccc; padding: 2px 5px;"><b>RFQ</b></p> </div> </div>