

Honeywell

Honeywell Sensing and Productivity Solutions

F07018057

Tau Wae:	F07018057
Kaihanga / Waitohu:	Honeywell Sensing and Productivity Solutions
Whakaahuatanga hua:	POS TRANS-XDCR JP/2 8/3.0% 1/8
Ngā Rauemi:	
RoHS Tūnga:	Whakahaerehia te kore utu / RoHS
Waehere Stock:	3700 pcs stock
Tuhinga mai i:	Hong Kong
Te Ara Tuhi:	DHL/Fedex/TNT/UPS/EMS

TONO MO TE WHAKAHUA

Ko te whakaahua he tohu. Tirohia nga korero mo nga taipitopito hua.

Ngā whakaaturanga o F07018057

TAU WAE	F07018057
KAIHANGA	Honeywell Sensing and Productivity Solutions
WHAKAAHUATANGA	POS TRANS-XDCR JP/2 8/3.0% 1/8
WHAKAHAERE TOKO WHAKAHAERE / ROHS TŪNGA	Whakahaerehia te kore utu / RoHS
HE RAHINGA KEI TE WĀTEA	3700 pcs
PEPA RARAUNGA	
RAUPAPA	-
TAUMATA WHAKAARO MOE (MSL)	1 (Unlimited)
WHAKAHAERE TOKO WHAKAHAERE / ROHS TŪNGA	Lead free / RoHS Compliant
WHAKAAHUATANGA TAIPITOPITO	Sensor

Ngā tūtohu e hāngai ana

Honeywell Sensing and Productivity Solutions F07018057	F07018057 Kaiwhiwhi	F07018057 Kaiwhakarato
F07018057 Utu	F07018057 Pikitia	F07018057 Whakaahua
F07018057 PDF Datasheet	F07018057 Download Datasheet	Tuhinga F07018057
F07018057 Stock	Hokona F07018057	Hokona Honeywell Sensing and Productivity Solutions F07018057
Honeywell Sensing and Productivity Solutions F07018057	Honeywell Sensing and Productivity Solutions Kaiwhakarato	Honeywell Sensing and Productivity Solutions Kaiwhiwhi
Honeywell Sensing and Productivity Solutions F07018057	HONEYWELL F07018057	Honeywell Sensing and Control EMEA F07018057
Honeywell Sensing and Productivity Solutions T&M F07018057		

Ngā Hua e hāngai ana

<p>F07018036 Kaihanga: Honeywell Sensing and Productivity Solutions Whakaahuatanga: POS TRANS-XDCR JP/2 2K/3.0% 1/8 I roto i te taonga: 5876 pcs</p> <p style="text-align: center; background-color: #ccc; padding: 2px;">RFQ</p>	<p>F07A-0102 Kaihanga: TPK America LLC Whakaahuatanga: TOUCH DISPLAY FUSION 7 7" PCAP I roto i te taonga: 4720 pcs</p> <p style="text-align: center; background-color: #ccc; padding: 2px;">RFQ</p>
<p>F07018005 Kaihanga: Honeywell Sensing and Productivity Solutions Whakaahuatanga: POS TRANS-XDCR JP/2 1K/5.0% I roto i te taonga: 4762 pcs</p> <p style="text-align: center; background-color: #ccc; padding: 2px;">RFQ</p>	<p>F07018031 Kaihanga: Honeywell Sensing and Productivity Solutions Whakaahuatanga: POS TRANS-XDCR JP/2 2.5K/5.0% I roto i te taonga: 5955 pcs</p> <p style="text-align: center; background-color: #ccc; padding: 2px;">RFQ</p>
<p>F07A-0114 Kaihanga: TPK America LLC Whakaahuatanga: TOUCH DISPLAY FUSION I roto i te taonga: 4812 pcs</p> <p style="text-align: center; background-color: #ccc; padding: 2px;">RFQ</p>	<p>F07A-0104 Kaihanga: TPK America LLC Whakaahuatanga: TOUCH DISPLAY FUSION I roto i te taonga: 5327 pcs</p> <p style="text-align: center; background-color: #ccc; padding: 2px;">RFQ</p>
<p>F07018039 Kaihanga: Honeywell Sensing and Productivity Solutions Whakaahuatanga: POS TRANS-XDCR JP/2 200/5.0% 1/8 I roto i te taonga: 5020 pcs</p> <p style="text-align: center; background-color: #ccc; padding: 2px;">RFQ</p>	<p>F07018030 Kaihanga: Honeywell Sensing and Productivity Solutions Whakaahuatanga: POS TRANS-XDCR JP/2 5K/5.0% 1/8 I roto i te taonga: 3069 pcs</p> <p style="text-align: center; background-color: #ccc; padding: 2px;">RFQ</p>
<p>F07018026 Kaihanga: Honeywell Sensing and Productivity Solutions Whakaahuatanga: POS TRANS-XDCR JP/2 500/5.0% I roto i te taonga: 3112 pcs</p> <p style="text-align: center; background-color: #ccc; padding: 2px;">RFQ</p>	<p>F07018056 Kaihanga: Honeywell Sensing and Productivity Solutions Whakaahuatanga: POS TRANS-XDCR JP/2 4/3.0% 1/8 I roto i te taonga: 3281 pcs</p> <p style="text-align: center; background-color: #ccc; padding: 2px;">RFQ</p>
<p>F07018021 Kaihanga: Honeywell Sensing and Productivity Solutions Whakaahuatanga: POS TRANS-XDCR JP/2 10K/5.0% 1/8 I roto i te taonga: 6704 pcs</p> <p style="text-align: center; background-color: #ccc; padding: 2px;">RFQ</p>	<p>F07018023 Kaihanga: Honeywell Sensing and Productivity Solutions Whakaahuatanga: POS TRANS-XDCR JP/2 1K/5.0% 1/8 I roto i te taonga: 3543 pcs</p> <p style="text-align: center; background-color: #ccc; padding: 2px;">RFQ</p>