

Advanced Photonix (Luna

Optoelectronics)

PDB-C119-LC

Tau Wae:	PDB-C119-LC
Kaihanga / Waitohu:	Advanced Photonix (Luna Optoelectronics)
Whakaahuatanga hua:	PHOTODIODE BLUE 7.95MM SQ TO-5
Ngā Rauemi:	PDB-C119-LC.pdf
RoHS Tūnga:	Kei roto nga rangatira / RoHS kaore i te ture
Waehere Stock:	3968 pcs stock
Tuhinga mai i:	Hong Kong
Te Ara Tuhi:	DHL/Fedex/TNT/UPS/EMS

TONO MO TE WHAKAHUA

Ko te whakaahua he tohu. Tirohia nga korero mo nga taipitopito hua.

Ngā whakaaturanga o PDB-C119-LC

TAU WAE	PDB-C119-LC
KAIHANGA	Advanced Photonix (Luna Optoelectronics)
WHAKAAHUATANGA	PHOTODIODE BLUE 7.95MM SQ TO-5
WHAKAHAERE TOKO WHAKAHAERE / ROHS TŪNGA	Kei roto nga rangatira / RoHS kaore i te ture
HE RAHINGA KEI TE WĀTEA	3968 pcs
PEPA RARAUNGA	PDB-C119-LC.pdf
WAIMOTU	950nm
NGAOHIHI - DC REVERSE (VR) (MAX)	100V
TIROHIA TE ANGLE	102°
ARONGA WHAKAARO	350nm ~ 1100nm
RAUPAPA	-
WHAKAUTU @ NM	-
WĀ WHAKAUTU	50ns
PACKAGING	Bulk
PAA / CASE	TO-5
ĒTAHI INGOA	PT-PDB-C119-LC
TAE MAHI	-40°C ~ 125°C
MOMO TAE	Through Hole
TAUMATA WHAKAARO MOE (MSL)	1 (Unlimited)
WHAKAHAERE TOKO WHAKAHAERE / ROHS TŪNGA	Contains lead / RoHS non-compliant
MOMO TONO	PIN
WHAKAAHUATANGA TAIPITOPITO	Photodiode 950nm 50ns 102° TO-5
I TEIE NEI - POROKE (KORE)	5nA
TAE - WHAKAPAI AKE	Blue
AREA MAHINGA	7.95mm ²

Ngā tūtohu e hāngai ana

Advanced Photonix (Luna Optoelectronics) PDB-C119-LC	PDB-C119-LC Kaiwhiwhi	PDB-C119-LC Kaiwhakarato
PDB-C119-LC Utu	PDB-C119-LC Pikitia	PDB-C119-LC Whakaahua
PDB-C119-LC PDF Datasheet	PDB-C119-LC Download Datasheet	Tuhinga PDB-C119-LC
PDB-C119-LC Stock	Hokona PDB-C119-LC	Hokona Advanced Photonix (Luna Optoelectronics) PDB-C119-LC
Advanced Photonix (Luna Optoelectronics) PDB-C119-LC	Advanced Photonix (Luna Optoelectronics) Kaiwhakarato	Advanced Photonix (Luna Optoelectronics) Kaiwhiwhi
Advanced Photonix (Luna Optoelectronics) PDB-C119-LC	Advanced Photonix Inc PDB-C119-LC	Advanced Photonix (Luna Optoelectronics) PDB-C119-LC
Luna Optoelectronics PDB-C119-LC		

Ngā Hua e hāngai ana

<div style="display: flex; align-items: center;"> <div> <p style="font-weight: bold; color: blue; font-size: 0.8em;">PDB-C116</p> <p style="font-size: 0.7em;">Kaihanga: Advanced Photonix (Luna Optoelectronics) Whakaahuatanga: PHOTODIODE BLUE .073MM SQ SMD I roto i te taonga: 3755 pcs</p> <div style="background-color: #ccc; padding: 2px; text-align: center; font-weight: bold; font-size: 0.7em; margin-top: 5px;">RFQ</div> </div> </div>	<div style="display: flex; align-items: center;"> <div> <p style="font-weight: bold; color: blue; font-size: 0.8em;">PDB-C119-LP</p> <p style="font-size: 0.7em;">Kaihanga: Advanced Photonix (Luna Optoelectronics) Whakaahuatanga: PHOTO DIODE BLUE ENHANCE TO-5 I roto i te taonga: 5137 pcs</p> <div style="background-color: #ccc; padding: 2px; text-align: center; font-weight: bold; font-size: 0.7em; margin-top: 5px;">RFQ</div> </div> </div>
<div style="display: flex; align-items: center;"> <div> <p style="font-weight: bold; color: blue; font-size: 0.8em;">PDB-C119-L</p> <p style="font-size: 0.7em;">Kaihanga: Advanced Photonix (Luna Optoelectronics) Whakaahuatanga: PHOTODIODE BLUE 7.95MM SQ TO-5 I roto i te taonga: 3111 pcs</p> <div style="background-color: #ccc; padding: 2px; text-align: center; font-weight: bold; font-size: 0.7em; margin-top: 5px;">RFQ</div> </div> </div>	<div style="display: flex; align-items: center;"> <div> <p style="font-weight: bold; color: blue; font-size: 0.8em;">PDB-C114</p> <p style="font-size: 0.7em;">Kaihanga: Advanced Photonix (Luna Optoelectronics) Whakaahuatanga: PHOTODIODE BLUE 17.63MM SQ TO-5 I roto i te taonga: 6559 pcs</p> <div style="background-color: #ccc; padding: 2px; text-align: center; font-weight: bold; font-size: 0.7em; margin-top: 5px;">RFQ</div> </div> </div>
<div style="display: flex; align-items: center;"> <div> <p style="font-weight: bold; color: blue; font-size: 0.8em;">PDB-C120</p> <p style="font-size: 0.7em;">Kaihanga: Advanced Photonix (Luna Optoelectronics) Whakaahuatanga: PHOTODIODE BLUE 0.073MM SQ TO-46 I roto i te taonga: 4799 pcs</p> <div style="background-color: #ccc; padding: 2px; text-align: center; font-weight: bold; font-size: 0.7em; margin-top: 5px;">RFQ</div> </div> </div>	<div style="display: flex; align-items: center;"> <div> <p style="font-weight: bold; color: blue; font-size: 0.8em;">PDB-C115</p> <p style="font-size: 0.7em;">Kaihanga: Advanced Photonix (Luna Optoelectronics) Whakaahuatanga: PHOTODIODE BLUE 5.07MM SQ TO-5 I roto i te taonga: 5636 pcs</p> <div style="background-color: #ccc; padding: 2px; text-align: center; font-weight: bold; font-size: 0.7em; margin-top: 5px;">RFQ</div> </div> </div>
<div style="display: flex; align-items: center;"> <div> <p style="font-weight: bold; color: blue; font-size: 0.8em;">PDB-C120-I</p> <p style="font-size: 0.7em;">Kaihanga: Advanced Photonix (Luna Optoelectronics) Whakaahuatanga: PHOTODIODE BLUE 0.073MM SQ TO-18 I roto i te taonga: 4246 pcs</p> <div style="background-color: #ccc; padding: 2px; text-align: center; font-weight: bold; font-size: 0.7em; margin-top: 5px;">RFQ</div> </div> </div>	<div style="display: flex; align-items: center;"> <div> <p style="font-weight: bold; color: blue; font-size: 0.8em;">PDB-C120-L</p> <p style="font-size: 0.7em;">Kaihanga: Advanced Photonix (Luna Optoelectronics) Whakaahuatanga: PHOTODIODE BLUE 0.073MM SQ TO-46 I roto i te taonga: 5115 pcs</p> <div style="background-color: #ccc; padding: 2px; text-align: center; font-weight: bold; font-size: 0.7em; margin-top: 5px;">RFQ</div> </div> </div>
<div style="display: flex; align-items: center;"> <div> <p style="font-weight: bold; color: blue; font-size: 0.8em;">PDB-C118</p> <p style="font-size: 0.7em;">Kaihanga: Advanced Photonix (Luna Optoelectronics) Whakaahuatanga: PHOTODIODE BL 9.09MM RND HS TO-5 I roto i te taonga: 6346 pcs</p> <div style="background-color: #ccc; padding: 2px; text-align: center; font-weight: bold; font-size: 0.7em; margin-top: 5px;">RFQ</div> </div> </div>	<div style="display: flex; align-items: center;"> <div> <p style="font-weight: bold; color: blue; font-size: 0.8em;">PDB-C131</p> <p style="font-size: 0.7em;">Kaihanga: Advanced Photonix (Luna Optoelectronics) Whakaahuatanga: PHOTODIODE BLUE .65MM SQ T1 FLAT I roto i te taonga: 4375 pcs</p> <div style="background-color: #ccc; padding: 2px; text-align: center; font-weight: bold; font-size: 0.7em; margin-top: 5px;">RFQ</div> </div> </div>
<div style="display: flex; align-items: center;"> <div> <p style="font-weight: bold; color: blue; font-size: 0.8em;">PDB-C119</p> <p style="font-size: 0.7em;">Kaihanga: Advanced Photonix (Luna Optoelectronics) Whakaahuatanga: PHOTODIODE BLUE 7.95MM SQ TO-5 I roto i te taonga: 6879 pcs</p> <div style="background-color: #ccc; padding: 2px; text-align: center; font-weight: bold; font-size: 0.7em; margin-top: 5px;">RFQ</div> </div> </div>	<div style="display: flex; align-items: center;"> <div> <p style="font-weight: bold; color: blue; font-size: 0.8em;">PDB-C122</p> <p style="font-size: 0.7em;">Kaihanga: Advanced Photonix (Luna Optoelectronics) Whakaahuatanga: PHOTODIODE BLUE ENH 0.3X0.3 CERM I roto i te taonga: 2971 pcs</p> <div style="background-color: #ccc; padding: 2px; text-align: center; font-weight: bold; font-size: 0.7em; margin-top: 5px;">RFQ</div> </div> </div>