



Omron Automation & Safety

A165W-J3AR

Tau Wae:

A165W-J3AR

Kaihanga / Waitohu:

Omron Automation & Safety

Whakaahuatanga hua

CONFIG SW BODY SELECTOR ILLUM

Ngā Rauemi:

A165W-J3AR.pdf

RoHS Tūnga

Whakahaerehia te kore utu / RoHS

Waehere Stock

3918 pcs stock

Tuhinga mai i

Hong Kong

Te Ara Tuhi

DHL/Fedex/TNT/UPS/EMS



TONO MO TE WHAKAHUA

Ko te whakaahua he tohu. Tirohia nga korero mo nga taipitopito hua.

Ngā whakaaturanga o A165W-J3AR

TAU WAE	A165W-J3AR
KAIHANGA	Omron Automation & Safety
WHAKAAHUATANGA	CONFIG SW BODY SELECTOR ILLUM
WHAKAHAERE TOKO WHAKAHAERE / ROHS TŪNGA	Whakahaerehia te kore utu / RoHS
HE RAHINGA KEI TE WĀTEA	3918 pcs
PEPA RARAUNGA	A165W-J3AR.pdf
MOMO	Momentary
RAUPAPA	A165W
E HIAHIA ANA	Contact Block(s), Illumination Source
PIHANGA WHAKAPAE PAEPAE	16mm (Round)
ĒTAHI INGOA	A165WJ3AR
TAUMATA WHAKAARO MOE (MSL)	1 (Unlimited)
WHAKAHAERE TOKO WHAKAHAERE / ROHS TŪNGA	Lead free / RoHS Compliant
WHAKAAHUATANGA	Illuminated - Red
WHAKAAHUATANGA TAIPITOPITO	Configurable Switch Body Selector Illuminated - Red
MOMO KAIHOKO	Selector
(TĪPAKOHIA TUATAHI, KA WHAKAMAHIA NGĀ TAEKA) RARAUNGA WHAKAMAHIA	Omron, A165W

Ngā tūtohu e hāngai ana

Omron Automation & Safety A165W-J3AR	A165W-J3AR Kaiwhiwhi	A165W-J3AR Kaiwhakarato
A165W-J3AR Utu	A165W-J3AR Pikitia	A165W-J3AR Whakaahua
A165W-J3AR PDF Datasheet	A165W-J3AR Download Datasheet	Tuhinga A165W-J3AR
A165W-J3AR Stock	Hokona A165W-J3AR	Hokona Omron Automation & Safety A165W-J3AR
Omron Automation & Safety A165W-J3AR	Omron Automation & Safety Kaiwhakarato	Omron Automation & Safety Kaiwhiwhi
Omron Automation & Safety A165W-J3AR	Omron Automation and Safety A165W-J3AR	

Ngā Hua e hāngai ana

<p>A165W-J3MR-24D-2 Kaihanga: Omron Automation & Safety Whakaahuatanga: SWITCH SELECT 3POS DPDT 5A 125V I roto i te taonga: 2049 pcs</p> <p>RFQ</p>	<p>A165W-J2MY-24D-2 Kaihanga: Omron Automation & Safety Whakaahuatanga: SWITCH SELECT 2POS DPDT 5A 125V I roto i te taonga: 2255 pcs</p> <p>RFQ</p>
<p>A165W-J2MY Kaihanga: Omron Automation & Safety Whakaahuatanga: CONFIG SW BODY SELECTOR ILLUM I roto i te taonga: 3870 pcs</p> <p>RFQ</p>	<p>A165W-J3MG-24D-2 Kaihanga: Omron Automation & Safety Whakaahuatanga: SWITCH SELECT 3POS DPDT 5A 125V I roto i te taonga: 2167 pcs</p> <p>RFQ</p>
<p>A165W-J3AG Kaihanga: Omron Automation & Safety Whakaahuatanga: CONFIG SW BODY SELECTOR ILLUM I roto i te taonga: 3355 pcs</p> <p>RFQ</p>	<p>A165W-J3AY Kaihanga: Omron Automation & Safety Whakaahuatanga: CONFIG SW BODY SELECTOR ILLUM I roto i te taonga: 3727 pcs</p> <p>RFQ</p>
<p>A165W-J3MR Kaihanga: Omron Automation & Safety Whakaahuatanga: CONFIG SW BODY SELECTOR ILLUM I roto i te taonga: 2959 pcs</p> <p>RFQ</p>	<p>A165W-J2MY-24D-1 Kaihanga: Omron Automation & Safety Whakaahuatanga: SWITCH SELECT 2POS SPDT 5A 125V I roto i te taonga: 2001 pcs</p> <p>RFQ</p>
<p>A165W-J3MY Kaihanga: Omron Automation & Safety Whakaahuatanga: CONFIG SW BODY SELECTOR ILLUM I roto i te taonga: 3916 pcs</p> <p>RFQ</p>	<p>A165W-J3MG Kaihanga: Omron Automation & Safety Whakaahuatanga: CONFIG SW BODY SELECTOR ILLUM I roto i te taonga: 3222 pcs</p> <p>RFQ</p>
<p>A165W-J2MR-24D-1 Kaihanga: Omron Automation & Safety Whakaahuatanga: SWITCH SELECT 2POS SPDT 5A 125V I roto i te taonga: 2249 pcs</p> <p>RFQ</p>	<p>A165W-J2MR-24D-2 Kaihanga: Omron Automation & Safety Whakaahuatanga: SWITCH SELECT 2POS DPDT 5A 125V I roto i te taonga: 1982 pcs</p> <p>RFQ</p>

