

ams

CMV2000-3E5M1LP

Tau Wae:	CMV2000-3E5M1LP
Kaihanga / Waitohu:	ams
Whakaahuatanga hua	IMAGE SENSORS & COLOR SENSORS AR
Ngā Rauemi:	1.CMV2000-3E5M1LP.pdf 2.CMV2000-3E5M1LP.pdf
RoHs Tūnga	Whakahaerehia te kore utu / RoHS
Waehere Stock	333 pcs stock
Tuhinga mai i	Hong Kong
Te Ara Tuhi	DHL/Fedex/TNT/UPS/EMS

TONO MO TE WHAKAHUA

Ko te whakaahua he tohu. Tirohia nga korero mo nga taipitopito hua.

Ngā whakaaturanga o CMV2000-3E5M1LP

TAU WAE	CMV2000-3E5M1LP
KAIHANGA	ams
WHAKAAHUATANGA	IMAGE SENSORS & COLOR SENSORS AR
WHAKAHAERE TOKO WHAKAHAERE / ROHS TŪNGA	Whakahaerehia te kore utu / RoHS
HE RAHINGA KEI TE WĀTEA	333 pcs
PEPA RARAUNGA	1.CMV2000-3E5M1LP.pdf 2.CMV2000-3E5M1LP.pdf
TUHINGA O MUA	1.8V, 3.3V
MOMO	CMOS
PŪRERE PŪRERE WHAKARATO	95-LGA
RAUPAPA	-
RAHI PIKA	5.5µm x 5.5µm
PACKAGING	-
PAA / CASE	-
ĒTAHI INGOA	301870006
TAE MAHI	-30°C ~ 70°C (TA)
TAUMATA WHAKAARO MOE (MSL)	3 (168 Hours)
WHAKAHAERE TOKO WHAKAHAERE / ROHS TŪNGA	Lead free / RoHS Compliant
MAHERE TUARUA	340
WHAKAAHUATANGA TAIPITOPITO	CMOS Image Sensor 2048H x 1088V 5.5µm x 5.5µm 95-LGA
PIHANGA PIKA MAHI	2048H x 1088V

Ngā tūtohu e hāngai ana

ams CMV2000-3E5M1LP	CMV2000-3E5M1LP Kaiwhiwhi	CMV2000-3E5M1LP Kaiwhakarato
CMV2000-3E5M1LP Utu	CMV2000-3E5M1LP Pikitia	CMV2000-3E5M1LP Whakaahua
CMV2000-3E5M1LP PDF Datasheet	CMV2000-3E5M1LP Download Datasheet	Tuhinga CMV2000-3E5M1LP
CMV2000-3E5M1LP Stock	Hokona CMV2000-3E5M1LP	Hokona ams CMV2000-3E5M1LP
ams CMV2000-3E5M1LP	ams Kaiwhakarato	ams Kaiwhiwhi
ams CMV2000-3E5M1LP	ams AG CMV2000-3E5M1LP	TAOS / ams CMV2000-3E5M1LP

Ngā Hua e hāngai ana

<p>CMV20000-1E5C1PA Kaihanga: ams Whakaahuatanga: IMAGE SENSORS & COLOR SENSORS AR I roto i te taonga: 22 pcs</p> <p style="text-align: center; background-color: #ccc; padding: 2px 10px; font-weight: bold;">RFQ</p>	<p>CMV20000-1E5M1PA Kaihanga: ams Whakaahuatanga: IMAGE SENSORS & COLOR SENSORS AR I roto i te taonga: 23 pcs</p> <p style="text-align: center; background-color: #ccc; padding: 2px 10px; font-weight: bold;">RFQ</p>
<p>CMV2000-3E5C1CA Kaihanga: ams Whakaahuatanga: IMAGE SENSORS & COLOR SENSORS AR I roto i te taonga: 258 pcs</p> <p style="text-align: center; background-color: #ccc; padding: 2px 10px; font-weight: bold;">RFQ</p>	<p>CMV2000-3E5C1LP Kaihanga: ams Whakaahuatanga: IMAGE SENSORS & COLOR SENSORS AR I roto i te taonga: 317 pcs</p> <p style="text-align: center; background-color: #ccc; padding: 2px 10px; font-weight: bold;">RFQ</p>
<p>CMV2000-3E5C1PA Kaihanga: ams Whakaahuatanga: IMAGE SENSORS & COLOR SENSORS AR I roto i te taonga: 4914 pcs</p> <p style="text-align: center; background-color: #ccc; padding: 2px 10px; font-weight: bold;">RFQ</p>	<p>CMV2000-3E5M1CA Kaihanga: ams Whakaahuatanga: IMAGE SENSORS & COLOR SENSORS AR I roto i te taonga: 301 pcs</p> <p style="text-align: center; background-color: #ccc; padding: 2px 10px; font-weight: bold;">RFQ</p>
<p>CMV2000-3E12M1PP Kaihanga: ams Whakaahuatanga: IMAGE SENSORS & COLOR SENSORS AR I roto i te taonga: 244 pcs</p> <p style="text-align: center; background-color: #ccc; padding: 2px 10px; font-weight: bold;">RFQ</p>	<p>CMV20000-1E5M1PN Kaihanga: ams Whakaahuatanga: CMV20000-1E5M1PN QA I roto i te taonga: 28 pcs</p> <p style="text-align: center; background-color: #ccc; padding: 2px 10px; font-weight: bold;">RFQ</p>
<p>CMV2000-3E5M1PN Kaihanga: ams Whakaahuatanga: IMAGE SENSORS & COLOR SENSORS AR I roto i te taonga: 261 pcs</p> <p style="text-align: center; background-color: #ccc; padding: 2px 10px; font-weight: bold;">RFQ</p>	<p>CMV2000-3E5M1PP Kaihanga: ams Whakaahuatanga: IMAGE SENSORS & COLOR SENSORS AR I roto i te taonga: 266 pcs</p> <p style="text-align: center; background-color: #ccc; padding: 2px 10px; font-weight: bold;">RFQ</p>
<p>CMV2000-3E5C1PP Kaihanga: ams Whakaahuatanga: IMAGE SENSORS & COLOR SENSORS AR I roto i te taonga: 289 pcs</p> <p style="text-align: center; background-color: #ccc; padding: 2px 10px; font-weight: bold;">RFQ</p>	<p>CMV2000-3E5M1PA Kaihanga: ams Whakaahuatanga: IMAGE SENSORS & COLOR SENSORS AR I roto i te taonga: 352 pcs</p> <p style="text-align: center; background-color: #ccc; padding: 2px 10px; font-weight: bold;">RFQ</p>