

BROADCOM
connecting everything

Limited)

BROADCO
connecting everything

HEDS-6500#J13

Tau Wae:	HEDS-6500#J13
Kaihanga / Waitohu:	Avago Technologies (Broadcom Limited)
Whakaahuatanga hua:	ROTARY ENCODER OPTICAL 1024PPR
Ngā Rauemi:	HEDS-6500#J13.pdf
RoHS Tūnga:	Whakahaerehia te kore utu / RoHS
Waehere Stock:	6638 pcs stock
Tuhinga mai i:	Hong Kong
Te Ara Tuhi:	DHL/Fedex/TNT/UPS/EMS

TONO MO TE WHAKAHUA

Ko te whakaahua he tohu. Tirohia nga korero mo nga taipitopito hua.

Ngā whakaaturanga o HEDS-6500#J13

TAU WAE	HEDS-6500#J13
KAIHANGA	Avago Technologies (Broadcom Limited)
WHAKAAHUATANGA	ROTARY ENCODER OPTICAL 1024PPR
WHAKAHAERE TOKO WHAKAHAERE / ROHS TŪNGA	Whakahaerehia te kore utu / RoHS
HE RAHINGA KEI TE WĀTEA	6638 pcs
PEPA RARAUNGA	HEDS-6500#J13.pdf
TUHINGA O MUA	5V
KĀHUA WHAKAMUTUNGA	Cable with Connector
RAUPAPA	HEDS
KO TE ROTATIONAL LIFE (CYCLES MIN)	-
PULSES IA REVOLUTION	1024
MOMO PUTANGA	Quadrature (Incremental)
WHAKATAKOTORANGA	Vertical
MOMO TAE	Chassis Mount, Motors
TAUMATA WHAKAARO MOE (MSL)	1 (Unlimited)
WHAKAHAERE TOKO WHAKAHAERE / ROHS TŪNGA	Lead free / RoHS Compliant
MOMO KUPUTUHI	Optical
TUHINGA	No
HANGAIA KI TE WHAKAWHITI	No
MOMO KAIHOKO	8mm Open Center

Ngā tūtohu e hāngai ana

Avago Technologies (Broadcom Limited) HEDS-6500#J13	HEDS-6500#J13 Kaiwhiwhi	HEDS-6500#J13 Kaiwhakarato
HEDS-6500#J13 Utu	HEDS-6500#J13 Pikitia	HEDS-6500#J13 Whakaahua
HEDS-6500#J13 PDF Datasheet	HEDS-6500#J13 Download Datasheet	Tuhinga HEDS-6500#J13
HEDS-6500#J13 Stock	Hokona HEDS-6500#J13	Hokona Avago Technologies (Broadcom Limited) HEDS-6500#J13
Avago Technologies (Broadcom Limited) HEDS-6500#J13	Avago Technologies (Broadcom Limited) Kaiwhakarato	Avago Technologies (Broadcom Limited) Kaiwhiwhi
Avago Technologies (Broadcom Limited) HEDS-6500#J13	Avago Technologies Limited HEDS-6500#J13	Avago Technologies US Inc. HEDS-6500#J13
Avago Technologies HEDS-6500#J13	Avago Technologies (Broadcom Limited) HEDS-6500#J13	Broadcom Limited HEDS-6500#J13

Ngā Hua e hāngai ana

<div style="display: flex; align-items: center;"> <div> <p>HEDS-6510#005</p> <p>Kaihanga: Avago Technologies (Broadcom Limited)</p> <p>Whakaahuatanga: CENTERING TOOL HEDX-65XX 3/16"</p> <p>I roto i te taonga: 6969 pcs</p> <div style="background-color: #ccc; padding: 5px; text-align: center; width: fit-content; margin-top: 10px;">RFQ</div> </div> </div>	<div style="display: flex; align-items: center;"> <div> <p>HEDS-6510#011</p> <p>Kaihanga: Avago Technologies (Broadcom Limited)</p> <p>Whakaahuatanga: CENTERING TOOL HEDX-65XX 4MM</p> <p>I roto i te taonga: 6832 pcs</p> <div style="background-color: #ccc; padding: 5px; text-align: center; width: fit-content; margin-top: 10px;">RFQ</div> </div> </div>
<div style="display: flex; align-items: center;"> <div> <p>HEDS-6510#009</p> <p>Kaihanga: Avago Technologies (Broadcom Limited)</p> <p>Whakaahuatanga: CENTERING TOOL HEDX-65XX 1/2"</p> <p>I roto i te taonga: 3444 pcs</p> <div style="background-color: #ccc; padding: 5px; text-align: center; width: fit-content; margin-top: 10px;">RFQ</div> </div> </div>	<div style="display: flex; align-items: center;"> <div> <p>HEDS-6500#J10</p> <p>Kaihanga: Avago Technologies (Broadcom Limited)</p> <p>Whakaahuatanga: ROTARY ENCODER OPTICAL 1024PPR</p> <p>I roto i te taonga: 5057 pcs</p> <div style="background-color: #ccc; padding: 5px; text-align: center; width: fit-content; margin-top: 10px;">RFQ</div> </div> </div>
<div style="display: flex; align-items: center;"> <div> <p>HEDS-6500#B09</p> <p>Kaihanga: Avago Technologies (Broadcom Limited)</p> <p>Whakaahuatanga: ROTARY ENCODER OPTICAL 1000PPR</p> <p>I roto i te taonga: 4328 pcs</p> <div style="background-color: #ccc; padding: 5px; text-align: center; width: fit-content; margin-top: 10px;">RFQ</div> </div> </div>	<div style="display: flex; align-items: center;"> <div> <p>HEDS-6510#010</p> <p>Kaihanga: Avago Technologies (Broadcom Limited)</p> <p>Whakaahuatanga: CENTERING TOOL HEDX-65XX 5/8"</p> <p>I roto i te taonga: 5469 pcs</p> <div style="background-color: #ccc; padding: 5px; text-align: center; width: fit-content; margin-top: 10px;">RFQ</div> </div> </div>
<div style="display: flex; align-items: center;"> <div> <p>HEDS-6510#006</p> <p>Kaihanga: Avago Technologies (Broadcom Limited)</p> <p>Whakaahuatanga: CENTERING TOOL HEDX-65XX 1/4"</p> <p>I roto i te taonga: 4812 pcs</p> <div style="background-color: #ccc; padding: 5px; text-align: center; width: fit-content; margin-top: 10px;">RFQ</div> </div> </div>	<div style="display: flex; align-items: center;"> <div> <p>HEDS-6500#J11</p> <p>Kaihanga: Avago Technologies (Broadcom Limited)</p> <p>Whakaahuatanga: ROTARY ENCODER OPTICAL 1024PPR</p> <p>I roto i te taonga: 2910 pcs</p> <div style="background-color: #ccc; padding: 5px; text-align: center; width: fit-content; margin-top: 10px;">RFQ</div> </div> </div>
<div style="display: flex; align-items: center;"> <div> <p>HEDS-6510#008</p> <p>Kaihanga: Avago Technologies (Broadcom Limited)</p> <p>Whakaahuatanga: CENTERING TOOL HEDX-65XX 3/8"</p> <p>I roto i te taonga: 6212 pcs</p> <div style="background-color: #ccc; padding: 5px; text-align: center; width: fit-content; margin-top: 10px;">RFQ</div> </div> </div>	<div style="display: flex; align-items: center;"> <div> <p>HEDS-6500#B13</p> <p>Kaihanga: Avago Technologies (Broadcom Limited)</p> <p>Whakaahuatanga: ROTARY ENCODER OPTICAL 1000PPR</p> <p>I roto i te taonga: 6015 pcs</p> <div style="background-color: #ccc; padding: 5px; text-align: center; width: fit-content; margin-top: 10px;">RFQ</div> </div> </div>
<div style="display: flex; align-items: center;"> <div> <p>HEDS-6500#B12</p> <p>Kaihanga: Avago Technologies (Broadcom Limited)</p> <p>Whakaahuatanga: ROTARY ENCODER OPTICAL 1000PPR</p> <p>I roto i te taonga: 4950 pcs</p> <div style="background-color: #ccc; padding: 5px; text-align: center; width: fit-content; margin-top: 10px;">RFQ</div> </div> </div>	<div style="display: flex; align-items: center;"> <div> <p>HEDS-6500#J06</p> <p>Kaihanga: Avago Technologies (Broadcom Limited)</p> <p>Whakaahuatanga: ROTARY ENCODER OPTICAL 1024PPR</p> <p>I roto i te taonga: 3288 pcs</p> <div style="background-color: #ccc; padding: 5px; text-align: center; width: fit-content; margin-top: 10px;">RFQ</div> </div> </div>