

**Agastat Relays / TE Connectivity**

## 9-1617786-9

Tau Wae:	9-1617786-9
Kaihanga / Waitohu:	Agastat Relays / TE Connectivity
Whakaahuatanga hua	FCB-405-0512L=M83536/5-012L
Ngā Rauemi:	
RoHS Tūnga	Kei roto nga rangatira / RoHS kaore i te ture
Waehere Stock	527 pcs stock
Tuhinga mai i	Hong Kong
Te Ara Tuhi	DHL/Fedex/TNT/UPS/EMS

TONO MO TE WHAKAHUA

Ko te whakaahua he tohu. Tirohia nga korero mo nga taipitopito hua.

### Ngā whakaaturanga o 9-1617786-9

TAU WAE	9-1617786-9
KAIHANGA	Agastat Relays / TE Connectivity
WHAKAAHUATANGA	FCB-405-0512L=M83536/5-012L
WHAKAHAERE TOKO WHAKAHAERE / ROHS TŪNGA	Kei roto nga rangatira / RoHS kaore i te ture
HE RAHINGA KEI TE WĀTEA	527 pcs
PEPA RARAUNGA	
RAUPAPA	*
ĒTAHI INGOA	FCB-405-0512L M83536/5-012L
WHAKAHAERE TOKO WHAKAHAERE / ROHS TŪNGA	Contains lead / RoHS non-compliant
WHAKAAHUATANGA TAIPITOPITO	Relay Coil

### Ngā tūtohu e hāngai ana

Agastat Relays / TE Connectivity 9-1617786-9	9-1617786-9 Kaiwhiwhi	9-1617786-9 Kaiwhakarato
9-1617786-9 Utu	9-1617786-9 Pikitia	9-1617786-9 Whakaahua
9-1617786-9 PDF Datasheet	9-1617786-9 Download Datasheet	Tuhinga 9-1617786-9
9-1617786-9 Stock	Hokona 9-1617786-9	Hokona Agastat Relays / TE Connectivity 9-1617786-9
Agastat Relays / TE Connectivity 9-1617786-9	Agastat Relays / TE Connectivity Kaiwhakarato	Agastat Relays / TE Connectivity Kaiwhiwhi
Agastat Relays / TE Connectivity 9-1617786-9	Axicom Relays / TE Connectivity 9-1617786-9	Buchanan Terminal Blocks / TE Connectivity 9-1617786-9
CGS Resistors / TE Connectivity 9-1617786-9	CII / TE Connectivity 9-1617786-9	Elcon Connectors / TE Connectivity 9-1617786-9
Holsworthy Resistors / TE Connectivity 9-1617786-9	Kilovac Relays / TE Connectivity 9-1617786-9	Neohm Resistors / TE Connectivity 9-1617786-9
OEG Relays / TE Connectivity 9-1617786-9	Products Unlimited Transformers & Relays / TE Conn 9-1617786-9	Q-Cee's / TE Connectivity 9-1617786-9
Schrack Relays / TE Connectivity 9-1617786-9	Sigma Inductors / TE Connectivity 9-1617786-9	TE Connectivity's Agastat Relays 9-1617786-9
TE Connectivity's Axicom Relays 9-1617786-9	TE Connectivity's Buchanan Terminal Blocks 9-1617786-9	TE Connectivity's CGS Resistors 9-1617786-9
TE Connectivity's CII 9-1617786-9	TE Connectivity's Elcon Connectors 9-1617786-9	TE Connectivity's Holsworthy Resistors 9-1617786-9
TE Connectivity's Neohm Resistors 9-1617786-9	TE Connectivity's OEG Relays 9-1617786-9	TE Connectivity's Q-Cee's 9-1617786-9
TE Connectivity's Schrack Relays 9-1617786-9	TE Connectivity's Sigma Inductors 9-1617786-9	TE Connectivity's Products Unlimited Transformers 9-1617786-9
TE Connectivity's Kilovac Relays 9-1617786-9		

### Ngā Hua e hāngai ana

<div style="border: 1px solid #ccc; padding: 5px;"> <p><b>9-1617787-4</b> Kaihanga: Agastat Relays / TE Connectivity Whakaahuatanga: FCA-210-0909M=M83536/9-009M I roto i te taonga: 702 pcs</p> <p style="text-align: center; background-color: #ccc; padding: 2px 10px; font-weight: bold;">RFQ</p> </div>	<div style="border: 1px solid #ccc; padding: 5px;"> <p><b>9-1617786-7</b> Kaihanga: Agastat Relays / TE Connectivity Whakaahuatanga: FCB-405-0511L=M83536/5-011L I roto i te taonga: 588 pcs</p> <p style="text-align: center; background-color: #ccc; padding: 2px 10px; font-weight: bold;">RFQ</p> </div>
<div style="border: 1px solid #ccc; padding: 5px;"> <p><b>9-1617787-1</b> Kaihanga: Agastat Relays / TE Connectivity Whakaahuatanga: FCA-210-0907M=M83536/9-007M I roto i te taonga: 608 pcs</p> <p style="text-align: center; background-color: #ccc; padding: 2px 10px; font-weight: bold;">RFQ</p> </div>	<div style="border: 1px solid #ccc; padding: 5px;"> <p><b>9-1617787-5</b> Kaihanga: Agastat Relays / TE Connectivity Whakaahuatanga: FCA-210-0910L=M83536/9-010L I roto i te taonga: 738 pcs</p> <p style="text-align: center; background-color: #ccc; padding: 2px 10px; font-weight: bold;">RFQ</p> </div>
<div style="border: 1px solid #ccc; padding: 5px;"> <p><b>9-1617787-2</b> Kaihanga: Agastat Relays / TE Connectivity Whakaahuatanga: FCA-210-0908L=M83536/9-008L I roto i te taonga: 760 pcs</p> <p style="text-align: center; background-color: #ccc; padding: 2px 10px; font-weight: bold;">RFQ</p> </div>	<div style="border: 1px solid #ccc; padding: 5px;"> <p><b>9-1617786-6</b> Kaihanga: Agastat Relays / TE Connectivity Whakaahuatanga: FCB-405-0510M=M83536/5-010M I roto i te taonga: 633 pcs</p> <p style="text-align: center; background-color: #ccc; padding: 2px 10px; font-weight: bold;">RFQ</p> </div>
<div style="border: 1px solid #ccc; padding: 5px;"> <p><b>9-1617786-3</b> Kaihanga: Agastat Relays / TE Connectivity Whakaahuatanga: FCB-405-0509L=M83536/5-009L I roto i te taonga: 609 pcs</p> <p style="text-align: center; background-color: #ccc; padding: 2px 10px; font-weight: bold;">RFQ</p> </div>	<div style="border: 1px solid #ccc; padding: 5px;"> <p><b>9-1617786-8</b> Kaihanga: Agastat Relays / TE Connectivity Whakaahuatanga: FCB-405-0511M=M83536/5-011M I roto i te taonga: 522 pcs</p> <p style="text-align: center; background-color: #ccc; padding: 2px 10px; font-weight: bold;">RFQ</p> </div>
<div style="border: 1px solid #ccc; padding: 5px;"> <p><b>9-1617786-4</b> Kaihanga: Agastat Relays / TE Connectivity Whakaahuatanga: FCB-405-0509M=M83536/5-009M I roto i te taonga: 549 pcs</p> <p style="text-align: center; background-color: #ccc; padding: 2px 10px; font-weight: bold;">RFQ</p> </div>	<div style="border: 1px solid #ccc; padding: 5px;"> <p><b>9-1617787-3</b> Kaihanga: Agastat Relays / TE Connectivity Whakaahuatanga: FCA-210-0909L=M83536/9-009L I roto i te taonga: 725 pcs</p> <p style="text-align: center; background-color: #ccc; padding: 2px 10px; font-weight: bold;">RFQ</p> </div>
<div style="border: 1px solid #ccc; padding: 5px;"> <p><b>9-1617786-5</b> Kaihanga: Agastat Relays / TE Connectivity Whakaahuatanga: FCB-405-0510L=M83536/5-010L I roto i te taonga: 526 pcs</p> <p style="text-align: center; background-color: #ccc; padding: 2px 10px; font-weight: bold;">RFQ</p> </div>	<div style="border: 1px solid #ccc; padding: 5px;"> <p><b>9-1617787-0</b> Kaihanga: Agastat Relays / TE Connectivity Whakaahuatanga: FCA-210-0907L=M83536/9-007L I roto i te taonga: 755 pcs</p> <p style="text-align: center; background-color: #ccc; padding: 2px 10px; font-weight: bold;">RFQ</p> </div>