



Omron Automation & Safety

A30NZ-3MM-TRA

Tau Wae:

Kaihanga / Waitohu:

Whakaahuatanga hua

Ngā Rauemi:

Waehere Stock

Tuhinga mai i

Te Ara Tuhi

A30NZ-3MM-TRA

Omron Automation & Safety

CONFIG SW BODY SELECTOR ILLUM

[A30NZ-3MM-TRA.pdf](#)

6335 pcs stock

Hong Kong

DHL/Fedex/TNT/UPS/EMS

TONO MO TE WHAKAHUA

Ko te whakaahua he tohu. Tirohia nga korero mo nga taipitopito hua.

Ngā whakaaturanga o A30NZ-3MM-TRA

TAU WAE	A30NZ-3MM-TRA
KAIHANGA	Omron Automation & Safety
WHAKAAHUATANGA	CONFIG SW BODY SELECTOR ILLUM
WHAKAHAERE TOKO WHAKAHAERE / ROHS TŪNGA	
HE RAHINGA KEI TE WĀTEA	6335 pcs
PEPA RARAUNGA	A30NZ-3MM-TRA.pdf
MOMO	Maintained
RAUPAPA	A30NW
E HIAHIA ANA	Contact Block(s), Illumination Source
PIHANGA WHAKAPAE PAEPAE	30.5mm (Round)
ĒTAHI INGOA	A30NZ3MMTRA Z8080
WHAKAAHUATANGA	Illuminated - Red
WHAKAAHUATANGA TAIPITOPITO	Configurable Switch Body Selector Illuminated - Red
MOMO KAIHOKO	Selector
(TĪPAKOHIA TUATAHI, KA WHAKAMAHAIA NGĀ TAEKA) RARAUNGA WHAKAMAHAIA	Omron, A30NW

Ngā tūtohu e hāngai ana

Omron Automation & Safety A30NZ-3MM-TRA	A30NZ-3MM-TRA Kaiwhiwhi	A30NZ-3MM-TRA Kaiwhakarato
A30NZ-3MM-TRA Utu	A30NZ-3MM-TRA Pikitia	A30NZ-3MM-TRA Whakaahua
A30NZ-3MM-TRA PDF Datasheet	A30NZ-3MM-TRA Download Datasheet	Tuhinga A30NZ-3MM-TRA
A30NZ-3MM-TRA Stock	Hokona A30NZ-3MM-TRA	Hokona Omron Automation & Safety A30NZ-3MM-TRA
Omron Automation & Safety A30NZ-3MM-TRA	Omron Automation & Safety Kaiwhakarato	Omron Automation & Safety Kaiwhiwhi
Omron Automation & Safety A30NZ-3MM-TRA	Omron Automation and Safety A30NZ-3MM-TRA	

Ngā Hua e hāngai ana

<p>A30NZ-MGA-NRA Kaihanga: Omron Automation & Safety Whakaahuatanga: CONFIG SW BODY PUSHBUT NON-ILLUM I roto i te taonga: 7478 pcs</p> <p>RFQ</p>	<p>A30NZ-2MM-TGA Kaihanga: Omron Automation & Safety Whakaahuatanga: CONFIG SW BODY SELECTOR ILLUM I roto i te taonga: 6360 pcs</p> <p>RFQ</p>
<p>A30NZ-2MM-NBA Kaihanga: Omron Automation & Safety Whakaahuatanga: CONFIG SW BODY SELECTR NON-ILLUM I roto i te taonga: 6766 pcs</p> <p>RFQ</p>	<p>A30NZ-2MM-TWA Kaihanga: Omron Automation & Safety Whakaahuatanga: CONFIG SW BODY SELECTOR ILLUM I roto i te taonga: 5115 pcs</p> <p>RFQ</p>
<p>A30NZ-3MM-TWA Kaihanga: Omron Automation & Safety Whakaahuatanga: CONFIG SW BODY SELECTOR ILLUM I roto i te taonga: 5673 pcs</p> <p>RFQ</p>	<p>A30NZ-2MM-TRA Kaihanga: Omron Automation & Safety Whakaahuatanga: CONFIG SW BODY SELECTOR ILLUM I roto i te taonga: 4997 pcs</p> <p>RFQ</p>
<p>A30NZ-MGA-NAA Kaihanga: Omron Automation & Safety Whakaahuatanga: CONFIG SW BODY PUSHBUT NON-ILLUM I roto i te taonga: 7224 pcs</p> <p>RFQ</p>	<p>A30NZ-MGA-NGA Kaihanga: Omron Automation & Safety Whakaahuatanga: CONFIG SW BODY PUSHBUT NON-ILLUM I roto i te taonga: 6234 pcs</p> <p>RFQ</p>
<p>A30NZ-MGA-NBA Kaihanga: Omron Automation & Safety Whakaahuatanga: CONFIG SW BODY PUSHBUT NON-ILLUM I roto i te taonga: 7576 pcs</p> <p>RFQ</p>	<p>A30NZ-MGA-NWA Kaihanga: Omron Automation & Safety Whakaahuatanga: CONFIG SW BODY PUSHBUT NON-ILLUM I roto i te taonga: 7612 pcs</p> <p>RFQ</p>
<p>A30NZ-3MM-NBA Kaihanga: Omron Automation & Safety Whakaahuatanga: CONFIG SW BODY SELECTR NON-ILLUM I roto i te taonga: 5725 pcs</p> <p>RFQ</p>	<p>A30NZ-3MM-TGA Kaihanga: Omron Automation & Safety Whakaahuatanga: CONFIG SW BODY SELECTOR ILLUM I roto i te taonga: 6427 pcs</p> <p>RFQ</p>

