



Omron Automation & Safety

A22NZ-MPM-TAA

Tau Wae:

A22NZ-MPM-TAA

Kaihanga / Waitohu:

Omron Automation & Safety

Whakaahuatanga hua

CONFIG SW BODY PUSHBUTTON ILLUM

Ngā Rauemi:

A22NZ-MPM-TAA.pdf

RoHS Tūnga

Whakahaerehia te kore utu / RoHS

Waehere Stock

13000 pcs stock

Tuhinga mai i

Hong Kong

Te Ara Tuhi

DHL/Fedex/TNT/UPS/EMS



TONO MO TE WHAKAHUA

Ko te whakaahua he tohu. Tirohia nga korero mo nga taipitopito hua.

Ngā whakaaturanga o A22NZ-MPM-TAA

TAU WAE	A22NZ-MPM-TAA
KAIHANGA	Omron Automation & Safety
WHAKAAHUATANGA	CONFIG SW BODY PUSHBUTTON ILLUM
WHAKAHAERE TOKO WHAKAHAERE / ROHS TŪNGA	Whakahaerehia te kore utu / RoHS
HE RAHINGA KEI TE WĀTEA	13000 pcs
PEPA RARAUNGA	A22NZ-MPM-TAA.pdf
MOMO	Momentary
RAUPAPA	A22NL
E HIAHIA ANA	Contact Block(s), Illumination Source
PIHANGA WHAKAPAE PAEPAE	22.3mm (Round)
ĒTAHI INGOA	A22NZMPMTAA
TAUMATA WHAKAARO MOE (MSL)	1 (Unlimited)
WHAKAHAERE TOKO WHAKAHAERE / ROHS TŪNGA	Lead free / RoHS Compliant
WHAKAAHUATANGA	Illuminated - Blue
WHAKAAHUATANGA TAIPITOPITO	Configurable Switch Body Pushbutton, Round Illuminated - Blue
MOMO KAIHOKO	Pushbutton, Round
(TĪPAKOHIA TUATAHI, KA WHAKAMAHIA NGĀ TAEKA) RARAUNGA WHAKAMAHIA	Omron, A22NL

Ngā tūtohu e hāngai ana

Omron Automation & Safety A22NZ-MPM-TAA	A22NZ-MPM-TAA Kaiwhiwhi	A22NZ-MPM-TAA Kaiwhakarato
A22NZ-MPM-TAA Utu	A22NZ-MPM-TAA Pikitia	A22NZ-MPM-TAA Whakaahua
A22NZ-MPM-TAA PDF Datasheet	A22NZ-MPM-TAA Download Datasheet	Tuhinga A22NZ-MPM-TAA
A22NZ-MPM-TAA Stock	Hokona A22NZ-MPM-TAA	Hokona Omron Automation & Safety A22NZ-MPM-TAA
Omron Automation & Safety A22NZ-MPM-TAA	Omron Automation & Safety Kaiwhakarato	Omron Automation & Safety Kaiwhiwhi
Omron Automation & Safety A22NZ-MPM-TAA	Omron Automation and Safety A22NZ-MPM-TAA	

Ngā Hua e hāngai ana

<p>A22NZ-MPM-UAA Kaihanga: Omron Automation & Safety Whakaahuatanga: CONFIG SW BODY PUSHBUT NON-ILLUM I roto i te taonga: 16385 pcs</p> <p>RFQ</p>	<p>A22NZ-MPM-TYA Kaihanga: Omron Automation & Safety Whakaahuatanga: CONFIG SW BODY PUSHBUTTON ILLUM I roto i te taonga: 13786 pcs</p> <p>RFQ</p>
<p>A22NZ-MPM-TWA Kaihanga: Omron Automation & Safety Whakaahuatanga: CONFIG SW BODY PUSHBUTTON ILLUM I roto i te taonga: 17259 pcs</p> <p>RFQ</p>	<p>A22NZ-MPM-NGA Kaihanga: Omron Automation & Safety Whakaahuatanga: CONFIG SW BODY PUSHBUT NON-ILLUM I roto i te taonga: 18274 pcs</p> <p>RFQ</p>
<p>A22NZ-MPM-NAA Kaihanga: Omron Automation & Safety Whakaahuatanga: CONFIG SW BODY PUSHBUT NON-ILLUM I roto i te taonga: 16723 pcs</p> <p>RFQ</p>	<p>A22NZ-MPM-NWA Kaihanga: Omron Automation & Safety Whakaahuatanga: CONFIG SW BODY PUSHBUT NON-ILLUM I roto i te taonga: 18665 pcs</p> <p>RFQ</p>
<p>A22NZ-MPM-TGA Kaihanga: Omron Automation & Safety Whakaahuatanga: CONFIG SW BODY PUSHBUTTON ILLUM I roto i te taonga: 16468 pcs</p> <p>RFQ</p>	<p>A22NZ-MPM-TOA Kaihanga: Omron Automation & Safety Whakaahuatanga: CONFIG SW BODY PUSHBUTTON ILLUM I roto i te taonga: 18725 pcs</p> <p>RFQ</p>
<p>A22NZ-MPM-TRA Kaihanga: Omron Automation & Safety Whakaahuatanga: CONFIG SW BODY PUSHBUTTON ILLUM I roto i te taonga: 13304 pcs</p> <p>RFQ</p>	<p>A22NZ-MPM-NRA Kaihanga: Omron Automation & Safety Whakaahuatanga: CONFIG SW BODY PUSHBUT NON-ILLUM I roto i te taonga: 17986 pcs</p> <p>RFQ</p>
<p>A22NZ-MPM-NBA Kaihanga: Omron Automation & Safety Whakaahuatanga: CONFIG SW BODY PUSHBUT NON-ILLUM I roto i te taonga: 20570 pcs</p> <p>RFQ</p>	<p>A22NZ-MPM-NYA Kaihanga: Omron Automation & Safety Whakaahuatanga: CONFIG SW BODY PUSHBUT NON-ILLUM I roto i te taonga: 19956 pcs</p> <p>RFQ</p>

