

BROADCOM
connecting everything

BROADCO
connecting everything

Avago Technologies (Broadcom Limited)

AEDT-9340-B00

Tau Wae: Kaihanga / Waitohu: Whakaahuatanga hua Ngā Rauemi: RoHs Tūnga Waehere Stock Tuhinga mai i Te Ara Tuhi	AEDT-9340-B00 Avago Technologies (Broadcom Limited) ROTARY ENCODER OPTICAL 1000PPR AEDT-9340-B00.pdf Whakahaerehia te kore utu / RoHS 4211 pcs stock Hong Kong DHL/Fedex/TNT/UPS/EMS
---	---

TONO MO TE WHAKAHUA

Ko te whakaahua he tohu. Tirohia nga korero mo nga taipitopito hua.

Ngā whakaaturanga o AEDT-9340-B00

TAU WAE	AEDT-9340-B00
KAIHANGA	Avago Technologies (Broadcom Limited)
WHAKAAHUATANGA	ROTARY ENCODER OPTICAL 1000PPR
WHAKAHAERE TOKO WHAKAHAERE / ROHS TŪNGA	Whakahaerehia te kore utu / RoHS
HE RAHINGA KEI TE WĀTEA	4211 pcs
PEPA RARAUNGA	AEDT-9340-B00.pdf
TUHINGA O MUA	5V
KĀHUA WHAKAMUTUNGA	Terminal Pins
RAUPAPA	AEDT-9340
KO TE ROTATIONAL LIFE (CYCLES MIN)	-
PULSES IA REVOLUTION	1000
MOMO PUTANGA	Quadrature with Index (Incremental)
WHAKATAKOTORANGA	-
MOMO TAE	Chassis Mount
TAUMATA WHAKAARO MOE (MSL)	1 (Unlimited)
WHAKAHAERE TOKO WHAKAHAERE / ROHS TŪNGA	Lead free / RoHS Compliant
MOMO KUPUTUHI	Optical
TUHINGA	No
HANGAIA KI TE WHAKAWHITI	No
MOMO KAIHOKO	Codewheel Not Included

Ngā tūtohu e hāngai ana

Avago Technologies (Broadcom Limited) AEDT-9340-B00	AEDT-9340-B00 Kaihiwhi	AEDT-9340-B00 Kaiwhakarato
AEDT-9340-B00 Utu	AEDT-9340-B00 Pikitia	AEDT-9340-B00 Whakaahua
AEDT-9340-B00 PDF Datasheet	AEDT-9340-B00 Download Datasheet	Tuhinga AEDT-9340-B00
AEDT-9340-B00 Stock	Hokona AEDT-9340-B00	Hokona Avago Technologies (Broadcom Limited) AEDT-9340-B00
Avago Technologies (Broadcom Limited) AEDT-9340-B00	Avago Technologies (Broadcom Limited) Kaiwhakarato	Avago Technologies (Broadcom Limited) Kaihiwhi
Avago Technologies (Broadcom Limited) AEDT-9340-B00	Avago Technologies Limited AEDT-9340-B00	Avago Technologies US Inc. AEDT-9340-B00
Avago Technologies AEDT-9340-B00	Avago Technologies (Broadcom Limited) AEDT-9340-B00	Broadcom Limited AEDT-9340-B00

Ngā Hua e hāngai ana

<div style="display: flex; align-items: center;"> <div> <p>AEDT-9140-I00</p> <p>Kaihanga: Avago Technologies (Broadcom Limited)</p> <p>Whakaahuatanga: ROTARY ENCODER OPTICAL 512PPR</p> <p>I roto i te taonga: 3177 pcs</p> <div style="background-color: #ccc; padding: 5px; text-align: center; width: fit-content; margin-top: 10px;">RFQ</div> </div> </div>	<div style="display: flex; align-items: center;"> <div> <p>AEDT-9340-L00</p> <p>Kaihanga: Avago Technologies (Broadcom Limited)</p> <p>Whakaahuatanga: ROTARY ENCODER OPTICAL 1250PPR</p> <p>I roto i te taonga: 5376 pcs</p> <div style="background-color: #ccc; padding: 5px; text-align: center; width: fit-content; margin-top: 10px;">RFQ</div> </div> </div>
<div style="display: flex; align-items: center;"> <div> <p>AEDT-9140-G00</p> <p>Kaihanga: Avago Technologies (Broadcom Limited)</p> <p>Whakaahuatanga: ROTARY ENCODER OPTICAL 360PPR</p> <p>I roto i te taonga: 4795 pcs</p> <div style="background-color: #ccc; padding: 5px; text-align: center; width: fit-content; margin-top: 10px;">RFQ</div> </div> </div>	<div style="display: flex; align-items: center;"> <div> <p>AEDT-9140-F00</p> <p>Kaihanga: Avago Technologies (Broadcom Limited)</p> <p>Whakaahuatanga: ROTARY ENCODER OPTICAL 256PPR</p> <p>I roto i te taonga: 2753 pcs</p> <div style="background-color: #ccc; padding: 5px; text-align: center; width: fit-content; margin-top: 10px;">RFQ</div> </div> </div>
<div style="display: flex; align-items: center;"> <div> <p>AEDT-9140-E00</p> <p>Kaihanga: Avago Technologies (Broadcom Limited)</p> <p>Whakaahuatanga: ROTARY ENCODER OPTICAL 200PPR</p> <p>I roto i te taonga: 3597 pcs</p> <div style="background-color: #ccc; padding: 5px; text-align: center; width: fit-content; margin-top: 10px;">RFQ</div> </div> </div>	<div style="display: flex; align-items: center;"> <div> <p>AEDT-9340-W00</p> <p>Kaihanga: Avago Technologies (Broadcom Limited)</p> <p>Whakaahuatanga: ROTARY ENCODER OPTICAL 2500PPR</p> <p>I roto i te taonga: 2291 pcs</p> <div style="background-color: #ccc; padding: 5px; text-align: center; width: fit-content; margin-top: 10px;">RFQ</div> </div> </div>
<div style="display: flex; align-items: center;"> <div> <p>AEDT-9340-J00</p> <p>Kaihanga: Avago Technologies (Broadcom Limited)</p> <p>Whakaahuatanga: ROTARY ENCODER OPTICAL 1024PPR</p> <p>I roto i te taonga: 4216 pcs</p> <div style="background-color: #ccc; padding: 5px; text-align: center; width: fit-content; margin-top: 10px;">RFQ</div> </div> </div>	<div style="display: flex; align-items: center;"> <div> <p>AEDT-9340-U00</p> <p>Kaihanga: Avago Technologies (Broadcom Limited)</p> <p>Whakaahuatanga: ROTARY ENCODER OPTICAL 2048PPR</p> <p>I roto i te taonga: 4815 pcs</p> <div style="background-color: #ccc; padding: 5px; text-align: center; width: fit-content; margin-top: 10px;">RFQ</div> </div> </div>
<div style="display: flex; align-items: center;"> <div> <p>AEDT-9140-C00</p> <p>Kaihanga: Avago Technologies (Broadcom Limited)</p> <p>Whakaahuatanga: ROTARY ENCODER OPTICAL 100PPR</p> <p>I roto i te taonga: 4295 pcs</p> <div style="background-color: #ccc; padding: 5px; text-align: center; width: fit-content; margin-top: 10px;">RFQ</div> </div> </div>	<div style="display: flex; align-items: center;"> <div> <p>AEDT-9340-T00</p> <p>Kaihanga: Avago Technologies (Broadcom Limited)</p> <p>Whakaahuatanga: ROTARY ENCODER OPTICAL 2000PPR</p> <p>I roto i te taonga: 2710 pcs</p> <div style="background-color: #ccc; padding: 5px; text-align: center; width: fit-content; margin-top: 10px;">RFQ</div> </div> </div>
<div style="display: flex; align-items: center;"> <div> <p>AEDT-9140-H00</p> <p>Kaihanga: Avago Technologies (Broadcom Limited)</p> <p>Whakaahuatanga: ROTARY ENCODER OPTICAL 400PPR</p> <p>I roto i te taonga: 5733 pcs</p> <div style="background-color: #ccc; padding: 5px; text-align: center; width: fit-content; margin-top: 10px;">RFQ</div> </div> </div>	<div style="display: flex; align-items: center;"> <div> <p>AEDT-9810-A00</p> <p>Kaihanga: Avago Technologies (Broadcom Limited)</p> <p>Whakaahuatanga: ROTARY ENCODER OPTICAL 500PPR</p> <p>I roto i te taonga: 3862 pcs</p> <div style="background-color: #ccc; padding: 5px; text-align: center; width: fit-content; margin-top: 10px;">RFQ</div> </div> </div>