



Omron Automation & Safety

A22NZ-RNA-NWA

Tau Wae:

A22NZ-RNA-NWA

Kaihanga / Waitohu:

Omron Automation & Safety

Whakaahuatanga hua

CONFIG SW BODY PUSHBUT NON-ILLUM

Ngā Rauemi:

A22NZ-RNA-NWA.pdf

RoHS Tūnga

Whakahaerehia te kore utu / RoHS

Waehere Stock

11414 pcs stock

Tuhinga mai i

Hong Kong

Te Ara Tuhi

DHL/Fedex/TNT/UPS/EMS



TONO MO TE WHAKAHUA

Ko te whakaahua he tohu. Tirohia nga korero mo nga taipitopito hua.

Ngā whakaaturanga o A22NZ-RNA-NWA

TAU WAE	A22NZ-RNA-NWA
KAIHANGA	Omron Automation & Safety
WHAKAAHUATANGA	CONFIG SW BODY PUSHBUT NON-ILLUM
WHAKAHAERE TOKO WHAKAHAERE / ROHS TŪNGA	Whakahaerehia te kore utu / RoHS
HE RAHINGA KEI TE WĀTEA	11414 pcs
PEPA RARAUNGA	A22NZ-RNA-NWA.pdf
MOMO	Maintained
RAUPAPA	A22NN
E HIAHIA ANA	Contact Block(s)
PIHANGA WHAKAPAE PAEPAE	22.3mm (Round)
ĒTAHI INGOA	A22NZRNANWA
TAUMATA WHAKAARO MOE (MSL)	1 (Unlimited)
WHAKAHAERE TOKO WHAKAHAERE / ROHS TŪNGA	Lead free / RoHS Compliant
WHAKAAHUATANGA	Non-Illuminated
WHAKAAHUATANGA TAIPITOPITO	Configurable Switch Body Pushbutton, Round Non-Illuminated
MOMO KAIHOKO	Pushbutton, Round
(TĪPAKOHIA TUATAHI, KA WHAKAMAHIA NGĀ TAEKA) RARAUNGA WHAKAMAHIA	Omron, A22NN

Ngā tūtohu e hāngai ana

Omron Automation & Safety A22NZ-RNA-NWA	A22NZ-RNA-NWA Kaiwhiwhi	A22NZ-RNA-NWA Kaiwhakarato
A22NZ-RNA-NWA Utu	A22NZ-RNA-NWA Pikitia	A22NZ-RNA-NWA Whakaahua
A22NZ-RNA-NWA PDF Datasheet	A22NZ-RNA-NWA Download Datasheet	Tuhinga A22NZ-RNA-NWA
A22NZ-RNA-NWA Stock	Hokona A22NZ-RNA-NWA	Hokona Omron Automation & Safety A22NZ-RNA-NWA
Omron Automation & Safety A22NZ-RNA-NWA	Omron Automation & Safety Kaiwhakarato	Omron Automation & Safety Kaiwhiwhi
Omron Automation & Safety A22NZ-RNA-NWA	Omron Automation and Safety A22NZ-RNA-NWA	

Ngā Hua e hāngai ana

<p>A22NZ-RNA-TWA Kaihanga: Omron Automation & Safety Whakaahuatanga: CONFIG SW BODY PUSHBUTTON ILLUM I roto i te taonga: 21314 pcs</p> <p>RFQ</p>	<p>A22NZ-RNA-TAA Kaihanga: Omron Automation & Safety Whakaahuatanga: CONFIG SW BODY PUSHBUTTON ILLUM I roto i te taonga: 23139 pcs</p> <p>RFQ</p>
<p>A22NZ-RMM-UWA Kaihanga: Omron Automation & Safety Whakaahuatanga: CONFIG SW BODY PUSHBUT NON-ILLUM I roto i te taonga: 25337 pcs</p> <p>RFQ</p>	<p>A22NZ-RNA-NAA Kaihanga: Omron Automation & Safety Whakaahuatanga: CONFIG SW BODY PUSHBUT NON-ILLUM I roto i te taonga: 13041 pcs</p> <p>RFQ</p>
<p>A22NZ-RNA-TOA Kaihanga: Omron Automation & Safety Whakaahuatanga: CONFIG SW BODY PUSHBUTTON ILLUM I roto i te taonga: 19488 pcs</p> <p>RFQ</p>	<p>A22NZ-RNA-NGA Kaihanga: Omron Automation & Safety Whakaahuatanga: CONFIG SW BODY PUSHBUT NON-ILLUM I roto i te taonga: 14918 pcs</p> <p>RFQ</p>
<p>A22NZ-RNA-TRA Kaihanga: Omron Automation & Safety Whakaahuatanga: CONFIG SW BODY PUSHBUTTON ILLUM I roto i te taonga: 23708 pcs</p> <p>RFQ</p>	<p>A22NZ-RNA-NBA Kaihanga: Omron Automation & Safety Whakaahuatanga: CONFIG SW BODY PUSHBUT NON-ILLUM I roto i te taonga: 13746 pcs</p> <p>RFQ</p>
<p>A22NZ-RMM-UYA Kaihanga: Omron Automation & Safety Whakaahuatanga: CONFIG SW BODY PUSHBUT NON-ILLUM I roto i te taonga: 25356 pcs</p> <p>RFQ</p>	<p>A22NZ-RNA-NRA Kaihanga: Omron Automation & Safety Whakaahuatanga: CONFIG SW BODY PUSHBUT NON-ILLUM I roto i te taonga: 14936 pcs</p> <p>RFQ</p>
<p>A22NZ-RNA-TGA Kaihanga: Omron Automation & Safety Whakaahuatanga: CONFIG SW BODY PUSHBUTTON ILLUM I roto i te taonga: 19008 pcs</p> <p>RFQ</p>	<p>A22NZ-RNA-NYA Kaihanga: Omron Automation & Safety Whakaahuatanga: CONFIG SW BODY PUSHBUT NON-ILLUM I roto i te taonga: 14098 pcs</p> <p>RFQ</p>

