



Thomas Research Products

LHUSD0-N-BK

Tau Wae:

LHUSD0-N-BK

Kaihanga / Waitohu:

Thomas Research Products

Whakaahuatanga hua

ULTRASONIC WALL SWITCH SENSOR

Ngā Rauemi:

LHUSD0-N-BK.pdf

RoHS Tūnga

Whakahaerehia te kore utu / RoHS

Waehere Stock

4078 pcs stock

Tuhinga mai i

Hong Kong

Te Ara Tuhi

DHL/Fedex/TNT/UPS/EMS

TONO MO TE WHAKAHUA

Ko te whakaahua he tohu. Tirohia nga korero mo nga taipitopito hua.

Ngā whakaaturanga o LHUSD0-N-BK

TAU WAE	LHUSD0-N-BK
KAIHANGA	Thomas Research Products
WHAKAAHUATANGA	ULTRASONIC WALL SWITCH SENSOR
WHAKAHAERE TOKO WHAKAHAERE / ROHS TŪNGA	Whakahaerehia te kore utu / RoHS
HE RAHINGA KEI TE WĀTEA	4078 pcs
PEPA RARAUNGA	LHUSD0-N-BK.pdf
TUHINGA O MUA	120/277VAC
RAUPAPA	LightHAWK2™
MOMO PATO	Ultrasonic
MOMO PUTANGA	Relay
TAE MAHI	0°C ~ 40°C
MOMO TAE	Wall Mount
TAUMATA WHAKAARO MOE (MSL)	1 (Unlimited)
ARATAU TOHU	No
WHAKAHAERE TOKO WHAKAHAERE / ROHS TŪNGA	Lead free / RoHS Compliant
WHAKAAHUATANGA TAIPITOPITO	Proximity/Occupancy Sensor Ultrasonic 400 Square Feet Relay Wall Mount Black
TE KOHINGA	400 Square Feet
TAE	Black
CALIFORNIA PROP 65	Warning Information WARNING: This product can expose you to chemicals including Lead and lead compounds which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65warnings.ca.gov.

Ngā tūtohu e hāngai ana

Thomas Research Products LHUSD0-N-BK	LHUSD0-N-BK Kaiwhiwhi	LHUSD0-N-BK Kaiwhakarato
LHUSD0-N-BK Utu	LHUSD0-N-BK Pikitia	LHUSD0-N-BK Whakaahua
LHUSD0-N-BK PDF Datasheet	LHUSD0-N-BK Download Datasheet	Tuhinga LHUSD0-N-BK
LHUSD0-N-BK Stock	Hokona LHUSD0-N-BK	Hokona Thomas Research Products LHUSD0-N-BK
Thomas Research Products LHUSD0-N-BK	Thomas Research Products Kaiwhakarato	Thomas Research Products Kaiwhiwhi
Thomas Research Products LHUSD0-N-BK		

Ngā Hua e hāngai ana

<p>LHUSD0-N-GY Kaihanga: Thomas Research Products Whakaahuatanga: ULTRASONIC WALL SWITCH SENSOR I roto i te taonga: 6874 pcs</p> <p>RFQ</p>	<p>LHUSD2-G-BK Kaihanga: Thomas Research Products Whakaahuatanga: ULTRASONIC WALL SWITCH SENSOR I roto i te taonga: 5707 pcs</p> <p>RFQ</p>
<p>LHUSD0-G-LA Kaihanga: Thomas Research Products Whakaahuatanga: ULTRASONIC WALL SWITCH SENSOR I roto i te taonga: 4094 pcs</p> <p>RFQ</p>	<p>LHUSD2-G-GY Kaihanga: Thomas Research Products Whakaahuatanga: ULTRASONIC WALL SWITCH SENSOR I roto i te taonga: 6175 pcs</p> <p>RFQ</p>
<p>LHUSD0-N-IV Kaihanga: Thomas Research Products Whakaahuatanga: ULTRASONIC WALL SWITCH SENSOR I roto i te taonga: 5401 pcs</p> <p>RFQ</p>	<p>LHUSD0-N-LA Kaihanga: Thomas Research Products Whakaahuatanga: ULTRASONIC WALL SWITCH SENSOR I roto i te taonga: 3561 pcs</p> <p>RFQ</p>
<p>LHUSD0-G-IV Kaihanga: Thomas Research Products Whakaahuatanga: ULTRASONIC WALL SWITCH SENSOR I roto i te taonga: 4539 pcs</p> <p>RFQ</p>	<p>LHUSD2-G-IV Kaihanga: Thomas Research Products Whakaahuatanga: ULTRASONIC WALL SWITCH SENSOR I roto i te taonga: 2945 pcs</p> <p>RFQ</p>
<p>LHUSD0-G-BK Kaihanga: Thomas Research Products Whakaahuatanga: ULTRASONIC WALL SWITCH SENSOR I roto i te taonga: 6825 pcs</p> <p>RFQ</p>	<p>LHUSD0-G-WH Kaihanga: Thomas Research Products Whakaahuatanga: ULTRASONIC WALL SWITCH SENSOR I roto i te taonga: 5444 pcs</p> <p>RFQ</p>
<p>LHUSD0-G-GY Kaihanga: Thomas Research Products Whakaahuatanga: ULTRASONIC WALL SWITCH SENSOR I roto i te taonga: 4107 pcs</p> <p>RFQ</p>	<p>LHUSD0-N-WH Kaihanga: Thomas Research Products Whakaahuatanga: ULTRASONIC WALL SWITCH SENSOR I roto i te taonga: 3640 pcs</p> <p>RFQ</p>

