




Agastat Relays / TE Connectivity

PRD-60024



Tau Wae:
 Kaihanga / Waitohu:
 Whakaahuatanga hua
 Ngā Rauemi:
 RoHS Tūnga
 Waehere Stock
 Tuhinga mai i
 Te Ara Tuhi

PRD-60024
 Agastat Relays / TE Connectivity
 POWER RELAY ASSEMBLY

 Kei roto i te awhina / RoHS Compliant
 622 pcs stock
 Hong Kong
 DHL/Fedex/TNT/UPS/EMS

TONO MO TE WHAKAHUA

Ko te whakaahua he tohu. Tirohia nga korero mo nga taipitopito hua.













Ngā whakaaturanga o PRD-60024

TAU WAE	PRD-60024
KAIHANGA	Agastat Relays / TE Connectivity
WHAKAAHUATANGA	POWER RELAY ASSEMBLY
WHAKAHAERE TOKO WHAKAHAERE / ROHS TŪNGA	Kei roto i te awhina / RoHS Compliant
HE RAHINGA KEI TE WĀTEA	622 pcs
PEPA RARAUNGA	
RAUPAPA	*
ĒTAHI INGOA	2-1393128-3 PRD60024
TAUMATA WHAKAARO MOE (MSL)	1 (Unlimited)
WHAKAHAERE TOKO WHAKAHAERE / ROHS TŪNGA	Contains lead / RoHS Compliant
WHAKAAHUATANGA TAIPITOPITO	Relay Coil

Ngā tūtohu e hāngai ana

Agastat Relays / TE Connectivity PRD-60024	PRD-60024 Kaihiwhi	PRD-60024 Kaiwhakarato
PRD-60024 Utu	PRD-60024 Pikitia	PRD-60024 Whakaahua
PRD-60024 PDF Datasheet	PRD-60024 Download Datasheet	Tuhinga PRD-60024
PRD-60024 Stock	Hokona PRD-60024	Hokona Agastat Relays / TE Connectivity PRD-60024
Agastat Relays / TE Connectivity PRD-60024	Agastat Relays / TE Connectivity Kaiwhakarato	Agastat Relays / TE Connectivity Kaihiwhi
Agastat Relays / TE Connectivity PRD-60024	Axicom Relays / TE Connectivity PRD-60024	Buchanan Terminal Blocks / TE Connectivity PRD-60024
CGS Resistors / TE Connectivity PRD-60024	CII / TE Connectivity PRD-60024	Elcon Connectors / TE Connectivity PRD-60024
Holsworthy Resistors / TE Connectivity PRD-60024	Kilovac Relays / TE Connectivity PRD-60024	Neohm Resistors / TE Connectivity PRD-60024
OEG Relays / TE Connectivity PRD-60024	Products Unlimited Transformers & Relays / TE Conn PRD-60024	Q-Cee's / TE Connectivity PRD-60024
Schrack Relays / TE Connectivity PRD-60024	Sigma Inductors / TE Connectivity PRD-60024	TE Connectivity's Agastat Relays PRD-60024
TE Connectivity's Axicom Relays PRD-60024	TE Connectivity's Buchanan Terminal Blocks PRD-60024	TE Connectivity's CGS Resistors PRD-60024
TE Connectivity's CII PRD-60024	TE Connectivity's Elcon Connectors PRD-60024	TE Connectivity's Holsworthy Resistors PRD-60024
TE Connectivity's Neohm Resistors PRD-60024	TE Connectivity's OEG Relays PRD-60024	TE Connectivity's Q-Cee's PRD-60024
TE Connectivity's Schrack Relays PRD-60024	TE Connectivity's Sigma Inductors PRD-60024	TE Connectivity's Products Unlimited Transformers PRD-60024
TE Connectivity's Kilovac Relays PRD-60024		

Ngā Hua e hāngai ana

<div style="border: 1px solid #ccc; padding: 5px;"> <div style="display: flex; align-items: center;">  <div style="margin-left: 10px;"> <p style="margin: 0;">PRD-60029</p> <p style="margin: 0; font-size: small;">Kaihanga: Agastat Relays / TE Connectivity Whakaahuatanga: POWER RELAY ASSEMBLY I roto i te taonga: 952 pcs</p> <p style="text-align: center; background-color: #ccc; padding: 2px 10px; font-weight: bold; margin: 5px 0;">RFQ</p> </div> </div> </div>	<div style="border: 1px solid #ccc; padding: 5px;"> <div style="display: flex; align-items: center;">  <div style="margin-left: 10px;"> <p style="margin: 0;">PRD-5DY3-110</p> <p style="margin: 0; font-size: small;">Kaihanga: Agastat Relays / TE Connectivity Whakaahuatanga: RELAY GEN PURPOSE SPDT 25A 110V I roto i te taonga: 1817 pcs</p> <p style="text-align: center; background-color: #ccc; padding: 2px 10px; font-weight: bold; margin: 5px 0;">RFQ</p> </div> </div> </div>
<div style="border: 1px solid #ccc; padding: 5px;"> <div style="display: flex; align-items: center;">  <div style="margin-left: 10px;"> <p style="margin: 0;">PRD-5DY0-75</p> <p style="margin: 0; font-size: small;">Kaihanga: Agastat Relays / TE Connectivity Whakaahuatanga: RELAY GEN PURPOSE SPDT 25A 75V I roto i te taonga: 2706 pcs</p> <p style="text-align: center; background-color: #ccc; padding: 2px 10px; font-weight: bold; margin: 5px 0;">RFQ</p> </div> </div> </div>	<div style="border: 1px solid #ccc; padding: 5px;"> <div style="display: flex; align-items: center;">  <div style="margin-left: 10px;"> <p style="margin: 0;">PRD-60033</p> <p style="margin: 0; font-size: small;">Kaihanga: Agastat Relays / TE Connectivity Whakaahuatanga: POWER RELAY ASSEMBLY I roto i te taonga: 614 pcs</p> <p style="text-align: center; background-color: #ccc; padding: 2px 10px; font-weight: bold; margin: 5px 0;">RFQ</p> </div> </div> </div>
<div style="border: 1px solid #ccc; padding: 5px;"> <div style="display: flex; align-items: center;">  <div style="margin-left: 10px;"> <p style="margin: 0;">PRD-60028</p> <p style="margin: 0; font-size: small;">Kaihanga: Agastat Relays / TE Connectivity Whakaahuatanga: POWER RELAY ASSEMBLY I roto i te taonga: 1526 pcs</p> <p style="text-align: center; background-color: #ccc; padding: 2px 10px; font-weight: bold; margin: 5px 0;">RFQ</p> </div> </div> </div>	<div style="border: 1px solid #ccc; padding: 5px;"> <div style="display: flex; align-items: center;">  <div style="margin-left: 10px;"> <p style="margin: 0;">PRD-5DY0-12</p> <p style="margin: 0; font-size: small;">Kaihanga: Agastat Relays / TE Connectivity Whakaahuatanga: RELAY GEN PURPOSE SPDT 25A 12V I roto i te taonga: 2617 pcs</p> <p style="text-align: center; background-color: #ccc; padding: 2px 10px; font-weight: bold; margin: 5px 0;">RFQ</p> </div> </div> </div>
<div style="border: 1px solid #ccc; padding: 5px;"> <div style="display: flex; align-items: center;">  <div style="margin-left: 10px;"> <p style="margin: 0;">PRD-60034</p> <p style="margin: 0; font-size: small;">Kaihanga: Agastat Relays / TE Connectivity Whakaahuatanga: POWER RELAY ASSEMBLY I roto i te taonga: 1000 pcs</p> <p style="text-align: center; background-color: #ccc; padding: 2px 10px; font-weight: bold; margin: 5px 0;">RFQ</p> </div> </div> </div>	<div style="border: 1px solid #ccc; padding: 5px;"> <div style="display: flex; align-items: center;">  <div style="margin-left: 10px;"> <p style="margin: 0;">PRD-60038</p> <p style="margin: 0; font-size: small;">Kaihanga: Agastat Relays / TE Connectivity Whakaahuatanga: POWER RELAY ASSEMBLY I roto i te taonga: 883 pcs</p> <p style="text-align: center; background-color: #ccc; padding: 2px 10px; font-weight: bold; margin: 5px 0;">RFQ</p> </div> </div> </div>
<div style="border: 1px solid #ccc; padding: 5px;"> <div style="display: flex; align-items: center;">  <div style="margin-left: 10px;"> <p style="margin: 0;">PRD-60023-2</p> <p style="margin: 0; font-size: small;">Kaihanga: Agastat Relays / TE Connectivity Whakaahuatanga: POWER RELAY ASSEMBLY I roto i te taonga: 478 pcs</p> <p style="text-align: center; background-color: #ccc; padding: 2px 10px; font-weight: bold; margin: 5px 0;">RFQ</p> </div> </div> </div>	<div style="border: 1px solid #ccc; padding: 5px;"> <div style="display: flex; align-items: center;">  <div style="margin-left: 10px;"> <p style="margin: 0;">PRD-60036</p> <p style="margin: 0; font-size: small;">Kaihanga: Agastat Relays / TE Connectivity Whakaahuatanga: POWER RELAY ASSEMBLY I roto i te taonga: 1132 pcs</p> <p style="text-align: center; background-color: #ccc; padding: 2px 10px; font-weight: bold; margin: 5px 0;">RFQ</p> </div> </div> </div>
<div style="border: 1px solid #ccc; padding: 5px;"> <div style="display: flex; align-items: center;">  <div style="margin-left: 10px;"> <p style="margin: 0;">PRD-5DY0-24</p> <p style="margin: 0; font-size: small;">Kaihanga: Agastat Relays / TE Connectivity Whakaahuatanga: RELAY GEN PURPOSE SPDT 25A 24V I roto i te taonga: 2828 pcs</p> <p style="text-align: center; background-color: #ccc; padding: 2px 10px; font-weight: bold; margin: 5px 0;">RFQ</p> </div> </div> </div>	<div style="border: 1px solid #ccc; padding: 5px;"> <div style="display: flex; align-items: center;">  <div style="margin-left: 10px;"> <p style="margin: 0;">PRD-5DY0-48</p> <p style="margin: 0; font-size: small;">Kaihanga: Agastat Relays / TE Connectivity Whakaahuatanga: POWER RELAY ASSEMBLY I roto i te taonga: 2107 pcs</p> <p style="text-align: center; background-color: #ccc; padding: 2px 10px; font-weight: bold; margin: 5px 0;">RFQ</p> </div> </div> </div>