



Omron Automation & Safety

A22NZ-MGM-TWA

Tau Wae:

A22NZ-MGM-TWA

Kaihanga / Waitohu:

Omron Automation & Safety

Whakaahuatanga hua

CONFIG SW BODY PUSHBUTTON ILLUM

Ngā Rauemi:

A22NZ-MGM-TWA.pdf

RoHS Tūnga

Whakahaerehia te kore utu / RoHS

Waehere Stock

13071 pcs stock

Tuhinga mai i

Hong Kong

Te Ara Tuhi

DHL/Fedex/TNT/UPS/EMS



TONO MO TE WHAKAHUA

Ko te whakaahua he tohu. Tirohia nga korero mo nga taipitopito hua.

Ngā whakaaturanga o A22NZ-MGM-TWA

TAU WAE	A22NZ-MGM-TWA
KAIHANGA	Omron Automation & Safety
WHAKAAHUATANGA	CONFIG SW BODY PUSHBUTTON ILLUM
WHAKAHAERE TOKO WHAKAHAERE / ROHS TŪNGA	Whakahaerehia te kore utu / RoHS
HE RAHINGA KEI TE WĀTEA	13071 pcs
PEPA RARAUNGA	A22NZ-MGM-TWA.pdf
MOMO	Momentary
RAUPAPA	A22NL
E HIAHIA ANA	Contact Block(s), Illumination Source
PIHANGA WHAKAPAE PAEPAE	22.3mm (Round)
ĒTAHI INGOA	A22NZMGMTWA
TAUMATA WHAKAARO MOE (MSL)	1 (Unlimited)
WHAKAHAERE TOKO WHAKAHAERE / ROHS TŪNGA	Lead free / RoHS Compliant
WHAKAAHUATANGA	Illuminated - White
WHAKAAHUATANGA TAIPITOPITO	Configurable Switch Body Pushbutton, Round Illuminated - White
MOMO KAIHOKO	Pushbutton, Round
(TĪPAKOHIA TUATAHI, KA WHAKAMAHIA NGĀ TAEKA) RARAUNGA WHAKAMAHIA	Omron, A22NL

Ngā tūtohu e hāngai ana

Omron Automation & Safety A22NZ-MGM-TWA	A22NZ-MGM-TWA Kaiwhiwhi	A22NZ-MGM-TWA Kaiwhakarato
A22NZ-MGM-TWA Utu	A22NZ-MGM-TWA Pikitia	A22NZ-MGM-TWA Whakaahua
A22NZ-MGM-TWA PDF Datasheet	A22NZ-MGM-TWA Download Datasheet	Tuhinga A22NZ-MGM-TWA
A22NZ-MGM-TWA Stock	Hokona A22NZ-MGM-TWA	Hokona Omron Automation & Safety A22NZ-MGM-TWA
Omron Automation & Safety A22NZ-MGM-TWA	Omron Automation & Safety Kaiwhakarato	Omron Automation & Safety Kaiwhiwhi
Omron Automation & Safety A22NZ-MGM-TWA	Omron Automation and Safety A22NZ-MGM-TWA	

Ngā Hua e hāngai ana

<p>A22NZ-MGM-TRA Kaihanga: Omron Automation & Safety Whakaahuatanga: CONFIG SW BODY PUSHBUTTON ILLUM I roto i te taonga: 12597 pcs</p> <p>RFQ</p>	<p>A22NZ-MGM-UAA Kaihanga: Omron Automation & Safety Whakaahuatanga: CONFIG SW BODY PUSHBUT NON-ILLUM I roto i te taonga: 14004 pcs</p> <p>RFQ</p>
<p>A22NZ-MGM-UOA Kaihanga: Omron Automation & Safety Whakaahuatanga: CONFIG SW BODY PUSHBUT NON-ILLUM I roto i te taonga: 13437 pcs</p> <p>RFQ</p>	<p>A22NZ-MGM-TAA Kaihanga: Omron Automation & Safety Whakaahuatanga: CONFIG SW BODY PUSHBUTTON ILLUM I roto i te taonga: 14617 pcs</p> <p>RFQ</p>
<p>A22NZ-MGM-TYA Kaihanga: Omron Automation & Safety Whakaahuatanga: CONFIG SW BODY PUSHBUTTON ILLUM I roto i te taonga: 12626 pcs</p> <p>RFQ</p>	<p>A22NZ-MGM-TOA Kaihanga: Omron Automation & Safety Whakaahuatanga: CONFIG SW BODY PUSHBUTTON ILLUM I roto i te taonga: 11578 pcs</p> <p>RFQ</p>
<p>A22NZ-MGM-NYA Kaihanga: Omron Automation & Safety Whakaahuatanga: CONFIG SW BODY PUSHBUT NON-ILLUM I roto i te taonga: 16135 pcs</p> <p>RFQ</p>	<p>A22NZ-MGM-URA Kaihanga: Omron Automation & Safety Whakaahuatanga: CONFIG SW BODY PUSHBUT NON-ILLUM I roto i te taonga: 15797 pcs</p> <p>RFQ</p>
<p>A22NZ-MGM-TGA Kaihanga: Omron Automation & Safety Whakaahuatanga: CONFIG SW BODY PUSHBUTTON ILLUM I roto i te taonga: 12775 pcs</p> <p>RFQ</p>	<p>A22NZ-MGM-NWA Kaihanga: Omron Automation & Safety Whakaahuatanga: CONFIG SW BODY PUSHBUT NON-ILLUM I roto i te taonga: 16835 pcs</p> <p>RFQ</p>
<p>A22NZ-MGM-UGA Kaihanga: Omron Automation & Safety Whakaahuatanga: CONFIG SW BODY PUSHBUT NON-ILLUM I roto i te taonga: 15447 pcs</p> <p>RFQ</p>	<p>A22NZ-MGM-UWA Kaihanga: Omron Automation & Safety Whakaahuatanga: CONFIG SW BODY PUSHBUT NON-ILLUM I roto i te taonga: 14175 pcs</p> <p>RFQ</p>

