



Azoteq

## IQS127D-00008-TSR

Tau Wae:	IQS127D-00008-TSR
Kaihanga / Waitohu:	Azoteq
Whakaahuatanga hua	1 CH. CAPACITIVE TOUCH SENSOR WI
Ngā Rauemi:	<a href="#">IQS127D-00008-TSR.pdf</a>
RoHS Tūnga	Whakahaerehia te kore utu / RoHS
Waehere Stock	122401 pcs stock
Tuhinga mai i	Hong Kong
Te Ara Tuhi	DHL/Fedex/TNT/UPS/EMS

**TONO MO TE WHAKAHUA**

Ko te whakaahua he tohu. Tirohia nga korero mo nga taipitopito hua.

### Ngā whakaaturanga o IQS127D-00008-TSR

TAU WAE	IQS127D-00008-TSR
KAIHANGA	Azoteq
WHAKAAHUATANGA	1 CH. CAPACITIVE TOUCH SENSOR WI
WHAKAHAERE TOKO WHAKAHAERE / ROHS TŪNGA	Whakahaerehia te kore utu / RoHS
HE RAHINGA KEI TE WĀTEA	122401 pcs
PEPA RARAUNGA	<a href="#">IQS127D-00008-TSR.pdf</a>
TUHINGA O MUA	2.95 V ~ 5.5 V
MOMO	Button
PŪRERE PŪRERE WHAKARATO	TSOT-23-6
RAUPAPA	IQ Switch®, ProxSense®
TE WHAKATAU	-
TE RAPU WHAKATAKI	Yes
PACKAGING	Cut Tape (CT)
PAA / CASE	SOT-23-6 Thin, TSOT-23-6
ĒTAHI INGOA	1790-1027-1
TAE MAHI	-40°C ~ 85°C
TAU O NGA UTU	1
TAUMATA WHAKAARO MOE (MSL)	1 (Unlimited)
WHAKAHAERE TOKO WHAKAHAERE / ROHS TŪNGA	Lead free / RoHS Compliant
ARATAU ATEKENEKE RARA	Up to 1
ATANGA	-
WHAKAAHUATANGA TAIPITOPITO	Capacitive Touch Button TSOT-23-6
I TEIE NEI - TE TUKU	29µA

### Ngā tūtohu e hāngai ana

<a href="#">Azoteq IQS127D-00008-TSR</a>	<a href="#">IQS127D-00008-TSR Kaiwhiwhi</a>	<a href="#">IQS127D-00008-TSR Kaiwhakarato</a>
<a href="#">IQS127D-00008-TSR Utu</a>	<a href="#">IQS127D-00008-TSR Pikitia</a>	<a href="#">IQS127D-00008-TSR Whakaahua</a>
<a href="#">IQS127D-00008-TSR PDF Datasheet</a>	<a href="#">IQS127D-00008-TSR Download Datasheet</a>	<a href="#">Tuhinga IQS127D-00008-TSR</a>
<a href="#">IQS127D-00008-TSR Stock</a>	<a href="#">Hokona IQS127D-00008-TSR</a>	<a href="#">Hokona Azoteq IQS127D-00008-TSR</a>
<a href="#">Azoteq IQS127D-00008-TSR</a>	<a href="#">Azoteq Kaiwhakarato</a>	<a href="#">Azoteq Kaiwhiwhi</a>
<a href="#">Azoteq IQS127D-00008-TSR</a>		

### Ngā Hua e hāngai ana

<p><b>IQS213A-00000000-MSR</b> Kaihanga: Azoteq Whakaahuatanga: 3 CH. CAPACITIVE TOUCH SENSOR WI I roto i te taonga: 312351 pcs</p> <p><b>RFQ</b></p>	<p><b>IQS127D-00200-TSR</b> Kaihanga: Azoteq Whakaahuatanga: 1 CH. CAPACITIVE TOUCH SENSOR WI I roto i te taonga: 305612 pcs</p> <p><b>RFQ</b></p>
<p><b>IQS127D-00000-TSR</b> Kaihanga: Azoteq Whakaahuatanga: 1 CH. CAPACITIVE TOUCH SENSOR WI I roto i te taonga: 321982 pcs</p> <p><b>RFQ</b></p>	<p><b>IQS211AEV02-S</b> Kaihanga: Azoteq Whakaahuatanga: IQS211A EVALUATION KIT 2 I roto i te taonga: 12263 pcs</p> <p><b>RFQ</b></p>
<p><b>IQS128-00100-TSR</b> Kaihanga: Azoteq Whakaahuatanga: 1 CH. CAPACITIVE TOUCH SENSOR DY I roto i te taonga: 307498 pcs</p> <p><b>RFQ</b></p>	<p><b>IQS211A-00000000-TSR</b> Kaihanga: Azoteq Whakaahuatanga: 1 CH. CAPACITIVE PROXIMITY/TOUCH I roto i te taonga: 340413 pcs</p> <p><b>RFQ</b></p>
<p><b>IQS128EV01-S</b> Kaihanga: Azoteq Whakaahuatanga: IQS128 EVALUATION KIT 1 I roto i te taonga: 33492 pcs</p> <p><b>RFQ</b></p>	<p><b>IQS128-00000-TSR</b> Kaihanga: Azoteq Whakaahuatanga: 1 CH. CAPACITIVE TOUCH SENSOR DY I roto i te taonga: 127011 pcs</p> <p><b>RFQ</b></p>
<p><b>IQS127DEV01-S</b> Kaihanga: Azoteq Whakaahuatanga: IQS127D EVALUATION KIT 1 I roto i te taonga: 31004 pcs</p> <p><b>RFQ</b></p>	<p><b>IQS127D-00002-TSR</b> Kaihanga: Azoteq Whakaahuatanga: 1 CH. CAPACITIVE TOUCH SENSOR WI I roto i te taonga: 345408 pcs</p> <p><b>RFQ</b></p>
<p><b>IQS127EV02-S</b> Kaihanga: Azoteq Whakaahuatanga: IQS127D EVALUATION KIT 2 I roto i te taonga: 11364 pcs</p> <p><b>RFQ</b></p>	<p><b>IQS133-00000-MSR</b> Kaihanga: Azoteq Whakaahuatanga: 3 CH. CAPACITIVE TOUCH SENSOR WI I roto i te taonga: 187234 pcs</p> <p><b>RFQ</b></p>