



Optek Technology / TT Electronics

## OP644SL

Tau Wae:

OP644SL

Kaihanga / Waitohu:

Optek Technology / TT Electronics

Whakaahuatanga hua

PHOTOTRANSIST NPN 890NM PILL PAK

Ngā Rauemi:

OP644SL.pdf

RoHS Tūnga

Whakahaerehia te kore utu / RoHS

Waehere Stock

44483 pcs stock

Tuhinga mai i

Hong Kong

Te Ara Tuhi

DHL/Fedex/TNT/UPS/EMS

### TONO MO TE WHAKAHUA

Ko te whakaahua he tohu. Tirohia nga korero mo nga taipitopito hua.

### Ngā whakaaturanga o OP644SL

TAU WAE	OP644SL
KAIHANGA	Optek Technology / TT Electronics
WHAKAAHUATANGA	PHOTOTRANSIST NPN 890NM PILL PAK
WHAKAHAERE TOKO WHAKAHAERE / ROHS TŪNGA	Whakahaerehia te kore utu / RoHS
HE RAHINGA KEI TE WĀTEA	44483 pcs
PEPA RARAUNGA	OP644SL.pdf
WAIMOTU	890nm
NGAOHIHI - TE WHAKATERE EMITTER BREAK (MAX)	25V
TIROHIA TE ANGLE	-
RAUPAPA	*
MANA - MAX	50mW
PACKAGING	Bulk
PAA / CASE	Pill
ĒTAHI INGOA	365-1078
WHAKATAKOTORANGA	Top View
TAE MAHI	-65°C ~ 125°C (TA)
MOMO TAE	Surface Mount
TAUMATA WHAKAARO MOE (MSL)	1 (Unlimited)
WHAKAHAERE TOKO WHAKAHAERE / ROHS TŪNGA	Lead free / RoHS Compliant
WHAKAAHUATANGA TAIPITOPITO	Phototransistor 890nm Top View Pill
I TEIE NEI - DARK (ID) (MAX)	100nA
I TEIE NEI - KOHIKOHI (IC) (MAX)	50mA

### Ngā tūtohu e hāngai ana

Optek Technology / TT Electronics OP644SL	OP644SL Kaiwhiwhi	OP644SL Kaiwhakarato
OP644SL Utu	OP644SL Pikitia	OP644SL Whakaahua
OP644SL PDF Datasheet	OP644SL Download Datasheet	Tuhinga OP644SL
OP644SL Stock	Hokona OP644SL	Hokona Optek Technology / TT Electronics OP644SL
Optek Technology / TT Electronics OP644SL	Optek Technology / TT Electronics Kaiwhakarato	Optek Technology / TT Electronics Kaiwhiwhi
Optek Technology / TT Electronics OP644SL	OPTEK Technologies OP644SL	Optek Technology OP644SL
TT Electronics/Optek Technology OP644SL		

### Ngā Hua e hāngai ana

<p><b>OP603TXV</b> Kaihanga: Optek Technology / TT Electronics Whakaahuatanga: PHOTOTRNS SILCN NPN HERMETC PILL I roto i te taonga: 2518 pcs</p> <p><b>RFQ</b></p>	<p><b>OP604TXV</b> Kaihanga: Optek Technology / TT Electronics Whakaahuatanga: PHOTOTRNS SILCN NPN HERMETC PILL I roto i te taonga: 3481 pcs</p> <p><b>RFQ</b></p>
<p><b>OP600C</b> Kaihanga: Optek Technology / TT Electronics Whakaahuatanga: PHOTOTRNS SILCN NPN HERMETC PILL I roto i te taonga: 41704 pcs</p> <p><b>RFQ</b></p>	<p><b>OP642SL</b> Kaihanga: Optek Technology / TT Electronics Whakaahuatanga: PHOTOTRNS SILCN NPN HERMETC PILL I roto i te taonga: 4012 pcs</p> <p><b>RFQ</b></p>
<p><b>OP643SL</b> Kaihanga: Optek Technology / TT Electronics Whakaahuatanga: PHOTOTRNS SILCN NPN HERMET PILL I roto i te taonga: 52156 pcs</p> <p><b>RFQ</b></p>	<p><b>OP600B</b> Kaihanga: Optek Technology / TT Electronics Whakaahuatanga: PHOTOTRNS SILCN NPN HERMETC PILL I roto i te taonga: 37143 pcs</p> <p><b>RFQ</b></p>
<p><b>OP602TX</b> Kaihanga: Optek Technology / TT Electronics Whakaahuatanga: PHOTOTRNS SILCN NPN HERMETC PILL I roto i te taonga: 3400 pcs</p> <p><b>RFQ</b></p>	<p><b>OP603TX</b> Kaihanga: Optek Technology / TT Electronics Whakaahuatanga: PHOTOTRNS SILCN NPN HERMETC PILL I roto i te taonga: 2222 pcs</p> <p><b>RFQ</b></p>
<p><b>OP604S</b> Kaihanga: Optek Technology / TT Electronics Whakaahuatanga: PHOTOTRNS SILCN NPN HERMETC PILL I roto i te taonga: 250 pcs</p> <p><b>RFQ</b></p>	<p><b>OP602TXV</b> Kaihanga: Optek Technology / TT Electronics Whakaahuatanga: PHOTOTRNS SILCN NPN HERMETC PILL I roto i te taonga: 6718 pcs</p> <p><b>RFQ</b></p>
<p><b>OP604TX</b> Kaihanga: Optek Technology / TT Electronics Whakaahuatanga: PHOTOTRNS SILCN NPN HERMETC PILL I roto i te taonga: 5559 pcs</p> <p><b>RFQ</b></p>	<p><b>OP641SL</b> Kaihanga: Optek Technology / TT Electronics Whakaahuatanga: PHOTOTRNS SILCN NPN HERMETC PILL I roto i te taonga: 4458 pcs</p> <p><b>RFQ</b></p>

