



Omron Automation & Safety

A22NZ-BMA-TGA

Tau Wae:

A22NZ-BMA-TGA

Kaihanga / Waitohu:

Omron Automation & Safety

Whakaahuatanga hua

CONFIG SW BODY PUSHBUTTON ILLUM

Ngā Rauemi:

A22NZ-BMA-TGA.pdf

RoHS Tūnga

Whakahaerehia te kore utu / RoHS

Waehere Stock

18657 pcs stock

Tuhinga mai i

Hong Kong

Te Ara Tuhi

DHL/Fedex/TNT/UPS/EMS



TONO MO TE WHAKAHUA

Ko te whakaahua he tohu. Tirohia nga korero mo nga taipitopito hua.

Ngā whakaaturanga o A22NZ-BMA-TGA

TAU WAE	A22NZ-BMA-TGA
KAIHANGA	Omron Automation & Safety
WHAKAAHUATANGA	CONFIG SW BODY PUSHBUTTON ILLUM
WHAKAHAERE TOKO WHAKAHAERE / ROHS TŪNGA	Whakahaerehia te kore utu / RoHS
HE RAHINGA KEI TE WĀTEA	18657 pcs
PEPA RARAUNGA	A22NZ-BMA-TGA.pdf
MOMO	Maintained
RAUPAPA	A22NL
E HIAHIA ANA	Contact Block(s), Illumination Source
PIHANGA WHAKAPAE PAEPAE	22.3mm (Round)
ĒTAHI INGOA	A22NZBMTGA
TAUMATA WHAKAARO MOE (MSL)	1 (Unlimited)
WHAKAHAERE TOKO WHAKAHAERE / ROHS TŪNGA	Lead free / RoHS Compliant
WHAKAAHUATANGA	Illuminated - Green
WHAKAAHUATANGA TAIPITOPITO	Configurable Switch Body Pushbutton, Round Illuminated - Green
MOMO KAIHOKO	Pushbutton, Round
(TĪPAKOHIA TUATAHI, KA WHAKAMAHIA NGĀ TAEKA) RARAUNGA WHAKAMAHIA	Omron, A22NL

Ngā tūtohu e hāngai ana

Omron Automation & Safety A22NZ-BMA-TGA	A22NZ-BMA-TGA Kaiwhiwhi	A22NZ-BMA-TGA Kaiwhakarato
A22NZ-BMA-TGA Utu	A22NZ-BMA-TGA Pikitia	A22NZ-BMA-TGA Whakaahua
A22NZ-BMA-TGA PDF Datasheet	A22NZ-BMA-TGA Download Datasheet	Tuhinga A22NZ-BMA-TGA
A22NZ-BMA-TGA Stock	Hokona A22NZ-BMA-TGA	Hokona Omron Automation & Safety A22NZ-BMA-TGA
Omron Automation & Safety A22NZ-BMA-TGA	Omron Automation & Safety Kaiwhakarato	Omron Automation & Safety Kaiwhiwhi
Omron Automation & Safety A22NZ-BMA-TGA	Omron Automation and Safety A22NZ-BMA-TGA	

Ngā Hua e hāngai ana

<p>A22NZ-BMA-TRA Kaihanga: Omron Automation & Safety Whakaahuatanga: CONFIG SW BODY PUSHBUTTON ILLUM I roto i te taonga: 18566 pcs</p> <p>RFQ</p>	<p>A22NZ-BMA-UAA Kaihanga: Omron Automation & Safety Whakaahuatanga: CONFIG SW BODY PUSHBUT NON-ILLUM I roto i te taonga: 22464 pcs</p> <p>RFQ</p>
<p>A22NZ-BMA-NBA Kaihanga: Omron Automation & Safety Whakaahuatanga: CONFIG SW BODY PUSHBUT NON-ILLUM I roto i te taonga: 20696 pcs</p> <p>RFQ</p>	<p>A22NZ-BMA-NRA Kaihanga: Omron Automation & Safety Whakaahuatanga: CONFIG SW BODY PUSHBUT NON-ILLUM I roto i te taonga: 24320 pcs</p> <p>RFQ</p>
<p>A22NZ-BMA-TAA Kaihanga: Omron Automation & Safety Whakaahuatanga: CONFIG SW BODY PUSHBUTTON ILLUM I roto i te taonga: 15444 pcs</p> <p>RFQ</p>	<p>A22NZ-BMA-NGA Kaihanga: Omron Automation & Safety Whakaahuatanga: CONFIG SW BODY PUSHBUT NON-ILLUM I roto i te taonga: 24398 pcs</p> <p>RFQ</p>
<p>A22NZ-BMA-TWA Kaihanga: Omron Automation & Safety Whakaahuatanga: CONFIG SW BODY PUSHBUTTON ILLUM I roto i te taonga: 19464 pcs</p> <p>RFQ</p>	<p>A22NZ-BMA-TOA Kaihanga: Omron Automation & Safety Whakaahuatanga: CONFIG SW BODY PUSHBUTTON ILLUM I roto i te taonga: 18669 pcs</p> <p>RFQ</p>
<p>A22NZ-BMA-NWA Kaihanga: Omron Automation & Safety Whakaahuatanga: CONFIG SW BODY PUSHBUT NON-ILLUM I roto i te taonga: 21240 pcs</p> <p>RFQ</p>	<p>A22NZ-BMA-UGA Kaihanga: Omron Automation & Safety Whakaahuatanga: CONFIG SW BODY PUSHBUT NON-ILLUM I roto i te taonga: 23979 pcs</p> <p>RFQ</p>
<p>A22NZ-BMA-TYA Kaihanga: Omron Automation & Safety Whakaahuatanga: CONFIG SW BODY PUSHBUTTON ILLUM I roto i te taonga: 15392 pcs</p> <p>RFQ</p>	<p>A22NZ-BMA-NYA Kaihanga: Omron Automation & Safety Whakaahuatanga: CONFIG SW BODY PUSHBUT NON-ILLUM I roto i te taonga: 23203 pcs</p> <p>RFQ</p>

