

Omron

A6T-8101

Tau Wae:	A6T-8101
Kaihanga / Waitohu:	Omron
Whakaahuatanga hua	SWITCH SLIDE DIP SPST 25MA 24V
Ngā Rauemi:	A6T-8101.pdf
RoHS Tūnga	Whakahaerehia te kore utu / RoHS
Waehere Stock	37898 pcs stock
Tuhinga mai i	Hong Kong
Te Ara Tuhi	DHL/Fedex/TNT/UPS/EMS

TONO MO TE WHAKAHUA

Ko te whakaahua he tohu. Tirohia nga korero mo nga taipitopito hua.

Ngā whakaaturanga o A6T-8101

TAU WAE	A6T-8101
KAIHANGA	Omron
WHAKAAHUATANGA	SWITCH SLIDE DIP SPST 25MA 24V
WHAKAHAERE TOKO WHAKAHAERE / ROHS TŪNGA	Whakahaerehia te kore utu / RoHS
HE RAHINGA KEI TE WĀTEA	37898 pcs
PEPA RARAUNGA	A6T-8101.pdf
HE WAATEA	No
TE WHAKATAU NGAOHIKO	24VDC
KĀHUA WHAKAMUTUNGA	PC Pin
RAUPAPA	A6T
PANA	0.100" (2.54mm), Full
PACKAGING	Tube
ĒTAHI INGOA	A6T8101
TAE MAHI	-20°C ~ 70°C
TAU O NGA TAURANGA	8
MOMO TAE	Through Hole
TE MAHI MOMO	1,000 Cycles
TE ROA	0.837" (21.26mm)
WHAKAHAERE TOKO WHAKAHAERE / ROHS TŪNGA	Lead free / RoHS Compliant
TEITEI I RUNGA I TE POARI	0.142" (3.60mm)
NGĀ ĀHUATANGA	-
TE ORANGA RAWA	1,000 Cycles
WHAKAAHUATANGA TAIPITOPITO	Dip Switch SPST 8 Position Through Hole Slide (Standard) Actuator 25mA 24VDC
WHAKATAURANGA ONAMATA	25mA
WHAKAAETANGA MEA	-
WHAKAUTU WHAKAMUTUNGA	-
TAKAHANGA	SPST
RAUEMI ARA	-
MOMO KAIHOKO	Slide (Standard)
TAUMATA MAHI	Flush, Recessed

Ngā tūtohu e hāngai ana

Omron A6T-8101	A6T-8101 Kaiwhiwhi	A6T-8101 Kaiwhakarato
A6T-8101 Utu	A6T-8101 Pikitia	A6T-8101 Whakaahua
A6T-8101 PDF Datasheet	A6T-8101 Download Datasheet	Tuhinga A6T-8101
A6T-8101 Stock	Hokona A6T-8101	Hokona Omron A6T-8101
Omron A6T-8101	Omron Kaiwhakarato	Omron Kaiwhiwhi
Omron A6T-8101	Omron Electronics Inc-IA Div A6T-8101	Omron Electronics Inc-EMC Div A6T-8101
Omron Electronics LLC A6T-8101		

Ngā Hua e hāngai ana

<p>A6TN-0101 Kaihanga: Omron Whakaahuatanga: SWITCH SLIDE DIP SPST 25MA 24V I roto i te taonga: 41690 pcs</p> <p style="text-align: center; background-color: #ccc; padding: 2px; font-weight: bold;">RFQ</p>	<p>A6TN-1101 Kaihanga: Omron Whakaahuatanga: SWITCH SLIDE DIP SPST 25MA 24V I roto i te taonga: 106182 pcs</p> <p style="text-align: center; background-color: #ccc; padding: 2px; font-weight: bold;">RFQ</p>
<p>A6TN-0104 Kaihanga: Omron Whakaahuatanga: SWITCH SLIDE DIP SPST 25MA 24V I roto i te taonga: 40323 pcs</p> <p style="text-align: center; background-color: #ccc; padding: 2px; font-weight: bold;">RFQ</p>	<p>A6T-7102 Kaihanga: Omron Whakaahuatanga: SWITCH SLIDE DIP SPST 25MA 24V I roto i te taonga: 39541 pcs</p> <p style="text-align: center; background-color: #ccc; padding: 2px; font-weight: bold;">RFQ</p>
<p>A6T-6104 Kaihanga: Omron Whakaahuatanga: SWITCH SLIDE DIP SPST 25MA 24V I roto i te taonga: 66672 pcs</p> <p style="text-align: center; background-color: #ccc; padding: 2px; font-weight: bold;">RFQ</p>	<p>A6T-8104 Kaihanga: Omron Whakaahuatanga: SWITCH SLIDE DIP SPST 25MA 24V I roto i te taonga: 47463 pcs</p> <p style="text-align: center; background-color: #ccc; padding: 2px; font-weight: bold;">RFQ</p>
<p>A6TN-1104 Kaihanga: Omron Whakaahuatanga: SWITCH SLIDE DIP SPST 25MA 24V I roto i te taonga: 116993 pcs</p> <p style="text-align: center; background-color: #ccc; padding: 2px; font-weight: bold;">RFQ</p>	<p>A6T-6102 Kaihanga: Omron Whakaahuatanga: SWITCH SLIDE DIP SPST 25MA 24V I roto i te taonga: 47677 pcs</p> <p style="text-align: center; background-color: #ccc; padding: 2px; font-weight: bold;">RFQ</p>
<p>A6T-5101 Kaihanga: Omron Whakaahuatanga: SWITCH SLIDE DIP SPST 25MA 24V I roto i te taonga: 54233 pcs</p> <p style="text-align: center; background-color: #ccc; padding: 2px; font-weight: bold;">RFQ</p>	<p>A6T-8102 Kaihanga: Omron Whakaahuatanga: SWITCH SLIDE DIP SPST 25MA 24V I roto i te taonga: 32964 pcs</p> <p style="text-align: center; background-color: #ccc; padding: 2px; font-weight: bold;">RFQ</p>
<p>A6T-5102 Kaihanga: Omron Whakaahuatanga: DIP SWITCH I roto i te taonga: 42908 pcs</p> <p style="text-align: center; background-color: #ccc; padding: 2px; font-weight: bold;">RFQ</p>	<p>A6T-6101 Kaihanga: Omron Whakaahuatanga: SWITCH SLIDE DIP SPST 25MA 24V I roto i te taonga: 48950 pcs</p> <p style="text-align: center; background-color: #ccc; padding: 2px; font-weight: bold;">RFQ</p>