



Omron Automation & Safety

## A22NZ-2MM-TYA

Tau Wae:

Kaihanga / Waitohu:

Whakaahuatanga hua

Ngā Rauemi:

RoHS Tūnga

Waehere Stock

Tuhinga mai i

Te Ara Tuhi

A22NZ-2MM-TYA

Omron Automation & Safety

CONFIG SW BODY SELECTOR ILLUM

A22NZ-2MM-TYA.pdf

Whakahaerehia te kore utu / RoHS

15406 pcs stock

Hong Kong

DHL/Fedex/TNT/UPS/EMS



**TONO MO TE WHAKAHUA**

Ko te whakaahua he tohu. Tirohia nga korero mo nga taipitopito hua.

### Ngā whakaaturanga o A22NZ-2MM-TYA

TAU WAE	A22NZ-2MM-TYA
KAIHANGA	Omron Automation & Safety
WHAKAAHUATANGA	CONFIG SW BODY SELECTOR ILLUM
WHAKAHAERE TOKO WHAKAHAERE / ROHS TŪNGA	Whakahaerehia te kore utu / RoHS
HE RAHINGA KEI TE WĀTEA	15406 pcs
PEPA RARAUNGA	A22NZ-2MM-TYA.pdf
MOMO	Maintained
RAUPAPA	A22NW
E HIAHIA ANA	Contact Block(s), Illumination Source
PIHANGA WHAKAPAE PAEPAE	22.3mm (Round)
ĒTAHI INGOA	A22NZ2MMTYA
TAUMATA WHAKAARO MOE (MSL)	1 (Unlimited)
WHAKAHAERE TOKO WHAKAHAERE / ROHS TŪNGA	Lead free / RoHS Compliant
WHAKAAHUATANGA	Illuminated - Yellow
WHAKAAHUATANGA TAIPITOPITO	Configurable Switch Body Selector Illuminated - Yellow
MOMO KAIHOKO	Selector
(TĪPAKOHIA TUATAHI, KA WHAKAMAHIA NGĀ TAEKA) RARAUNGA WHAKAMAHIA	Omron, A22NW

### Ngā tūtohu e hāngai ana

Omron Automation & Safety A22NZ-2MM-TYA	A22NZ-2MM-TYA Kaiwhiwhi	A22NZ-2MM-TYA Kaiwhakarato
A22NZ-2MM-TYA Utu	A22NZ-2MM-TYA Pikitia	A22NZ-2MM-TYA Whakaahua
A22NZ-2MM-TYA PDF Datasheet	A22NZ-2MM-TYA Download Datasheet	Tuhinga A22NZ-2MM-TYA
A22NZ-2MM-TYA Stock	Hokona A22NZ-2MM-TYA	Hokona Omron Automation & Safety A22NZ-2MM-TYA
Omron Automation & Safety A22NZ-2MM-TYA	Omron Automation & Safety Kaiwhakarato	Omron Automation & Safety Kaiwhiwhi
Omron Automation & Safety A22NZ-2MM-TYA	Omron Automation and Safety A22NZ-2MM-TYA	

### Ngā Hua e hāngai ana

<p><b>A22NZ-2RL-NWA</b> Kaihanga: Omron Automation &amp; Safety Whakaahuatanga: CONFIG SW BODY SELECTR NON-ILLUM I roto i te taonga: 14897 pcs</p> <p><b>RFQ</b></p>	<p><b>A22NZ-2RL-01BA</b> Kaihanga: Omron Automation &amp; Safety Whakaahuatanga: CONFIG SW BODY KEYLOCK NON-ILLUM I roto i te taonga: 10580 pcs</p> <p><b>RFQ</b></p>
<p><b>A22NZ-2MM-TAA</b> Kaihanga: Omron Automation &amp; Safety Whakaahuatanga: CONFIG SW BODY SELECTOR ILLUM I roto i te taonga: 15264 pcs</p> <p><b>RFQ</b></p>	<p><b>A22NZ-2MM-TOA</b> Kaihanga: Omron Automation &amp; Safety Whakaahuatanga: CONFIG SW BODY SELECTOR ILLUM I roto i te taonga: 12366 pcs</p> <p><b>RFQ</b></p>
<p><b>A22NZ-2RL-NRA</b> Kaihanga: Omron Automation &amp; Safety Whakaahuatanga: CONFIG SW BODY SELECTR NON-ILLUM I roto i te taonga: 17530 pcs</p> <p><b>RFQ</b></p>	<p><b>A22NZ-2RL-NAA</b> Kaihanga: Omron Automation &amp; Safety Whakaahuatanga: CONFIG SW BODY SELECTR NON-ILLUM I roto i te taonga: 14947 pcs</p> <p><b>RFQ</b></p>
<p><b>A22NZ-2RL-NGA</b> Kaihanga: Omron Automation &amp; Safety Whakaahuatanga: CONFIG SW BODY SELECTR NON-ILLUM I roto i te taonga: 16279 pcs</p> <p><b>RFQ</b></p>	<p><b>A22NZ-2MM-TWA</b> Kaihanga: Omron Automation &amp; Safety Whakaahuatanga: CONFIG SW BODY SELECTOR ILLUM I roto i te taonga: 15879 pcs</p> <p><b>RFQ</b></p>
<p><b>A22NZ-2MM-TRA</b> Kaihanga: Omron Automation &amp; Safety Whakaahuatanga: CONFIG SW BODY SELECTOR ILLUM I roto i te taonga: 13099 pcs</p> <p><b>RFQ</b></p>	<p><b>A22NZ-2MM-TGA</b> Kaihanga: Omron Automation &amp; Safety Whakaahuatanga: CONFIG SW BODY SELECTOR ILLUM I roto i te taonga: 15524 pcs</p> <p><b>RFQ</b></p>
<p><b>A22NZ-2MM-NYA</b> Kaihanga: Omron Automation &amp; Safety Whakaahuatanga: CONFIG SW BODY SELECTR NON-ILLUM I roto i te taonga: 14908 pcs</p> <p><b>RFQ</b></p>	<p><b>A22NZ-2RL-NBA</b> Kaihanga: Omron Automation &amp; Safety Whakaahuatanga: CONFIG SW BODY SELECTR NON-ILLUM I roto i te taonga: 17110 pcs</p> <p><b>RFQ</b></p>

