



STMicroelectronics

## LPR5150AL

Tau Wae:

Kaihanga / Waitohu:

Whakaahuatanga hua

Ngā Rauemi:

RoHS Tūnga

Waehe Stock

Tuhinga mai i

Te Ara Tuhi

LPR5150AL

STMicroelectronics

GYROSCOPE DUAL AXIS 16-LGA


 LPR5150AL.pdf

 Whakahaerehia te kore utu / RoHS

18372 pcs stock


Hong Kong

DHL/Fedex/TNT/UPS/EMS


**TONO MO TE WHAKAHUA**

Ko te whakaahua he tohu. Tirohia nga korero mo nga taipitopito hua.


## Ngā whakaaturanga o LPR5150AL

|   |   |
|---|---|
| TAU WAE                                 | LPR5150AL   |
| KAIHANGA                                | STMicroelectronics  |
| WHAKAAHUATANGA                          | GYROSCOPE DUAL AXIS 16-LGA  |
| WHAKAHAERE TOKO WHAKAHAERE / ROHS TŪNGA | Whakahaerehia te kore utu / RoHS  |
| HE RAHINGA KEI TE WĀTEA                 | 18372 pcs   |
| PEPA RARAUNGA                           |  LPR5150AL.pdf |
| TUHINGA O MUA                           | 2.7 V ~ 3.6 V   |
| MOMO                                    | Analog  |
| RAUPAPA                                 | -   |
| WHAKAAROARO (MV / ° / S)                | 0.67  |
| WHAKAAROARO (LSB / (° / S))             | -   |
| RANGE ° / S                             | ±1500   |
| PACKAGING                               | Tray  |
| PAA / CASE                              | 16-LFLGA  |
| MOMO PUTANGA                            | Analog Voltage  |
| TAE MAHI                                | -40°C ~ 85°C (TA)   |
| TAUMATA WHAKAARO MOE (MSL)              | 3 (168 Hours)   |
| WHAKAHAERE TOKO WHAKAHAERE / ROHS TŪNGA | Lead free / RoHS Compliant  |
| NGĀ ĀHUATANGA                           | -   |
| WHAKAAHUATANGA TAIPITOPITO              | Gyroscope X (Pitch), Y (Roll) ±1500 140Hz Analog Voltage 16-LGA (5x5)                             |
| I TEIE NEI - TE TUKU                    | 6.8mA   |
| TUHINGA O MUA                           | 140Hz   |
| AXIS                                    | X (Pitch), Y (Roll)   |

## Ngā tūtohu e hāngai ana

|                              |                                 |                                     |
|------------------------------|---------------------------------|-------------------------------------|
| STMicroelectronics LPR5150AL | LPR5150AL Kaiwhiwhi             | LPR5150AL Kaiwhakarato              |
| LPR5150AL Utu                | LPR5150AL Pikitia               | LPR5150AL Whakaahua                 |
| LPR5150AL PDF Datasheet      | LPR5150AL Download Datasheet    | Tuhinga LPR5150AL                   |
| LPR5150AL Stock              | Hokona LPR5150AL                | Hokona STMicroelectronics LPR5150AL |
| STMicroelectronics LPR5150AL | STMicroelectronics Kaiwhakarato | STMicroelectronics Kaiwhiwhi        |
| STMicroelectronics LPR5150AL |                                 |                                     |

## Ngā Hua e hāngai ana

|  |   |
|--|---|
|  <p><b>LPR550AL</b><br/>Kaihanga: STMicroelectronics<br/>Whakaahuatanga: GYROSCOPE DUAL AXIS 16-LGA<br/>I roto i te taonga: 18895 pcs</p> <p><b>RFQ</b></p>        |  <p><b>LPR530AL</b><br/>Kaihanga: STMicroelectronics<br/>Whakaahuatanga: GYROSCOPE DUAL AXIS 16-LGA<br/>I roto i te taonga: 21086 pcs</p> <p><b>RFQ</b></p>        |
|  <p><b>LPR510ALTR</b><br/>Kaihanga: STMicroelectronics<br/>Whakaahuatanga: GYROSCOPE MEMS DUAL AXIS 16-LGA<br/>I roto i te taonga: 10593 pcs</p> <p><b>RFQ</b></p> |  <p><b>LPR550ALTR</b><br/>Kaihanga: STMicroelectronics<br/>Whakaahuatanga: GYROSCOPE MEMS DUAL AXIS 16-LGA<br/>I roto i te taonga: 17696 pcs</p> <p><b>RFQ</b></p> |
|  <p><b>LPR5-1250-3000DP</b><br/>Kaihanga: Bivar, Inc.<br/>Whakaahuatanga: LIGHT PIPE RIGID RA 4.93MM DIA<br/>I roto i te taonga: 46683 pcs</p> <p><b>RFQ</b></p>   |  <p><b>LPR503ALTR</b><br/>Kaihanga: STMicroelectronics<br/>Whakaahuatanga: GYROSCOPE MEMS DUAL AXIS 16-LGA<br/>I roto i te taonga: 16172 pcs</p> <p><b>RFQ</b></p> |
|  <p><b>LPR5150ALTR</b><br/>Kaihanga: STMicroelectronics<br/>Whakaahuatanga: GYROSCOPE MEMS DUAL AXIS 16-LGA<br/>I roto i te taonga: 9793 pcs</p> <p><b>RFQ</b></p> |  <p><b>LPR5-1250-3000FP</b><br/>Kaihanga: Bivar, Inc.<br/>Whakaahuatanga: LIGHT PIPE RIGID RA 4.93MM DIA<br/>I roto i te taonga: 43866 pcs</p> <p><b>RFQ</b></p>   |
|  <p><b>LPR530ALTR</b><br/>Kaihanga: STMicroelectronics<br/>Whakaahuatanga: GYROSCOPE MEMS DUAL AXIS 16-LGA<br/>I roto i te taonga: 5420 pcs</p> <p><b>RFQ</b></p>  |  <p><b>LPR5-1250-2500FP</b><br/>Kaihanga: Bivar, Inc.<br/>Whakaahuatanga: LIGHT PIPE RIGID RA 4.93MM DIA<br/>I roto i te taonga: 48632 pcs</p> <p><b>RFQ</b></p>   |
|  <p><b>LPR503AL</b><br/>Kaihanga: STMicroelectronics<br/>Whakaahuatanga: GYROSCOPE DUAL AXIS 16-LGA<br/>I roto i te taonga: 21508 pcs</p> <p><b>RFQ</b></p>        |  <p><b>LPR510AL</b><br/>Kaihanga: STMicroelectronics<br/>Whakaahuatanga: GYROSCOPE DUAL AXIS 16-LGA<br/>I roto i te taonga: 18631 pcs</p> <p><b>RFQ</b></p>        |