

Agastat Relays / TE Connectivity

DP09HN15A30K

| | |
|---------------------|----------------------------------|
| Tau Wae: | DP09HN15A30K |
| Kaihanga / Waitohu: | Agastat Relays / TE Connectivity |
| Whakaahuatanga hua | DP09 HOR 15P NDET 30K M7*5MM |
| Ngā Rauemi: | DP09HN15A30K.pdf |
| RoHS Tūnga | Whakahaerehia te kore utu / RoHS |
| Waehere Stock | 45349 pcs stock |
| Tuhinga mai i | Hong Kong |
| Te Ara Tuhi | DHL/Fedex/TNT/UPS/EMS |

TONO MO TE WHAKAHUA

Ko te whakaahua he tohu. Tirohia nga korero mo nga taipitopito hua.

Ngā whakaaturanga o DP09HN15A30K

| | |
|---|----------------------------------|
| TAU WAE | DP09HN15A30K |
| KAIHANGA | Agastat Relays / TE Connectivity |
| WHAKAAHUATANGA | DP09 HOR 15P NDET 30K M7*5MM |
| WHAKAHAERE TOKO WHAKAHAERE / ROHS TŪNGA | Whakahaerehia te kore utu / RoHS |
| HE RAHINGA KEI TE WĀTEA | 45349 pcs |
| PEPA RARAUNGA | DP09HN15A30K.pdf |
| RAUPAPA | * |
| ĒTAHI INGOA | 6-1879325-4 |
| TAUMATA WHAKAARO MOE (MSL) | 1 (Unlimited) |
| WHAKAHAERE TOKO WHAKAHAERE / ROHS TŪNGA | Lead free / RoHS Compliant |

Ngā tūtohu e hāngai ana

| | | |
|---|---|--|
| Agastat Relays / TE Connectivity DP09HN15A30K | DP09HN15A30K Kaiwhiwhi | DP09HN15A30K Kaiwhakarato |
| DP09HN15A30K Utu | DP09HN15A30K Pikitia | DP09HN15A30K Whakaahua |
| DP09HN15A30K PDF Datasheet | DP09HN15A30K Download Datasheet | Tuhinga DP09HN15A30K |
| DP09HN15A30K Stock | Hokona DP09HN15A30K | Hokona Agastat Relays / TE Connectivity DP09HN15A30K |
| Agastat Relays / TE Connectivity DP09HN15A30K | Agastat Relays / TE Connectivity Kaiwhakarato | Agastat Relays / TE Connectivity Kaiwhiwhi |
| Agastat Relays / TE Connectivity DP09HN15A30K | Axicom Relays / TE Connectivity DP09HN15A30K | Buchanan Terminal Blocks / TE Connectivity DP09HN15A30K |
| CGS Resistors / TE Connectivity DP09HN15A30K | CII / TE Connectivity DP09HN15A30K | Elcon Connectors / TE Connectivity DP09HN15A30K |
| Holsworthy Resistors / TE Connectivity DP09HN15A30K | Kilovac Relays / TE Connectivity DP09HN15A30K | Neohm Resistors / TE Connectivity DP09HN15A30K |
| OEG Relays / TE Connectivity DP09HN15A30K | Products Unlimited Transformers & Relays / TE Conn DP09HN15A30K | Q-Cee's / TE Connectivity DP09HN15A30K |
| Schrack Relays / TE Connectivity DP09HN15A30K | Sigma Inductors / TE Connectivity DP09HN15A30K | TE Connectivity's Agastat Relays DP09HN15A30K |
| TE Connectivity's Axicom Relays DP09HN15A30K | TE Connectivity's Buchanan Terminal Blocks DP09HN15A30K | TE Connectivity's CGS Resistors DP09HN15A30K |
| TE Connectivity's CII DP09HN15A30K | TE Connectivity's Elcon Connectors DP09HN15A30K | TE Connectivity's Holsworthy Resistors DP09HN15A30K |
| TE Connectivity's Neohm Resistors DP09HN15A30K | TE Connectivity's OEG Relays DP09HN15A30K | TE Connectivity's Q-Cee's DP09HN15A30K |
| TE Connectivity's Schrack Relays DP09HN15A30K | TE Connectivity's Sigma Inductors DP09HN15A30K | TE Connectivity's Products Unlimited Transformers DP09HN15A30K |
| TE Connectivity's Kilovac Relays DP09HN15A30K | | |

Ngā Hua e hāngai ana

| | |
|---|---|
| <div style="border: 1px solid #ccc; padding: 5px;"> <p>DP09HN15B25F Kaihanga: Agastat Relays / TE Connectivity Whakaahuatanga: DP09 HOR 15P NDET 25F M7*7MM I roto i te taonga: 45511 pcs</p> <p style="text-align: center; background-color: #ccc; padding: 2px; font-weight: bold;">RFQ</p> </div> | <div style="border: 1px solid #ccc; padding: 5px;"> <p>DP09HN15B20F Kaihanga: Agastat Relays / TE Connectivity Whakaahuatanga: DP09 HOR 15P NDET 20F M7*7MM I roto i te taonga: 44303 pcs</p> <p style="text-align: center; background-color: #ccc; padding: 2px; font-weight: bold;">RFQ</p> </div> |
| <div style="border: 1px solid #ccc; padding: 5px;"> <p>DP09HN15B15F Kaihanga: Agastat Relays / TE Connectivity Whakaahuatanga: DP09 HOR 15P NDET 15F M7*7MM I roto i te taonga: 44403 pcs</p> <p style="text-align: center; background-color: #ccc; padding: 2px; font-weight: bold;">RFQ</p> </div> | <div style="border: 1px solid #ccc; padding: 5px;"> <p>DP09HN15A20K Kaihanga: Agastat Relays / TE Connectivity Whakaahuatanga: DP09 HOR 15P NDET 20K M7*5MM I roto i te taonga: 37869 pcs</p> <p style="text-align: center; background-color: #ccc; padding: 2px; font-weight: bold;">RFQ</p> </div> |
| <div style="border: 1px solid #ccc; padding: 5px;"> <p>DP09HN15A25F Kaihanga: Agastat Relays / TE Connectivity Whakaahuatanga: DP09 HOR 15P NDET 25F M7*5MM I roto i te taonga: 39705 pcs</p> <p style="text-align: center; background-color: #ccc; padding: 2px; font-weight: bold;">RFQ</p> </div> | <div style="border: 1px solid #ccc; padding: 5px;"> <p>DP09HN15A25K Kaihanga: Agastat Relays / TE Connectivity Whakaahuatanga: DP09 HOR 15P NDET 25K M7*5MM I roto i te taonga: 49369 pcs</p> <p style="text-align: center; background-color: #ccc; padding: 2px; font-weight: bold;">RFQ</p> </div> |
| <div style="border: 1px solid #ccc; padding: 5px;"> <p>DP09HN15B20K Kaihanga: Agastat Relays / TE Connectivity Whakaahuatanga: DP09 HOR 15P NDET 20K M7*7MM I roto i te taonga: 42200 pcs</p> <p style="text-align: center; background-color: #ccc; padding: 2px; font-weight: bold;">RFQ</p> </div> | <div style="border: 1px solid #ccc; padding: 5px;"> <p>DP09HN15B15K Kaihanga: Agastat Relays / TE Connectivity Whakaahuatanga: DP09 HOR 15P NDET 15K M7*7MM I roto i te taonga: 49502 pcs</p> <p style="text-align: center; background-color: #ccc; padding: 2px; font-weight: bold;">RFQ</p> </div> |
| <div style="border: 1px solid #ccc; padding: 5px;"> <p>DP09HN15A15K Kaihanga: Agastat Relays / TE Connectivity Whakaahuatanga: DP09 HOR 15P NDET 15K M7*5MM I roto i te taonga: 41726 pcs</p> <p style="text-align: center; background-color: #ccc; padding: 2px; font-weight: bold;">RFQ</p> </div> | <div style="border: 1px solid #ccc; padding: 5px;"> <p>DP09HN15B25K Kaihanga: Agastat Relays / TE Connectivity Whakaahuatanga: DP09 HOR 15P NDET 25K M7*7MM I roto i te taonga: 48335 pcs</p> <p style="text-align: center; background-color: #ccc; padding: 2px; font-weight: bold;">RFQ</p> </div> |
| <div style="border: 1px solid #ccc; padding: 5px;"> <p>DP09HN15A20F Kaihanga: Agastat Relays / TE Connectivity Whakaahuatanga: DP09 HOR 15P NDET 20F M7*5MM I roto i te taonga: 42190 pcs</p> <p style="text-align: center; background-color: #ccc; padding: 2px; font-weight: bold;">RFQ</p> </div> | <div style="border: 1px solid #ccc; padding: 5px;"> <p>DP09HN15A30F Kaihanga: Agastat Relays / TE Connectivity Whakaahuatanga: DP09 HOR 15P NDET 30F M7*5MM I roto i te taonga: 35785 pcs</p> <p style="text-align: center; background-color: #ccc; padding: 2px; font-weight: bold;">RFQ</p> </div> |