



Omron Automation & Safety

## A165W-J3AG

Tau Wae:

A165W-J3AG

Kaihanga / Waitohu:

Omron Automation & Safety

Whakaahuatanga hua

CONFIG SW BODY SELECTOR ILLUM

Ngā Rauemi:

A165W-J3AG.pdf

RoHS Tūnga

Whakahaerehia te kore utu / RoHS

Waehere Stock

3355 pcs stock

Tuhinga mai i

Hong Kong

Te Ara Tuhi

DHL/Fedex/TNT/UPS/EMS



**TONO MO TE WHAKAHUA**

Ko te whakaahua he tohu. Tirohia nga korero mo nga taipitopito hua.

### Ngā whakaaturanga o A165W-J3AG

TAU WAE	A165W-J3AG
KAIHANGA	Omron Automation & Safety
WHAKAAHUATANGA	CONFIG SW BODY SELECTOR ILLUM
WHAKAHAERE TOKO WHAKAHAERE / ROHS TŪNGA	Whakahaerehia te kore utu / RoHS
HE RAHINGA KEI TE WĀTEA	3355 pcs
PEPA RARAUNGA	A165W-J3AG.pdf
MOMO	Momentary
RAUPAPA	A165W
E HIAHIA ANA	Contact Block(s), Illumination Source
PIHANGA WHAKAPAE PAEPAE	16mm (Round)
ĒTAHI INGOA	A165WJ3AG
TAUMATA WHAKAARO MOE (MSL)	1 (Unlimited)
WHAKAHAERE TOKO WHAKAHAERE / ROHS TŪNGA	Lead free / RoHS Compliant
WHAKAAHUATANGA	Illuminated - Green
WHAKAAHUATANGA TAIPITOPITO	Configurable Switch Body Selector Illuminated - Green
MOMO KAIHOKO	Selector
(TĪPAKOHIA TUATAHI, KA WHAKAMAHIA NGĀ TAEKA) RARAUNGA WHAKAMAHIA	Omron, A165W

### Ngā tūtohu e hāngai ana

Omron Automation & Safety A165W-J3AG	A165W-J3AG Kaiwhiwhi	A165W-J3AG Kaiwhakarato
A165W-J3AG Utu	A165W-J3AG Pikitia	A165W-J3AG Whakaahua
A165W-J3AG PDF Datasheet	A165W-J3AG Download Datasheet	Tuhinga A165W-J3AG
A165W-J3AG Stock	Hokona A165W-J3AG	Hokona Omron Automation & Safety A165W-J3AG
Omron Automation & Safety A165W-J3AG	Omron Automation & Safety Kaiwhakarato	Omron Automation & Safety Kaiwhiwhi
Omron Automation & Safety A165W-J3AG	Omron Automation and Safety A165W-J3AG	

### Ngā Hua e hāngai ana

<p><b>A165W-J3MG</b> Kaihanga: Omron Automation &amp; Safety Whakaahuatanga: CONFIG SW BODY SELECTOR ILLUM I roto i te taonga: 3222 pcs</p> <p><b>RFQ</b></p>	<p><b>A165W-J2MR-24D-2</b> Kaihanga: Omron Automation &amp; Safety Whakaahuatanga: SWITCH SELECT 2POS DPDT 5A 125V I roto i te taonga: 1982 pcs</p> <p><b>RFQ</b></p>
<p><b>A165W-J3AY</b> Kaihanga: Omron Automation &amp; Safety Whakaahuatanga: CONFIG SW BODY SELECTOR ILLUM I roto i te taonga: 3727 pcs</p> <p><b>RFQ</b></p>	<p><b>A165W-J3MG-24D-2</b> Kaihanga: Omron Automation &amp; Safety Whakaahuatanga: SWITCH SELECT 3POS DPDT 5A 125V I roto i te taonga: 2167 pcs</p> <p><b>RFQ</b></p>
<p><b>A165W-J2MR</b> Kaihanga: Omron Automation &amp; Safety Whakaahuatanga: CONFIG SW BODY SELECTOR ILLUM I roto i te taonga: 3770 pcs</p> <p><b>RFQ</b></p>	<p><b>A165W-J2MR-24D-1</b> Kaihanga: Omron Automation &amp; Safety Whakaahuatanga: SWITCH SELECT 2POS SPDT 5A 125V I roto i te taonga: 2249 pcs</p> <p><b>RFQ</b></p>
<p><b>A165W-J2MY</b> Kaihanga: Omron Automation &amp; Safety Whakaahuatanga: CONFIG SW BODY SELECTOR ILLUM I roto i te taonga: 3870 pcs</p> <p><b>RFQ</b></p>	<p><b>A165W-J2MY-24D-2</b> Kaihanga: Omron Automation &amp; Safety Whakaahuatanga: SWITCH SELECT 2POS DPDT 5A 125V I roto i te taonga: 2255 pcs</p> <p><b>RFQ</b></p>
<p><b>A165W-J3MR</b> Kaihanga: Omron Automation &amp; Safety Whakaahuatanga: CONFIG SW BODY SELECTOR ILLUM I roto i te taonga: 2959 pcs</p> <p><b>RFQ</b></p>	<p><b>A165W-J2MY-24D-1</b> Kaihanga: Omron Automation &amp; Safety Whakaahuatanga: SWITCH SELECT 2POS SPDT 5A 125V I roto i te taonga: 2001 pcs</p> <p><b>RFQ</b></p>
<p><b>A165W-J3AR</b> Kaihanga: Omron Automation &amp; Safety Whakaahuatanga: CONFIG SW BODY SELECTOR ILLUM I roto i te taonga: 3918 pcs</p> <p><b>RFQ</b></p>	<p><b>A165W-J3MR-24D-2</b> Kaihanga: Omron Automation &amp; Safety Whakaahuatanga: SWITCH SELECT 3POS DPDT 5A 125V I roto i te taonga: 2049 pcs</p> <p><b>RFQ</b></p>

