

Agastat Relays / TE Connectivity

CR0002

Tau Wae:	CR0002
Kaihanga / Waitohu:	Agastat Relays / TE Connectivity
Whakaahuatanga hua	RLY SKT
Ngā Rauemi:	CR0002.pdf
RoHS Tūnga	Kei roto nga rangatira / RoHS kaore i te ture
Waehere Stock	1116 pcs stock
Tuhinga mai i	Hong Kong
Te Ara Tuhi	DHL/Fedex/TNT/UPS/EMS

TONO MO TE WHAKAHUA

Ko te whakaahua he tohu. Tirohia nga korero mo nga taipitopito hua.

Ngā whakaaturanga o CR0002

TAU WAE	CR0002
KAIHANGA	Agastat Relays / TE Connectivity
WHAKAAHUATANGA	RLY SKT
WHAKAHAERE TOKO WHAKAHAERE / ROHS TŪNGA	Kei roto nga rangatira / RoHS kaore i te ture
HE RAHINGA KEI TE WĀTEA	1116 pcs
PEPA RARAUNGA	CR0002.pdf
RAUPAPA	*
ĒTAHI INGOA	1-1437436-0
TAUMATA WHAKAARO MOE (MSL)	1 (Unlimited)
WHAKAHAERE TOKO WHAKAHAERE / ROHS TŪNGA	Contains lead / RoHS non-compliant
WHAKAAHUATANGA TAIPITOPITO	Relay

Ngā tūtohu e hāngai ana

Agastat Relays / TE Connectivity CR0002	CR0002 Kaiwhiwhi	CR0002 Kaiwhakarato
CR0002 Utu	CR0002 Pikitia	CR0002 Whakaahua
CR0002 PDF Datasheet	CR0002 Download Datasheet	Tuhinga CR0002
CR0002 Stock	Hokona CR0002	Hokona Agastat Relays / TE Connectivity CR0002
Agastat Relays / TE Connectivity CR0002	Agastat Relays / TE Connectivity Kaiwhakarato	Agastat Relays / TE Connectivity Kaiwhiwhi
Agastat Relays / TE Connectivity CR0002	Axicom Relays / TE Connectivity CR0002	Buchanan Terminal Blocks / TE Connectivity CR0002
CGS Resistors / TE Connectivity CR0002	CII / TE Connectivity CR0002	Elcon Connectors / TE Connectivity CR0002
Holsworthy Resistors / TE Connectivity CR0002	Kilovac Relays / TE Connectivity CR0002	Neohm Resistors / TE Connectivity CR0002
OEG Relays / TE Connectivity CR0002	Products Unlimited Transformers & Relays / TE Conn CR0002	Q-Cee's / TE Connectivity CR0002
Schrack Relays / TE Connectivity CR0002	Sigma Inductors / TE Connectivity CR0002	TE Connectivity's Agastat Relays CR0002
TE Connectivity's Axicom Relays CR0002	TE Connectivity's Buchanan Terminal Blocks CR0002	TE Connectivity's CGS Resistors CR0002
TE Connectivity's CII CR0002	TE Connectivity's Elcon Connectors CR0002	TE Connectivity's Holsworthy Resistors CR0002
TE Connectivity's Neohm Resistors CR0002	TE Connectivity's OEG Relays CR0002	TE Connectivity's Q-Cee's CR0002
TE Connectivity's Schrack Relays CR0002	TE Connectivity's Sigma Inductors CR0002	TE Connectivity's Products Unlimited Transformers CR0002
TE Connectivity's Kilovac Relays CR0002		

Ngā Hua e hāngai ana

<div style="display: flex; align-items: flex-start;"> <div> <p>CR0067</p> <p>Kaihanga: Agastat Relays / TE Connectivity</p> <p>Whakaahuatanga: CONNECTOR BLOCKS</p> <p>I roto i te taonga: 812 pcs</p> <p style="background-color: #ccc; padding: 2px 10px; display: inline-block; font-weight: bold;">RFQ</p> </div> </div>	<div style="display: flex; align-items: flex-start;"> <div> <p>CR0069</p> <p>Kaihanga: Agastat Relays / TE Connectivity</p> <p>Whakaahuatanga: HOLD DOWN SPRING</p> <p>I roto i te taonga: 1858 pcs</p> <p style="background-color: #ccc; padding: 2px 10px; display: inline-block; font-weight: bold;">RFQ</p> </div> </div>
<div style="display: flex; align-items: flex-start;"> <div> <p>CR0060</p> <p>Kaihanga: Arcoelectric (Bulgin)</p> <p>Whakaahuatanga: CROCODILE CLIP</p> <p>I roto i te taonga: 8059 pcs</p> <p style="background-color: #ccc; padding: 2px 10px; display: inline-block; font-weight: bold;">RFQ</p> </div> </div>	<div style="display: flex; align-items: flex-start;"> <div> <p>CR0095</p> <p>Kaihanga: Agastat Relays / TE Connectivity</p> <p>Whakaahuatanga: CONNECTOR BLOCKS</p> <p>I roto i te taonga: 253 pcs</p> <p style="background-color: #ccc; padding: 2px 10px; display: inline-block; font-weight: bold;">RFQ</p> </div> </div>
<div style="display: flex; align-items: flex-start;"> <div> <p>CR0170-000</p> <p>Kaihanga: Agastat Relays / TE Connectivity</p> <p>Whakaahuatanga: HOOK-UP DL WALL STRND 24AWG RED</p> <p>I roto i te taonga: 304270 pcs</p> <p style="background-color: #ccc; padding: 2px 10px; display: inline-block; font-weight: bold;">RFQ</p> </div> </div>	<div style="display: flex; align-items: flex-start;"> <div> <p>CR0001</p> <p>Kaihanga: Agastat Relays / TE Connectivity</p> <p>Whakaahuatanga: CONNECTOR BLOCKS</p> <p>I roto i te taonga: 1435 pcs</p> <p style="background-color: #ccc; padding: 2px 10px; display: inline-block; font-weight: bold;">RFQ</p> </div> </div>
<div style="display: flex; align-items: flex-start;"> <div> <p>CR0070</p> <p>Kaihanga: Agastat Relays / TE Connectivity</p> <p>Whakaahuatanga: HOLD DOWN SPRING</p> <p>I roto i te taonga: 412 pcs</p> <p style="background-color: #ccc; padding: 2px 10px; display: inline-block; font-weight: bold;">RFQ</p> </div> </div>	<div style="display: flex; align-items: flex-start;"> <div> <p>CR0028</p> <p>Kaihanga: Arcoelectric (Bulgin)</p> <p>Whakaahuatanga: CROCODILE CLIP</p> <p>I roto i te taonga: 23164 pcs</p> <p style="background-color: #ccc; padding: 2px 10px; display: inline-block; font-weight: bold;">RFQ</p> </div> </div>
<div style="display: flex; align-items: flex-start;"> <div> <p>CR0201-FW-1000GLF</p> <p>Kaihanga: Bourns, Inc.</p> <p>Whakaahuatanga: RES SMD 100 OHM 1% 1/20W 0201</p> <p>I roto i te taonga: 2497491 pcs</p> <p style="background-color: #ccc; padding: 2px 10px; display: inline-block; font-weight: bold;">RFQ</p> </div> </div>	<div style="display: flex; align-items: flex-start;"> <div> <p>CR0174-000</p> <p>Kaihanga: Agastat Relays / TE Connectivity</p> <p>Whakaahuatanga: HEAT SHRINK TUBING 3/4" BK</p> <p>I roto i te taonga: 10745 pcs</p> <p style="background-color: #ccc; padding: 2px 10px; display: inline-block; font-weight: bold;">RFQ</p> </div> </div>
<div style="display: flex; align-items: flex-start;"> <div> <p>CR0171-000</p> <p>Kaihanga: Agastat Relays / TE Connectivity</p> <p>Whakaahuatanga: HOOK-UP DUAL WALL STRND 24AWG</p> <p>I roto i te taonga: 286112 pcs</p> <p style="background-color: #ccc; padding: 2px 10px; display: inline-block; font-weight: bold;">RFQ</p> </div> </div>	<div style="display: flex; align-items: flex-start;"> <div> <p>CR0111</p> <p>Kaihanga: Agastat Relays / TE Connectivity</p> <p>Whakaahuatanga: RETAINING SPRING KIT</p> <p>I roto i te taonga: 2436 pcs</p> <p style="background-color: #ccc; padding: 2px 10px; display: inline-block; font-weight: bold;">RFQ</p> </div> </div>