

BEI Sensors

## L25G-625-ABZ-5V/OCR-EPT07

Tau Wae:	L25G-625-ABZ-5V/OCR-EPT07
Kaihanga / Waitohu:	BEI Sensors
Whakaahuatanga hua	ROTARY ENCODER OPTICAL 625PPR
Ngā Rauemi:	L25G-625-ABZ-5V/OCR-EPT07.pdf
RoHS Tūnga	Whakahaerehia te kore utu / RoHS
Waehere Stock	169 pcs stock
Tuhinga mai i	Hong Kong
Te Ara Tuhi	DHL/Fedex/TNT/UPS/EMS

TONO MO TE WHAKAHUA

Ko te whakaahua he tohu. Tirohia nga korero mo nga taipitopito hua.

### Ngā whakaaturanga o L25G-625-ABZ-5V/OCR-EPT07

TAU WAE	L25G-625-ABZ-5V/OCR-EPT07
KAIHANGA	BEI Sensors
WHAKAAHUATANGA	ROTARY ENCODER OPTICAL 625PPR
WHAKAHAERE TOKO WHAKAHAERE / ROHS TŪNGA	Whakahaerehia te kore utu / RoHS
HE RAHINGA KEI TE WĀTEA	169 pcs
PEPA RARAUNGA	L25G-625-ABZ-5V/OCR-EPT07.pdf
TUHINGA O MUA	5V
KĀHUA WHAKAMUTUNGA	Connector
RAUPAPA	L25
KO TE ROTATIONAL LIFE (CYCLES MIN)	1B
PULSES IA REVOLUTION	625
MOMO PUTANGA	Quadrature with Index (Incremental)
ĒTAHI INGOA	01008-2061
WHAKATAKOTORANGA	-
MOMO TAE	Servo Mount
TAUMATA WHAKAARO MOE (MSL)	1 (Unlimited)
WHAKAHAERE TOKO WHAKAHAERE / ROHS TŪNGA	Lead free / RoHS Compliant
MOMO KUPUTUHI	Optical
TUHINGA	No
HANGAIA KI TE WHAKAWHITI	No
MOMO KAIHOKO	Shaft

### Ngā tūtohu e hāngai ana

BEI Sensors L25G-625-ABZ-5V/OCR-EPT07	L25G-625-ABZ-5V/OCR-EPT07 Kaiwhiwhi	L25G-625-ABZ-5V/OCR-EPT07 Kaiwhakarato
L25G-625-ABZ-5V/OCR-EPT07 Utu	L25G-625-ABZ-5V/OCR-EPT07 Pikitia	L25G-625-ABZ-5V/OCR-EPT07 Whakaahua
L25G-625-ABZ-5V/OCR-EPT07 PDF Datasheet	L25G-625-ABZ-5V/OCR-EPT07 Download Datasheet	Tuhinga L25G-625-ABZ-5V/OCR-EPT07
L25G-625-ABZ-5V/OCR-EPT07 Stock	Hokona L25G-625-ABZ-5V/OCR-EPT07	Hokona BEI Sensors L25G-625-ABZ-5V/OCR-EPT07
BEI Sensors L25G-625-ABZ-5V/OCR-EPT07	BEI Sensors Kaiwhakarato	BEI Sensors Kaiwhiwhi
BEI Sensors L25G-625-ABZ-5V/OCR-EPT07	Sensata Technologies – BEI Sensors L25G-625-ABZ-5V/OCR-EPT07	

### Ngā Hua e hāngai ana

<div style="display: flex; align-items: center;"> <div> <p style="margin: 0;"><b>L25G-F2-1000-ABZ-28V/V-SC5-S</b></p> <p style="margin: 0; font-size: 0.8em;">Kaihanga: BEI Sensors Whakaahuatanga: ROTARY ENCODER OPTICAL 1000PPR I roto i te taonga: 172 pcs</p> <p style="text-align: center; background-color: #ccc; padding: 2px 5px; margin: 5px 0;">RFQ</p> </div> </div>	<div style="display: flex; align-items: center;"> <div> <p style="margin: 0;"><b>L25G-SB-500-ABZC-28V/5-SC24-S</b></p> <p style="margin: 0; font-size: 0.8em;">Kaihanga: BEI Sensors Whakaahuatanga: ROTARY ENCODER OPTICAL 500PPR I roto i te taonga: 179 pcs</p> <p style="text-align: center; background-color: #ccc; padding: 2px 5px; margin: 5px 0;">RFQ</p> </div> </div>
<div style="display: flex; align-items: center;"> <div> <p style="margin: 0;"><b>L25J100E</b></p> <p style="margin: 0; font-size: 0.8em;">Kaihanga: Ohmite Whakaahuatanga: RES CHAS MNT 100 OHM 5% 25W I roto i te taonga: 11842 pcs</p> <p style="text-align: center; background-color: #ccc; padding: 2px 5px; margin: 5px 0;">RFQ</p> </div> </div>	<div style="display: flex; align-items: center;"> <div> <p style="margin: 0;"><b>L253F-F8-SS-1000-ABC-15V/V-EM14-S</b></p> <p style="margin: 0; font-size: 0.8em;">Kaihanga: BEI Sensors Whakaahuatanga: ENCODER ROTARY 1000PPR 15V I roto i te taonga: 187 pcs</p> <p style="text-align: center; background-color: #ccc; padding: 2px 5px; margin: 5px 0;">RFQ</p> </div> </div>
<div style="display: flex; align-items: center;"> <div> <p style="margin: 0;"><b>L25G-F3-1-ABZC-5V/OCR-SM18</b></p> <p style="margin: 0; font-size: 0.8em;">Kaihanga: BEI Sensors Whakaahuatanga: ROTARY ENCODER OPTICAL PROG I roto i te taonga: 196 pcs</p> <p style="text-align: center; background-color: #ccc; padding: 2px 5px; margin: 5px 0;">RFQ</p> </div> </div>	<div style="display: flex; align-items: center;"> <div> <p style="margin: 0;"><b>L25G-F3-1024-ABZC-28V/V-SC18-S</b></p> <p style="margin: 0; font-size: 0.8em;">Kaihanga: BEI Sensors Whakaahuatanga: ROTARY ENCODER OPTICAL 1024PPR I roto i te taonga: 178 pcs</p> <p style="text-align: center; background-color: #ccc; padding: 2px 5px; margin: 5px 0;">RFQ</p> </div> </div>
<div style="display: flex; align-items: center;"> <div> <p style="margin: 0;"><b>L25G-F12-SB-2500-ABZC-28V/V-SM18</b></p> <p style="margin: 0; font-size: 0.8em;">Kaihanga: BEI Sensors Whakaahuatanga: ROTARY ENCODER OPTICAL 2500PPR I roto i te taonga: 180 pcs</p> <p style="text-align: center; background-color: #ccc; padding: 2px 5px; margin: 5px 0;">RFQ</p> </div> </div>	<div style="display: flex; align-items: center;"> <div> <p style="margin: 0;"><b>L25G-SB-250-ABZ-5V/OCR-SC24-S</b></p> <p style="margin: 0; font-size: 0.8em;">Kaihanga: BEI Sensors Whakaahuatanga: ROTARY ENCODER OPTICAL 250PPR I roto i te taonga: 213 pcs</p> <p style="text-align: center; background-color: #ccc; padding: 2px 5px; margin: 5px 0;">RFQ</p> </div> </div>
<div style="display: flex; align-items: center;"> <div> <p style="margin: 0;"><b>L25G-F3-1000-ABZC-28V/V-ED15-S</b></p> <p style="margin: 0; font-size: 0.8em;">Kaihanga: BEI Sensors Whakaahuatanga: ROTARY ENCODER OPTICAL 1000PPR I roto i te taonga: 186 pcs</p> <p style="text-align: center; background-color: #ccc; padding: 2px 5px; margin: 5px 0;">RFQ</p> </div> </div>	<div style="display: flex; align-items: center;"> <div> <p style="margin: 0;"><b>L254XF3S</b></p> <p style="margin: 0; font-size: 0.8em;">Kaihanga: Dielectric Laboratories Whakaahuatanga: LOWPASS FILTER I roto i te taonga: 1312 pcs</p> <p style="text-align: center; background-color: #ccc; padding: 2px 5px; margin: 5px 0;">RFQ</p> </div> </div>
<div style="display: flex; align-items: center;"> <div> <p style="margin: 0;"><b>L25J100</b></p> <p style="margin: 0; font-size: 0.8em;">Kaihanga: Ohmite Whakaahuatanga: RES CHAS MNT 100 OHM 5% 25W I roto i te taonga: 12127 pcs</p> <p style="text-align: center; background-color: #ccc; padding: 2px 5px; margin: 5px 0;">RFQ</p> </div> </div>	<div style="display: flex; align-items: center;"> <div> <p style="margin: 0;"><b>L25G-SB-12,000-T5-ABZC-28V/V-SC18-S</b></p> <p style="margin: 0; font-size: 0.8em;">Kaihanga: BEI Sensors Whakaahuatanga: ROTARY ENCODER OPTICAL 12000PPR I roto i te taonga: 137 pcs</p> <p style="text-align: center; background-color: #ccc; padding: 2px 5px; margin: 5px 0;">RFQ</p> </div> </div>