

Broadcom
connecting everything

Limited

AEDC-5570-B14

Tau Wae: Kaihanga / Waitohu: Whakaahuatanga hua Ngā Rauemi: RoHS Tūnga Waehere Stock Tuhinga mai i Te Ara Tuhi	AEDC-5570-B14 Avago Technologies (Broadcom Limited) ENCODER 3CH 1000CPR 5MM AEDC-5570-B14.pdf Whakahaerehia te kore utu / RoHS 1701 pcs stock Hong Kong DHL/Fedex/TNT/UPS/EMS
-------------------------------------------------------------------------------------------------------------------------------------	----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------

TONO MO TE WHAKAHUA

Ko te whakaahua he tohu. Tirohia nga korero mo nga taipitopito hua.

Ngā whakaaturanga o AEDC-5570-B14

TAU WAE KAIHANGA WHAKAAHUATANGA WHAKAHAERE TOKO WHAKAHAERE / ROHS TŪNGA HE RAHINGA KEI TE WĀTEA PEPA RARAUNGA RAUPAPA TAUMATA WHAKAARO MOE (MSL) WHAKAHAERE TOKO WHAKAHAERE / ROHS TŪNGA	AEDC-5570-B14 Avago Technologies (Broadcom Limited) ENCODER 3CH 1000CPR 5MM Whakahaerehia te kore utu / RoHS 1701 pcs AEDC-5570-B14.pdf * 1 (Unlimited) Lead free / RoHS Compliant
------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------	------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------

Ngā tūtohu e hāngai ana

Avago Technologies (Broadcom Limited) AEDC-5570-B14	AEDC-5570-B14 Kaihiwhi	AEDC-5570-B14 Kaiwhakarato
AEDC-5570-B14 Utu	AEDC-5570-B14 Pikitia	AEDC-5570-B14 Whakaahua
AEDC-5570-B14 PDF Datasheet	AEDC-5570-B14 Download Datasheet	Tuhinga AEDC-5570-B14
AEDC-5570-B14 Stock	Hokona AEDC-5570-B14	Hokona Avago Technologies (Broadcom Limited) AEDC-5570-B14
Avago Technologies (Broadcom Limited) AEDC-5570-B14	Avago Technologies (Broadcom Limited) Kaiwhakarato	Avago Technologies (Broadcom Limited) Kaihiwhi
Avago Technologies (Broadcom Limited) AEDC-5570-B14	Avago Technologies Limited AEDC-5570-B14	Avago Technologies US Inc. AEDC-5570-B14
Avago Technologies AEDC-5570-B14	Avago Technologies (Broadcom Limited) AEDC-5570-B14	Broadcom Limited AEDC-5570-B14

Ngā Hua e hāngai ana

<div style="display: flex; align-items: center;"> <div> <p>AEDC-5570-B12</p> <p>Kaihanga: Avago Technologies (Broadcom Limited) Whakaahuatanga: ENCODER 3CH 1000CPR 6MM I roto i te taonga: 1544 pcs</p> <p style="background-color: #ccc; padding: 2px 10px; text-align: center; font-weight: bold;">RFQ</p> </div> </div>	<div style="display: flex; align-items: center;"> <div> <p>AEDC-5570-J12</p> <p>Kaihanga: Avago Technologies (Broadcom Limited) Whakaahuatanga: ENCODER 3CH 1024CPR 6MM I roto i te taonga: 1662 pcs</p> <p style="background-color: #ccc; padding: 2px 10px; text-align: center; font-weight: bold;">RFQ</p> </div> </div>
<div style="display: flex; align-items: center;"> <div> <p>AEDC-5570-J14</p> <p>Kaihanga: Avago Technologies (Broadcom Limited) Whakaahuatanga: ENCODER 3CH 1024CPR 5MM I roto i te taonga: 1830 pcs</p> <p style="background-color: #ccc; padding: 2px 10px; text-align: center; font-weight: bold;">RFQ</p> </div> </div>	<div style="display: flex; align-items: center;"> <div> <p>AEDC-5570-T12</p> <p>Kaihanga: Avago Technologies (Broadcom Limited) Whakaahuatanga: ENCODER 3CH 2000CPR 6MM I roto i te taonga: 1601 pcs</p> <p style="background-color: #ccc; padding: 2px 10px; text-align: center; font-weight: bold;">RFQ</p> </div> </div>
<div style="display: flex; align-items: center;"> <div> <p>AEDC-5570-T14</p> <p>Kaihanga: Avago Technologies (Broadcom Limited) Whakaahuatanga: ENCODER 3CH 2000CPR 5MM I roto i te taonga: 1716 pcs</p> <p style="background-color: #ccc; padding: 2px 10px; text-align: center; font-weight: bold;">RFQ</p> </div> </div>	<div style="display: flex; align-items: center;"> <div> <p>AEDC-5570-J13</p> <p>Kaihanga: Avago Technologies (Broadcom Limited) Whakaahuatanga: ENCODER 3CH 1024CPR 8MM I roto i te taonga: 1837 pcs</p> <p style="background-color: #ccc; padding: 2px 10px; text-align: center; font-weight: bold;">RFQ</p> </div> </div>
<div style="display: flex; align-items: center;"> <div> <p>AEDC-5570-B13</p> <p>Kaihanga: Avago Technologies (Broadcom Limited) Whakaahuatanga: ENCODER 3CH 1000CPR 8MM I roto i te taonga: 1909 pcs</p> <p style="background-color: #ccc; padding: 2px 10px; text-align: center; font-weight: bold;">RFQ</p> </div> </div>	<div style="display: flex; align-items: center;"> <div> <p>AEDC-5570-T13</p> <p>Kaihanga: Avago Technologies (Broadcom Limited) Whakaahuatanga: ENCODER 3CH 2000CPR 8MM I roto i te taonga: 1498 pcs</p> <p style="background-color: #ccc; padding: 2px 10px; text-align: center; font-weight: bold;">RFQ</p> </div> </div>
<div style="display: flex; align-items: center;"> <div> <p>AEDC-5560-W12</p> <p>Kaihanga: Avago Technologies (Broadcom Limited) Whakaahuatanga: ROTARY ENCODER OPTICAL 2500PPR I roto i te taonga: 1493 pcs</p> <p style="background-color: #ccc; padding: 2px 10px; text-align: center; font-weight: bold;">RFQ</p> </div> </div>	<div style="display: flex; align-items: center;"> <div> <p>AEDC-5560-W13</p> <p>Kaihanga: Avago Technologies (Broadcom Limited) Whakaahuatanga: ROTARY ENCODER OPTICAL 2500PPR I roto i te taonga: 1476 pcs</p> <p style="background-color: #ccc; padding: 2px 10px; text-align: center; font-weight: bold;">RFQ</p> </div> </div>
<div style="display: flex; align-items: center;"> <div> <p>AEDC-5560-Z13</p> <p>Kaihanga: Avago Technologies (Broadcom Limited) Whakaahuatanga: ROTARY ENCODER OPTICAL 5000PPR I roto i te taonga: 1712 pcs</p> <p style="background-color: #ccc; padding: 2px 10px; text-align: center; font-weight: bold;">RFQ</p> </div> </div>	<div style="display: flex; align-items: center;"> <div> <p>AEDC-5560-Z12</p> <p>Kaihanga: Avago Technologies (Broadcom Limited) Whakaahuatanga: ROTARY ENCODER OPTICAL 5000PPR I roto i te taonga: 1481 pcs</p> <p style="background-color: #ccc; padding: 2px 10px; text-align: center; font-weight: bold;">RFQ</p> </div> </div>