

Broadcom
connecting everything

Avago Technologies (Broadcom Limited)

ADNS-5060

Tau Wae:
 Kaihanga / Waitohu:
 Whakaahuatanga hua
 Ngā Rauemi:
 RoHS Tūnga
 Waehere Stock
 Tuhinga mai i
 Te Ara Tuhi

ADNS-5060
 Avago Technologies (Broadcom Limited)
 IC USB OPT MOUSE SENSOR HS 8-DIP
 ADNS-5060.pdf
 Whakahaerehia te kore utu / RoHS
 2987 pcs stock
 Hong Kong
 DHL/Fedex/TNT/UPS/EMS

TONO MO TE WHAKAHUA

Ko te whakaahua he tohu. Tirohia nga korero mo nga taipitopito hua.

Ngā whakaaturanga o ADNS-5060

TAU WAE	ADNS-5060
KAIHANGA	Avago Technologies (Broadcom Limited)
WHAKAAHUATANGA	IC USB OPT MOUSE SENSOR HS 8-DIP
WHAKAHAERE TOKO WHAKAHAERE / ROHS TŪNGA	Whakahaerehia te kore utu / RoHS
HE RAHINGA KEI TE WĀTEA	2987 pcs
PEPA RARAUNGA	ADNS-5060.pdf
RAUPAPA	-
TAUMATA WHAKAARO MOE (MSL)	1 (Unlimited)
WHAKAHAERE TOKO WHAKAHAERE / ROHS TŪNGA	Lead free / RoHS Compliant
WHAKAAHUATANGA TAIPITOPITO	Optical Sensor

Ngā tūtohu e hāngai ana

Avago Technologies (Broadcom Limited) ADNS-5060	ADNS-5060 Kaiwhiwhi	ADNS-5060 Kaiwhakarato
ADNS-5060 Utu	ADNS-5060 Pikitia	ADNS-5060 Whakaahua
ADNS-5060 PDF Datasheet	ADNS-5060 Download Datasheet	Tuhinga ADNS-5060
ADNS-5060 Stock	Hokona ADNS-5060	Hokona Avago Technologies (Broadcom Limited) ADNS-5060
Avago Technologies (Broadcom Limited) ADNS-5060	Avago Technologies (Broadcom Limited) Kaiwhakarato	Avago Technologies (Broadcom Limited) Kaiwhiwhi
Avago Technologies (Broadcom Limited) ADNS-5060	Avago Technologies Limited ADNS-5060	Avago Technologies US Inc. ADNS-5060
Avago Technologies ADNS-5060	Avago Technologies (Broadcom Limited) ADNS-5060	Broadcom Limited ADNS-5060

Ngā Hua e hāngai ana

<div style="border: 1px solid #ccc; padding: 5px;"> <p>ADNS-5090 Kaihanga: Avago Technologies (Broadcom Limited) Whakaahuatanga: IC USB OPT MOUSE SENSOR LP 8-DIP I roto i te taonga: 3988 pcs</p> <p style="text-align: center; background-color: #ccc; padding: 2px; font-weight: bold;">RFQ</p> </div>	<div style="border: 1px solid #ccc; padding: 5px;"> <p>ADNS-5110-001 Kaihanga: Avago Technologies (Broadcom Limited) Whakaahuatanga: IC OPT MOUSE TRIM LENS ADNS-5090 I roto i te taonga: 5307 pcs</p> <p style="text-align: center; background-color: #ccc; padding: 2px; font-weight: bold;">RFQ</p> </div>
<div style="border: 1px solid #ccc; padding: 5px;"> <p>ADNS-5200 Kaihanga: Avago Technologies (Broadcom Limited) Whakaahuatanga: BLACK CLIP FOR ADNS-5000 I roto i te taonga: 5564 pcs</p> <p style="text-align: center; background-color: #ccc; padding: 2px; font-weight: bold;">RFQ</p> </div>	<div style="border: 1px solid #ccc; padding: 5px;"> <p>ADNS-5030 Kaihanga: Avago Technologies (Broadcom Limited) Whakaahuatanga: SENSOR OPTICAL MOUSE 8-DIP I roto i te taonga: 3535 pcs</p> <p style="text-align: center; background-color: #ccc; padding: 2px; font-weight: bold;">RFQ</p> </div>
<div style="border: 1px solid #ccc; padding: 5px;"> <p>ADNS-5070 Kaihanga: Avago Technologies (Broadcom Limited) Whakaahuatanga: IC USB OPT MOUSE SENSOR 8-DIP I roto i te taonga: 2881 pcs</p> <p style="text-align: center; background-color: #ccc; padding: 2px; font-weight: bold;">RFQ</p> </div>	<div style="border: 1px solid #ccc; padding: 5px;"> <p>ADNS-5020 Kaihanga: Avago Technologies (Broadcom Limited) Whakaahuatanga: SENSOR OPTICAL MOUSE 8-DIP I roto i te taonga: 6960 pcs</p> <p style="text-align: center; background-color: #ccc; padding: 2px; font-weight: bold;">RFQ</p> </div>
<div style="border: 1px solid #ccc; padding: 5px;"> <p>ADNS-4000 Kaihanga: Avago Technologies (Broadcom Limited) Whakaahuatanga: SENSOR OPTICAL MOUSE LP 8DIP I roto i te taonga: 4371 pcs</p> <p style="text-align: center; background-color: #ccc; padding: 2px; font-weight: bold;">RFQ</p> </div>	<div style="border: 1px solid #ccc; padding: 5px;"> <p>ADNS-5050 Kaihanga: Avago Technologies (Broadcom Limited) Whakaahuatanga: IC USB OPT MOUSE SENSOR HS 8-DIP I roto i te taonga: 4837 pcs</p> <p style="text-align: center; background-color: #ccc; padding: 2px; font-weight: bold;">RFQ</p> </div>
<div style="border: 1px solid #ccc; padding: 5px;"> <p>ADNS-5000 Kaihanga: Avago Technologies (Broadcom Limited) Whakaahuatanga: IC USB OPT MOUSE SENSOR 18-DIP I roto i te taonga: 6314 pcs</p> <p style="text-align: center; background-color: #ccc; padding: 2px; font-weight: bold;">RFQ</p> </div>	<div style="border: 1px solid #ccc; padding: 5px;"> <p>ADNS-5100 Kaihanga: Avago Technologies (Broadcom Limited) Whakaahuatanga: LENS ROUND FOR ADNS-5000 I roto i te taonga: 6309 pcs</p> <p style="text-align: center; background-color: #ccc; padding: 2px; font-weight: bold;">RFQ</p> </div>
<div style="border: 1px solid #ccc; padding: 5px;"> <p>ADNS-5020-EN Kaihanga: Avago Technologies (Broadcom Limited) Whakaahuatanga: IC USB OPT MOUSE SENSOR HS 8-DIP I roto i te taonga: 4088 pcs</p> <p style="text-align: center; background-color: #ccc; padding: 2px; font-weight: bold;">RFQ</p> </div>	<div style="border: 1px solid #ccc; padding: 5px;"> <p>ADNS-5100-001 Kaihanga: Avago Technologies (Broadcom Limited) Whakaahuatanga: LENS TRIM FOR ADNS-5000 I roto i te taonga: 6437 pcs</p> <p style="text-align: center; background-color: #ccc; padding: 2px; font-weight: bold;">RFQ</p> </div>